



Product Description

Plusline Large

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime of 2000 hours

Features

- Clear tubular quartz bulb
- Constant light output during life
- Colour temperature 2900K
- Excellent colour rendering (R a = 100)
- Limited burning position: $\pm 4^\circ$

Application

- Typically used in outdoor applications: billboards, car parks, security lighting and construction sites
- Also used in Indoor applications: homes, offices, shops and museums



Versions



LPPR HLINEAR 0001

Plusline Large

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
Plusline L 1000W R7s 230V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
Plusline L 1000W R7s 240V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm
Plusline L 1500W R7s 230V 1CT/10	11 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

Product	D (max)	C (max)
Plusline L 500W 240-250V CL 1SL/4X50CT	12.75 mm	185.7 mm

General Information	
Rated Lifetime (Hours)	2,000 hour(s)
Mechanical and Housing	
Bulb Finish	Clear

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime	Operating Position
923932143241	Plusline L 1000W R7s 230V 1CT/10	R7s	8,000	2,000 hour(s)	P4
923932143293	Plusline L 1000W R7s 230V 1CT/10	R7s	8,000	2,000 hour(s)	P4
923932145741	Plusline L 1000W R7s 240V 1CT/10	R7s	8,000	2,000 hour(s)	P4

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime	Operating Position
923932243241	Plusline L 1500W R7s 230V 1CT/10	R7s	8,000	2,000 hour(s)	P4
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	R7S	-	-	UNIVERSAL

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923932143241	Plusline L 1000W R7s 230V 1CT/10	2900 K	100	21.5 lm/W	21,500 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923932143293	Plusline L 1000W R7s 230V 1CT/10	2900 K	100	21.5 lm/W	21,500 lm

Plusline Large

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923932145741	Plusline L 1000W R7s 240V 1CT/10	2900 K	100	21.5 lm/W	21,500 lm
923932243241	Plusline L 1500W R7s 230V 1CT/10	2900 K	100	22 lm/W	33,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	-	-	8,900 lm

Operating and Electrical

Order Code	Full Product Name	Warm-up time to 60% light	Lamp Current (Nom)	Voltage (Nom)	Power Consumption	Starting Time (Nom)
923932143241	Plusline L 1000W R7s 230V 1CT/10	instant full light s	4.35 A	230 V	1,000 W	0.0 s
923932143293	Plusline L 1000W R7s 230V 1CT/10	instant full light s	4.35 A	230 V	1,000 W	0.0 s
923932145741	Plusline L 1000W R7s 240V 1CT/10	instant full light s	4.17 A	240 V	1,000.0 W	0.0 s
923932243241	Plusline L 1500W R7s 230V 1CT/10	instant full light s	6.52 A	230 V	1,500.0 W	0.0 s
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-	-	240-250 V	500 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
923932143241	Plusline L 1000W R7s 230V 1CT/10	Yes
923932143293	Plusline L 1000W R7s 230V 1CT/10	Yes
923932145741	Plusline L 1000W R7s 240V 1CT/10	Yes

Order Code	Full Product Name	Dimmable
923932243241	Plusline L 1500W R7s 230V 1CT/10	Yes
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
923932143241	Plusline L 1000W R7s 230V 1CT/10	T11
923932143293	Plusline L 1000W R7s 230V 1CT/10	T11
923932145741	Plusline L 1000W R7s 240V 1CT/10	T11

Order Code	Full Product Name	Bulb Shape
923932243241	Plusline L 1500W R7s 230V 1CT/10	T11
923880345799	Plusline L 500W 240-250V CL 1SL/4X50CT	T37

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923932143241	Plusline L 1000W R7s 230V 1CT/10	1000 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923932143293	Plusline L 1000W R7s 230V 1CT/10	1000 kWh

