



# Product Description

## Plusline Compact

Mains-voltage linear lamp giving white halogen light

### Benefits

- Bright halogen light
- Bright halogen light
- Long lifetime
- Long lifetime

### Features

- Clear tubular quartz bulb
- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Excellent colour rendering
- Constant light output during life
- Constant light output during life

### Application

- Typically used in shop lighting applications
- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites
- Outdoor: billboards, car parks, security lighting and construction sites


# Plusline Compact

## Versions



LPPR HDECOMP R7s 10

## Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 150W R7s 230V 1CT/10X10F	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

