



Product Description

Plusline Compact

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Long lifetime

Features

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

Application

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites


Plusline Compact

Versions



R7s/10, T11/T12

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline C 100W R7s 240V 1BC/10	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm
Plusline C 150W R7s 230V 1CT/ 10X10F	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm
Plusline C 100W R7s 230V 1CT/ 10X10F	12 mm	76.5 mm	74.9 mm	73.3 mm	78 mm
Plusline C 150W R7s 240V 1BC/12	15 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

Plusline Compact

Approval and Application

Energy Efficiency Label (EEL) D

Controls and Dimming

Dimmable Yes

Operating and Electrical

Starting Time (Nom) 0.0 s

General Information

Cap-Base R7S
 Nominal Lifetime (Nom) 2000 h
 Operating Position UNIVERSAL
 Rated Lifetime (Hours) 2000 h

Luminaire Design Requirements

Bulb Temperature (Max) 900 °C

Light Technical

Color Rendering Index (Nom) 100

Mechanical and Housing

Bulb Finish Clear
 Bulb Shape T3

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Rated) (Nom)
923919943202	Plusline C 150W R7s 230V 1CT/10X10F	0.65 A	230 V	150 W
923919945709	Plusline C 150W R7s 240V 1BC/12	0.63 A	240 V	150 W
923920043290	Plusline C 100W R7s 230V 1CT/10X10F	0.43 A	230 V	100 W
923920045792	Plusline C 100W R7s 240V 1BC/10	0.42 A	240 V	100 W

Light Technical

Order Code	Full Product Name	Correlated		
		Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)
923919943202	Plusline C 150W R7s - 230V 1CT/10X10F	-	16 lm/W	2400 lm
923919945709	Plusline C 150W R7s - 240V 1BC/12	-	16 lm/W	2400 lm
923920043290	Plusline C 100W R7s 230V 1CT/10X10F	2800 K	15.5 lm/W	1550 lm

Order Code	Full Product Name	Correlated		
		Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)
923920045792	Plusline C 100W R7s 240V 1BC/10	-	15.5 lm/W	1550 lm

