



# Product Description

## Plusline Small

Mains-voltage linear lamp giving white halogen light

### Benefits

- Bright halogen light
- Long lifetime

### Features

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

### Application

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites

### Versions



# Plusline Small

## Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline S 300W R7s 230V 1CT/ 10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
Plusline S 500W R7s 230V 1CT/ 10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

General Information	
Rated Lifetime (Hours)	2,000 hour(s)
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Voltage (Nom)	230 V
Starting Time (Nom)	0.0 s
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3

## General Information

Order Code	Full Product Name	Cap-Base
924735444201	Plusline S 300W R7s 230V 1CT/10X10F	R7s
924735544201	Plusline S 500W R7s 230V 1CT/10X10F	R7S

## Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
924735444201	Plusline S 300W R7s 230V 1CT/ 10X10F	17 lm/W	5,114 lm



# Plusline Small

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
924735544201	Plusline S 500W R7s 230V 1CT/10X10F	19.3 lm/W	9,660 lm

## Operating and Electrical

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
924735444201	Plusline S 300W R7s 230V 1CT/ 10X10F	1.3 A	300 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
924735544201	Plusline S 500W R7s 230V 1CT/ 10X10F	2.17 A	500 W

