



# Product Description

## Plusline Small

Mains-voltage linear lamp giving white halogen light

### 优点

- Bright halogen light
- Long lifetime

### 特点

- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Constant light output during life

### 应用

- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites