



# Trusted quality for best performance

## Essential MV MR16 Alu

The Essential MV MR16 Alu is part of the Philips "Value for Money" ranges. It is ideal for professional end-users looking for accent light - without a transformer - to create contrast in shops, hotels and restaurants.

### Benefits

- Accent light to create the perfect focus on the objects to be lit
- Aluminum reflector to direct most of the heat to the front, ideal for heat-sensitive ceilings and luminaires
- Best dimmability to meet different brightness requirements

### Features

- Bright sparkling light to create ambient atmosphere.
- Excellent color rendering (Ra=100) to present the true color of objects.
- Instant start to offer direct brightness from the moment switch on.
- No mercury to ensure the safety usage.
- Reliable quality to be trusted.

### Application

- Shops, hotels and restaurants


# Essential MV MR16 Alu

## Versions



LPPR HTWIST 0002

## Dimensional drawing



Product	D (max)	C (max)
ESS MR16 Alu 50W GU10 230V 36D 1CT	51 mm	51 mm

