



Product Description

PARTYTONE PAR38 Colour

Coloured pressed-glass 121 mm diameter reflector lamp

优点

- Gives striking decorative effects, both indoors and outdoors
- 20% lower power consumption compared with conventional coloured PAR lamps

特点

- Weatherproof silicon lacquer coating on the refractor face in a choice of colours
- Flood beam width

应用


- Parks, public and private gardens
- Festive illumination
- Restaurants, bars, dance halls, nightclubs
- Show-window displays, fountains and 'Son et Lumiere' spectacles
- Can be installed outdoors without any protection, provided they are used in a watertight lampholder
- For outdoor use, a heat-resistant rubber ring must be fitted between the lamp and the lampholder

PARTYTONE PAR38 Colour

Versions



二维绘图



Product	D (max)	C (max)
PARTYTONE 80W E27 230V PAR38 RE 1CT/15	123 mm	137 mm
PAR38 80W E27 220-240V BLUE 1CT/15	123 mm	137 mm

PARTYTONE PAR38 Colour

應用	
能源消耗 kWh/1000 h	80 kWh
能源效益標章 (EEL)	E
控制調光	
可調光	Yes
運作和電氣	
電壓 (標稱)	230 V
功率 (額定)(標稱)	80.0 W
起始時間 (標稱)	0.0 s
暖機時間 (60% 亮度) (標稱)	instant full light
基本資訊	
接口	E27
正常使用壽命 (標稱)	2000 h
操作位置	UNIVERSAL
額定壽命 (小時)	2000 h
切換週期	8000X
照明科技	
相關色溫 (標稱)	2700 K
顯色指數 (Nom)	100
機械和殼體	
燈泡形狀	PAR38

照明科技

Order Code	Full Product Name	光通量 (額定)(標稱)
923810944279	PAR38 80W E27 220-240V BLUE 1CT/15	45 lm
923811244279	PARTYTONE 80W E27 230V PAR38 RE 1CT/15	110 lm

機械和殼體

Order Code	Full Product Name	燈泡表層
923810944279	PAR38 80W E27 220-240V BLUE 1CT/15	藍色

Order Code	Full Product Name	燈泡表層
923811244279	PARTYTONE 80W E27 230V PAR38 RE 1CT/15	紅色

