



Product Description

SPOTONE Ring Mirror Spotlight

Reflector lamps based on advanced spotlighting technology

Benefits

- Centre-beam intensities up to 100% higher than with conventional reflector lamps

Features

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- Wide choice of diameters and wattages
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile
- Universal burning position

Application


- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes

SPOTONE Ring Mirror Spotline

Versions



Dimensional drawing



Product	D
REF SPOT 40W E27 240V NR63 30DFR2CT/4X3F	63 mm

