



The original!

PL-S 2 Pin

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

优点

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

特点

- 2-pin base with a housing incorporating the special instant starter and capacitor .
For use on conventional copper iron ballasts and the radio interference suppression capacitor is installed. Dimming is not possible
- Lamp characteristics are influenced by operating conditions and control gear used

应用


- Designed for use in hotels, restaurants, theatres and homes
- Suitable for use in signs, corridors, security and orientation lighting

PL-S 2 Pin

Versions



二维绘图



Product	D (max)	D1 (max)	C (max)
PL-S 13W/865/2P 1CT/25	27.1 mm	13 mm	178.2 mm
PL-S 7W/827/2P 1CT/25	27.1 mm	13 mm	135.5 mm
PL-S 9W/827/2P 1CT/25	27.1 mm	13 mm	167.5 mm
PL-S 9W/840/2P 1CT/25	27.1 mm	13 mm	167.5 mm
PL-S 7W/840/2P 1CT/25	27.1 mm	13 mm	135.5 mm

應用	
能源效益標章 (EEL)	B
汞 (Hg) 含量 (標稱)	1.4 mg
控制調光	
可調光	No
基本資訊	
壽命 (故障率 50%) (標稱)	8000 h

運作和電氣

Order Code	Full Product Name	燈具電流 (標稱)	電壓 (標稱)	功率 (額定)(標稱)
927901108265	PL-S 7W/827/2P 1CT/25	0.175 A	47 V	7.1 W
927901108465	PL-S 7W/840/2P 1CT/25	0.175 A	46 V	7.1 W
927901708265	PL-S 9W/827/2P 1CT/25	0.170 A	60 V	8.6 W

Order Code	Full Product Name	燈具電流 (標稱)	電壓 (標稱)	功率 (額定)(標稱)
927901708465	PL-S 9W/840/2P 1CT/25	0.170 A	60 V	8.6 W
927902886565	PL-S 13W/865/2P 1CT/25	0.290 A	56 V	13.0 W

基本資訊

Order Code	Full Product Name	接口
927901108265	PL-S 7W/827/2P 1CT/25	G23
927901108465	PL-S 7W/840/2P 1CT/25	G23
927901708265	PL-S 9W/827/2P 1CT/25	G23

Order Code	Full Product Name	接口
927901708465	PL-S 9W/840/2P 1CT/25	G23
927902886565	PL-S 13W/865/2P 1CT/25	GX23

PL-S 2 Pin

照明科技 (1/2)

Order Code	Full Product Name	色碼	色彩名稱	相關色溫 (標稱)	顯色指數 (Nom)	流明維持率 2000 h (標稱)	流明維持率 5000 h (標稱)	光效 (額定) (Nom)
927901108265	PL-S 7W/827/2P 1CT/25	827	白熾 白色	2700 K	83	90 %	81 %	57 lm/W
927901108465	PL-S 7W/840/2P 1CT/25	840	冷 白色 (CW)	4000 K	82	90 %	80 %	57 lm/W
927901708265	PL-S 9W/827/2P 1CT/25	827	白熾 白色	2700 K	>80	90 %	81 %	69 lm/W
927901708465	PL-S 9W/840/2P 1CT/25	840	冷 白色 (CW)	4000 K	82	90 %	85 %	67 lm/W
927902886565	PL-S 13W/865/2P 1CT/25	865	冷 日光	6500 K	82	82 %	77 %	63 lm/W

照明科技 (2/2)

Order Code	Full Product Name	光通量 (標稱)
927901108265	PL-S 7W/827/2P 1CT/25	405 lm
927901108465	PL-S 7W/840/2P 1CT/25	405 lm
927901708265	PL-S 9W/827/2P 1CT/25	600 lm

Order Code	Full Product Name	光通量 (標稱)
927901708465	PL-S 9W/840/2P 1CT/25	600 lm
927902886565	PL-S 13W/865/2P 1CT/25	900 lm

