



# The original!

## PL-S 2 Pin

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

### Features

- 2-pin base with a housing incorporating the special instant starter and capacitor .  
For use on conventional copper iron ballasts and the radio interference suppression capacitor is installed. Dimming is not possible
- Lamp characteristics are influenced by operating conditions and control gear used

### Application


- Designed for use in hotels, restaurants, theatres and homes
- Suitable for use in signs, corridors, security and orientation lighting

# PL-S 2 Pin

## Versions



## Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-S 9W/827/2P 1CT/25	27.1 mm	13 mm	167.5 mm

