



Efficient fluorescent lighting with improved color rendering

TL-D LIFEMAX Super 80

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

优点

- Good color rendering
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Create atmospheres from warm white to cool daylight

特点

- Highly efficient 3-band fluorescent coating
- High initial light output compared with standard colors
- Low mercury dose
- Can be used with conventional or electronic gear
- Higher efficacy is achieved with electronic gear

应用


- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc.

TL-D LIFEMAX Super 80

Versions



二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/830 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 30W/840 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
TL-D 30W/865 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

應用	
能源效益標章 (EEL)	A
汞 (Hg) 含量 (標稱)	2.0 mg
控制調光	
可調光	Yes
運作和電氣	
燈具電流 (標稱)	0.360 A
基本資訊	
接口	G13
壽命 (預熱故障率 50%) (標稱)	20000 h
壽命 (故障率 10%) (標稱)	10000 h
壽命 (故障率 50%) (標稱)	13000 h
照明科技	
流明維持率 2000 h (標稱)	96 %
流明維持率 5000 h (標稱)	94 %
機械和殼體	
燈泡形狀	T8

運作和電氣

Order Code	Full Product Name	電壓 (標稱)	功率 (額定)(標稱)
927980283036	TL-D 18W/830 1SL/25	59 V	18 W
927981284036	TL-D 30W/840 1SL/25	98 V	30 W
927981286536	TL-D 30W/865 1SL/25	98 V	30 W

照明科技 (1/2)

TL-D LIFEMAX Super 80

Order Code	Full Product Name	色碼	色彩名稱	相關色溫 (標稱)	顯色指數 (Nom)
927980283036	TL-D 18W/830 1SL/25	830	暖白色 (WW)	3000 K	83
927981284036	TL-D 30W/840 1SL/25	840	冷白色 (CW)	4000 K	82

Order Code	Full Product Name	色碼	色彩名稱	相關色溫 (標稱)	顯色指數 (Nom)
927981286536	TL-D 30W/865 1SL/25	865	冷日光	6500 K	80

照明科技 (2/2)

Order Code	Full Product Name	光效 (額定) (Nom)	光通量 (額定)(標稱)
927980283036	TL-D 18W/830 1SL/25	75 lm/W	1350 lm
927981284036	TL-D 30W/840 1SL/25	80 lm/W	2400 lm

Order Code	Full Product Name	光效 (額定) (Nom)	光通量 (額定)(標稱)
927981286536	TL-D 30W/865 1SL/25	77 lm/W	2300 lm

