



# Circular shaped, basic fluorescent lighting

## TL-E LIFEMAX Standard Colours

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.

### 优点

- Standard colours with moderate colour rendering (R a 50 - 70)
- Create atmospheres from warm white to cool daylight

### 特点

- Available in varying colour designations
- Symmetrical, omni-directional light distribution

### 应用


- Suitable for use in a wide range of luminaires for various purposes, including many decorative luminaires
- Ideal for 'human' applications such as schools, offices, shops, theatres etc. where colour rendering is not an important factor

# TL-E LIFEMAX Standard Colours

## Versions



## 二维绘图



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 22W/54-765	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
1CT/20						

