




TL10 Plus

The T10 Plus tubular fluorescent lamp line is available in 20W and 40W and is suitable for new installations, as well as replacement in existing installations. They work in conjunction with electromagnetic ballasts (Conventional and Quick Start) and electronic ballasts. Recommended for all types of installations, they deliver the reliability and guarantee of Philips applications.

Dimensional drawing



Product
T10 PLUS 20W/750 1SL/25
T10 PLUS 40W/750 1SL/25

TL10 Plus

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	69
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T10
Approval and Application	
Mercury (Hg) Content (Nom)	8.5 mg

Light Technical

Order Code	Full Product Name	Luminous Flux
928034607502	T10 PLUS 20W/750 1SL/25	1,060 lm

Order Code	Full Product Name	Luminous Flux
928034707502	T10 PLUS 40W/750 1SL/25	2,700 lm

Operating and Electrical

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
928034607502	T10 PLUS 20W/750 1SL/25	0.36 A	62.0 V	20 W

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
928034707502	T10 PLUS 40W/750 1SL/25	0.42 A	112 V	40 W

