



Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features



- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application



- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions



Dimensional drawing




Product	D	C
LEDClassic 4.5-50W B35 E14 WW CL D APR	35 mm	118 mm


Product	D	C
LEDClassic 7.5-70W A60 E27 WW CL D APR	60 mm	112 mm
LEDClA 7.5-60W A60 E27 2000K GOLD APR	60 mm	112 mm

Classic filament LEDbulbs


Dimensional drawing



Product	D	C
LEDClassic 4.5-50W P45 E27 WW CL D APR	45 mm	89 mm



Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm



Product	D	C
LEDClassic 7-70W ST64 E27 WW CL D APR	64 mm	148 mm

Classic filament LEDbulbs

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s

General Information

Nominal Lifetime (Nom)	15000 h
Rated Lifetime (Hours)	15000 h
Switching Cycle	20000X

Light Technical

Colour Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	5 kWh	A++
929001227608	LEDClassic 4.5-50W P45 E27 WW CL D APR	5 kWh	A++
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	8 kWh	A+
929001228108	LEDCla 7.5-60W A60 E27 2000K GOLD APR	8 kWh	A+
929001228608	LEDClassic 7-70W ST64 E27 WW CL D APR	7 kWh	A++
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	7 kWh	A+

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	4.5 W
929001227608	LEDClassic 4.5-50W P45 E27 WW CL D APR	4.5 W
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	7.5 W

Order Code	Full Product Name	Power (Rated) (Nom)
929001228108	LEDCla 7.5-60W A60 E27 2000K GOLD APR	7.5 W
929001228608	LEDClassic 7-70W ST64 E27 WW CL D APR	7 W
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	7 W

General Information

Order Code	Full Product Name	Cap-Base
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	E14
929001227608	LEDClassic 4.5-50W P45 E27 WW CL D APR	E27
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	E27

Order Code	Full Product Name	Cap-Base
929001228108	LEDCla 7.5-60W A60 E27 2000K GOLD APR	E27
929001228608	LEDClassic 7-70W ST64 E27 WW CL D APR	E27
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	E27

Light Technical

Order Code	Full Product Name	Colour Code	Correlated Colour Temperature (Nom)		Luminous Flux (Nom)	Luminous Flux (Rated)
			Temperature (Nom)	Luminous Flux (Nom)		
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	827	2700 K	470 lm	470 lm	
929001227608	LEDClassic 4.5-50W P45 E27 WW CL D APR	827	2700 K	470 lm	470 lm	
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	827	2700 K	806 lm	806 lm	
929001228108	LEDCla 7.5-60W A60 E27 2000K GOLD APR	820	2000 K	600 lm	600 lm	

Order Code	Full Product Name	Colour Code	Correlated Colour Temperature (Nom)		Luminous Flux (Nom)	Luminous Flux (Rated)
			Temperature (Nom)	Luminous Flux (Nom)		
929001228608	LEDClassic 7-70W ST64 E27 WW CL D APR	827	2700 K	806 lm	806 lm	
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	820	2000 K	630 lm	630 lm	

Mechanical and Housing

Classic filament LEDbulbs

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	Clear (CL)	B35
929001227608	LEDClassic 4.5-50W P45 E27 WW CL D APR	Clear (CL)	P45
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	Clear (CL)	A60
929001228108	LEDClas 7.5-60W A60 E27 2000K GOLD APR	Gold-Clear (GO-CL)	A60
929001228608	LEDClassic 7-70W ST64 E27 WW CL D APR	Clear (CL)	ST64
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	Gold-Clear (GO-CL)	G120

