



# ColorReach Compact Powercore RGBW/RGBA - High-performance compact architectural floodlight

## ColorReach Compact Powercore RGBW/RGBA

ColorReach Compact Powercore RGBW/RGBA is a high-performance architectural floodlight that represents the next generation in exterior illumination. It is ideally suited to dynamic lighting of large-scale façades and structures. These versions combine separate 4-channel LED sources in a single fixture to increase the total number of possible color combinations, including pastels, as well as delivering improved warmer tones and higher-quality white light than conventional RGB systems. A custom-designed 6° collimator optic creates a high-quality beam without compromising on performance. Secondary accessories allow customization and beam manipulation, ensuring flexibility for even the trickiest applications.

### Benefits

- 4-channel
- Color consistency and beam uniformity
- Suitable for long-throw, high-punch applications

# ColorReach Compact Powercore RGBW/RGBA

## Features

- Powercore® technology to directly accept line voltage
- Estimated output of up to 5,400 lumens when full-on
- Custom-designed 6° collimator optic
- Optional spread lenses of 8°, 13°, 23°, 40°, 63°, and 5° x 17°
- Rugged mounting bracket allows simple positioning and fixture rotation
- Complete set of accessories including glare shields and glare mask (cut-off 45°) attach directly to secondary diffuser trim bezels

## Application

- Illumination of large architectural façades
- Designed for large-scale installation, e.g. commercial skyscrapers, casinos, large retail exteriors, bridges, piers, public monuments, and themed attractions

## Versions



## Product details

ColorReach Compact Powercore  
four channel floodlight LED fixture  
back view



ColorReach Compact Powercore  
four channel floodlight LED fixture  
front view



ColorReach Compact Powercore  
four channel floodlight LED fixture  
side view



## ColorReach Compact Powercore RGBW/RGBA

