



ColorReach Powercore gen2 RGBW/RGBA - Premium long-throw exterior LED floodlight with intelligent colour light

ColorReach Powercore gen2 RGBW/RGBA

ColorReach Powercore gen2 RGBW/RGBA high-performance LED luminaires are premium exterior long-throw dynamic colour-changing luminaires for lighting tall buildings, bridges and iconic structures. ColorReach Powercore offers a range of accessories that allow for customisable beam angles for floodlighting, spotlighting, wall washing and grazing, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing.

Benefits

- 4-channel
- Colour consistency and beam uniformity
- Suitable for long-throw, high-punch applications

ColorReach Powercore gen2 RGBW/RGBA

Features

- Powercore® technology to directly accept line voltage
- Estimated output of up to 10,000 lumens when full-on
- Custom-designed 6° collimator optic
- Optional spread lenses of 8°, 13°, 23°, 43°, 63°, and 5° x 17°
- Rugged mounting bracket allows simple positioning and fixture rotation
- Complete set of accessories including glare shields and glare mask (cut-off 45°) attach directly to secondary diffuser trim bezels


Application

- Illumination of large architectural façades
- Designed for large-scale installation, e.g. commercial skyscrapers, casinos, large retail exteriors, bridges, piers, public monuments and themed attractions

Versions



Product details



ColorReach Powercore gen2 four
channel floodlight LED fixture back
view



ColorReach Powercore gen2 four
channel floodlight LED fixture
front view



ColorReach Powercore gen2 four
channel floodlight LED fixture side
view

ColorReach Powercore gen2 RGBW/RGBA

