



Philips TrueLine recessed: True line of light

TrueLine, recessed

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

Features

- Highly-uniform lighting with excellent glare control ($UGR < 19$, $L65 < 3000 \text{cd/m}^2$)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI > 90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options

Application

- Offices
- Education
- Retail

Warnings and Safety


- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions




TrueLine Recessed-U0

Dimensional drawing



Dimensional drawing



Product details

TrueLine_recessed-
RC530B_PCV_L1130-DP.tif



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



Product details



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-1DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-2DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI5-
DPP.tif



TrueLine-
RC534B_SM534C_SP534P-DPP.tif



TrueLine_Recessed-U3



TrueLine_Recessed-U0

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	≥90
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Color	White
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%
Suitable for random switching	No

General Information

Order Code	Full Product Name	Embedded control	Product family code
97161500	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	-	RC530B
97185100	RC532B LED25S/940 PSD W8L113 VPC PI5	-	RC532B
97173800	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	-	RC531B
97146200	RC530B LED15S/940 PSD W8L113 PCV PI5	-	RC530B
97150900	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	-	RC530B
97182000	RC532B LED19S/940 PSD W8L141 PCV PI5	-	RC532B
97149300	RC530B LED31S/940 PSD W8L141 PCV PI5	-	RC530B
97193600	RC533B LED15S/940 PSD W8L113 PCV PI5	-	RC533B
97159200	RC530B LED43S/940 PSD W8L141 PCV PI5	-	RC530B
97172100	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	-	RC531B
97170700	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	-	RC531B
97166000	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	-	RC530B
97147900	RC530B LED19S/940 PSD W8L141 PCV PI5	-	RC530B
97153000	RC530B LED34S/940 PSD W8L113 PCV PI5	-	RC530B
97169100	RC531B LED15S/930 PSD W8L113 PCV PI5	-	RC531B
97171400	RC531B LED15S/940 PSD W8L113 PCV PI5	-	RC531B
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	-	RC532B
97184400	RC532B LED25S/940 PSD W8L113 PCV PI5	-	RC532B
97178300	RC531B LED31S/940 PSD W8L141 PCV PI5	-	RC531B
97197400	RC533B LED31S/940 PSD W8L141 PCV PI5	-	RC533B
97165300	RC530B LED50S/940 PSD W8L141 PCV PI5	-	RC530B
97174500	RC531B LED19S/940 PSD W8L141 PCV PI5	-	RC531B
97194300	RC533B LED19S/940 PSD W8L141 PCV PI5	-	RC533B
97158500	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	-	RC530B
97154700	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	-	RC530B
97320600	RC530B LED34S/TW9 DIA W8L113 PCV PI5	-	RC530B
97322000	RC530B LED40S/TW9 DIA W8L113 PCV PI5	-	RC530B
97323700	RC530B LED50S/TW9 DIA W8L145 PCV PI5	-	RC530B
97328200	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	-	RC530B
97329900	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	-	RC530B
97186800	RC532B LED31S/940 PSD W8L141 PCV PI5	-	RC532B
97188200	RC532B LED43S/940 PSD W8L141 PCV PI5	-	RC532B
97180600	RC531B LED31S/940 W8L150 VPC ELP3 PI6	-	RC531B
97177600	RC531B LED19S/940 W8L150 VPC ELP3 PI6	-	RC531B
97168400	RC530B LED50S/940 W8L150 VPC ELP3 PI6	-	RC530B
97164600	RC530B LED43S/940 W8L150 VPC ELP3 PI6	-	RC530B
97160800	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	-	RC530B
97163900	RC530B LED43S/940 W8L145 PCV ELP3 PI6	-	RC530B
97167700	RC530B LED50S/940 W8L145 PCV ELP3 PI6	-	RC530B
97176900	RC531B LED19S/940 W8L145 PCV ELP3 PI6	-	RC531B
97179000	RC531B LED31S/940 W8L145 PCV ELP3 PI6	-	RC531B
97175200	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	-	RC531B
97199800	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	-	RC534B
97201800	RC534B LED50S/940 PSD W8L141 PCV PI5	-	RC534B
97200100	RC534B LED43S/940 PSD W8L141 PCV PI5	-	RC534B
97203200	RC535B LED50S/940 PSD W8L141 PCV PI5	-	RC535B
97202500	RC535B LED43S/940 PSD W8L141 PCV PI5	-	RC535B
97157800	RC530B LED40S/940 POE W8L120 VPC U3	Interact Ready light source with multi-sensor (upgradable)	RC530B

Order Code	Full Product Name	Embedded control	Product family code
97190500	RC532B LED43S/940 SRD W8L145 PCV U4 W	Upgradable sensor slot with SNS210 sensor	RC532B
97155400	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	Upgradable sensor slot with SNS210 sensor	RC530B
97151600	RC530B LED34S/930 SRD W8L120 VPC U4 W	Upgradable sensor slot with SNS210 sensor	RC530B
97152300	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	Upgradable sensor slot with SNS210 sensor	RC530B
97148600	RC530B LED25S/930 SRD W8L120 VPC U4 W	Upgradable sensor slot with SNS210 sensor	RC530B
97162200	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	Upgradable sensor slot with SNS210 sensor	RC530B
97321300	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	Upgradable sensor slot with SNS210 sensor	RC530B
97324400	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	Upgradable sensor slot with SNS210 sensor	RC530B
97325100	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	Upgradable sensor slot with SNS210 sensor	RC530B
97326800	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	Upgradable sensor slot with SNS210 sensor	RC534B
97327500	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	Upgradable sensor slot with SNS210 sensor	RC530B
97156100	RC530B LED40S/940 POE W8L120 VPC U0	Upgradable sensor slot empty with cover	RC530B

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
97161500	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	- degree(s)	4000 K	144 lm/W	4,300 lm
97185100	RC532B LED25S/940 PSD W8L113 VPC PI5	- degree(s)	4000 K	139 lm/W	2,500 lm
97173800	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	- degree(s)	3000 K	104 lm/W	1,900 lm
97146200	RC530B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	127 lm/W	1,500 lm
97150900	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	- degree(s)	3000 K	133 lm/W	3,400 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
97182000	RC532B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	139 lm/W	1,900 lm
97149300	RC530B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	148 lm/W	3,100 lm
97193600	RC533B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	127 lm/W	1,500 lm
97159200	RC530B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	144 lm/W	4,300 lm
97172100	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	106 lm/W	1,500 lm
97170700	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	- degree(s)	3000 K	99 lm/W	1,500 lm

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
97166000	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	- degree(s)	4000 K	142 lm/W	5,000 lm
97147900	RC530B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	139 lm/W	1,900 lm
97153000	RC530B LED34S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	145 lm/W	3,400 lm
97169100	RC531B LED15S/930 PSD W8L113 PCV PI5	- degree(s)	3000 K	99 lm/W	1,500 lm
97171400	RC531B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	106 lm/W	1,500 lm
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	127 lm/W	1,500 lm
97184400	RC532B LED25S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	139 lm/W	2,500 lm
97178300	RC531B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	3,100 lm
97197400	RC533B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	3,100 lm
97165300	RC530B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	142 lm/W	5,000 lm
97174500	RC531B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	1,900 lm
97194300	RC533B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	1,900 lm
97158500	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	140 lm/W	4,000 lm
97154700	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	145 lm/W	3,400 lm
97320600	RC530B LED34S/TW9 DIA W8L113 PCV PI5	120 degree(s)	Tunable white 2700-6500 K	124 lm/W	3,400 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
97322000	RC530B LED40S/TW9 DIA W8L113 PCV PI5	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,000 lm
97323700	RC530B LED50S/TW9 DIA W8L145 PCV PI5	120 degree(s)	Tunable white 2700-6500 K	120 lm/W	5,000 lm
97328200	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	120 degree(s)	4000 K	145 lm/W	3,400 lm
97329900	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	120 degree(s)	4000 K	145 lm/W	3,400 lm
97186800	RC532B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	148 lm/W	3,100 lm
97188200	RC532B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	144 lm/W	4,300 lm
97180600	RC531B LED31S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	110 lm/W	3,100 lm
97177600	RC531B LED19S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	110 lm/W	1,900 lm
97168400	RC530B LED50S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	142 lm/W	5,000 lm
97164600	RC530B LED43S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	144 lm/W	4,300 lm
97160800	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	- degree(s)	4000 K	144 lm/W	4,300 lm
97163900	RC530B LED43S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	144 lm/W	4,300 lm
97167700	RC530B LED50S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	142 lm/W	5,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
97176900	RC531B LED19S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	110 lm/W	1,900 lm
97179000	RC531B LED31S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	110 lm/W	3,100 lm
97175200	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	- degree(s)	4000 K	110 lm/W	1,900 lm
97199800	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	130 lm/W	4,000 lm
97201800	RC534B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	132 lm/W	5,000 lm
97200100	RC534B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	138 lm/W	4,300 lm
97203200	RC535B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	132 lm/W	5,000 lm
97202500	RC535B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	138 lm/W	4,300 lm
97157800	RC530B LED40S/940 POE W8L120 VPC U3	- degree(s)	4000 K	143 lm/W	4,000 lm
97190500	RC532B LED43S/940 SRD W8L145 PCV U4 W	- degree(s)	4000 K	143 lm/W	4,300 lm
97155400	RC530B LED34S/940 SRD	- degree(s)	4000 K	142 lm/W	3,400 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W8L120 VPC U4PI3SC				
97151600	RC530B LED34S/930 SRD W8L120 VPC U4 W	- degree(s)	3000 K	133 lm/W	3,400 lm
97152300	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	- degree(s)	3000 K	133 lm/W	3,400 lm
97148600	RC530B LED25S/930 SRD W8L120 VPC U4 W	- degree(s)	3000 K	133 lm/W	2,500 lm
97162200	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	- degree(s)	4000 K	143 lm/W	4,300 lm
97321300	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
97324400	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	120 degree(s)	Tunable white 2700-6500 K	124 lm/W	3,400 lm
97325100	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
97326800	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	120 degree(s)	Tunable white 2700-6500 K	93 lm/W	2,500 lm
97327500	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
97156100	RC530B LED40S/940 POE W8L120 VPC U0	- degree(s)	4000 K	143 lm/W	4,000 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
97161500	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	Wide beam
97185100	RC532B LED25S/940 PSD W8L113 VPC PI5	Wide beam
97173800	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	Wide beam
97146200	RC530B LED15S/940 PSD W8L113 PCV PI5	Wide beam
97150900	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	Wide beam
97182000	RC532B LED19S/940 PSD W8L141 PCV PI5	Wide beam

Order Code	Full Product Name	Optic type
97149300	RC530B LED31S/940 PSD W8L141 PCV PI5	Wide beam
97193600	RC533B LED15S/940 PSD W8L113 PCV PI5	Wide beam
97159200	RC530B LED43S/940 PSD W8L141 PCV PI5	Wide beam
97172100	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	Wide beam
97170700	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	Wide beam
97166000	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	Wide beam

Order Code	Full Product Name	Optic type
97147900	RC530B LED19S/940 PSD W8L141 PCV PI5	Wide beam
97153000	RC530B LED34S/940 PSD W8L113 PCV PI5	Wide beam
97169100	RC531B LED15S/930 PSD W8L113 PCV PI5	Wide beam
97171400	RC531B LED15S/940 PSD W8L113 PCV PI5	Wide beam
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	Wide beam
97184400	RC532B LED25S/940 PSD W8L113 PCV PI5	Wide beam
97178300	RC531B LED31S/940 PSD W8L141 PCV PI5	Wide beam
97197400	RC533B LED31S/940 PSD W8L141 PCV PI5	Wide beam
97165300	RC530B LED50S/940 PSD W8L141 PCV PI5	Wide beam
97174500	RC531B LED19S/940 PSD W8L141 PCV PI5	Wide beam
97194300	RC533B LED19S/940 PSD W8L141 PCV PI5	Wide beam
97158500	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	Wide beam
97154700	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	Wide beam
97320600	RC530B LED34S/TW9 DIA W8L113 PCV PI5	Wide beam
97322000	RC530B LED40S/TW9 DIA W8L113 PCV PI5	Wide beam
97323700	RC530B LED50S/TW9 DIA W8L145 PCV PI5	Wide beam
97328200	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	Wide beam
97329900	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	Wide beam
97186800	RC532B LED31S/940 PSD W8L141 PCV PI5	Wide beam
97188200	RC532B LED43S/940 PSD W8L141 PCV PI5	Wide beam
97180600	RC531B LED31S/940 W8L150 VPC ELP3 PI6	Wide beam
97177600	RC531B LED19S/940 W8L150 VPC ELP3 PI6	Wide beam
97168400	RC530B LED50S/940 W8L150 VPC ELP3 PI6	Wide beam
97164600	RC530B LED43S/940 W8L150 VPC ELP3 PI6	Wide beam

Order Code	Full Product Name	Optic type
97160800	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	Wide beam
97163900	RC530B LED43S/940 W8L145 PCV ELP3 PI6	Wide beam
97167700	RC530B LED50S/940 W8L145 PCV ELP3 PI6	Wide beam
97176900	RC531B LED19S/940 W8L145 PCV ELP3 PI6	Wide beam
97179000	RC531B LED31S/940 W8L145 PCV ELP3 PI6	Wide beam
97175200	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	Wide beam
97199800	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	Asymmetrical mirror
97201800	RC534B LED50S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
97200100	RC534B LED43S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
97203200	RC535B LED50S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
97202500	RC535B LED43S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
97157800	RC530B LED40S/940 POE W8L120 VPC U3	Wide beam
97190500	RC532B LED43S/940 SRD W8L145 PCV U4 W	Wide beam
97155400	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	Wide beam
97151600	RC530B LED34S/930 SRD W8L120 VPC U4 W	Wide beam
97152300	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	Wide beam
97148600	RC530B LED25S/930 SRD W8L120 VPC U4 W	Wide beam
97162200	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	Wide beam
97321300	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	Wide beam
97324400	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	Wide beam
97325100	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	Wide beam
97326800	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	Wide beam
97327500	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	Wide beam
97156100	RC530B LED40S/940 POE W8L120 VPC U0	Wide beam

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption
97161500	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	220 to 240 V	30.5 W
97185100	RC532B LED25S/940 PSD W8L113 VPC PI5	220 to 240 V	18 W
97173800	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	220 to 240 V	17.8 W
97146200	RC530B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	12.2 W
97150900	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	220 to 240 V	24.5 W
97182000	RC532B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	14 W
97149300	RC530B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	21 W
97193600	RC533B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	14.6 W
97159200	RC530B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	30.5 W
97172100	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	14.6 W
97170700	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	220 to 240 V	14.6 W
97166000	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	220 to 240 V	36 W

Order Code	Full Product Name	Input Voltage	Power Consumption
97147900	RC530B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	14 W
97153000	RC530B LED34S/940 PSD W8L113 PCV PI5	220 to 240 V	24.5 W
97169100	RC531B LED15S/930 PSD W8L113 PCV PI5	220 to 240 V	14.6 W
97171400	RC531B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	14.6 W
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	12.2 W
97184400	RC532B LED25S/940 PSD W8L113 PCV PI5	220 to 240 V	18 W
97178300	RC531B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	29 W
97197400	RC533B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	29 W
97165300	RC530B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V	36 W
97174500	RC531B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	17.8 W
97194300	RC533B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	17.8 W
97158500	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	29 W

Order Code	Full Product Name	Input Voltage	Power Consumption
97154700	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	24.5 W
97320600	RC530B LED34S/TW9 DIA W8L113 PCV PI5	220 to 240 V	27.5 W
97322000	RC530B LED40S/TW9 DIA W8L113 PCV PI5	220 to 240 V	33 W
97323700	RC530B LED50S/TW9 DIA W8L145 PCV PI5	220 to 240 V	41.5 W
97328200	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	220 to 240 V	24.5 W
97329900	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	220 to 240 V	24.5 W
97186800	RC532B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	21 W
97188200	RC532B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	30.5 W
97180600	RC531B LED31S/940 W8L150 VPC ELP3 PI6	220 to 240 V	29 W
97177600	RC531B LED19S/940 W8L150 VPC ELP3 PI6	220 to 240 V	17.8 W
97168400	RC530B LED50S/940 W8L150 VPC ELP3 PI6	220 to 240 V	36 W
97164600	RC530B LED43S/940 W8L150 VPC ELP3 PI6	220 to 240 V	30.5 W
97160800	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	220 to 240 V	30.5 W
97163900	RC530B LED43S/940 W8L145 PCV ELP3 PI6	220 to 240 V	30.5 W
97167700	RC530B LED50S/940 W8L145 PCV ELP3 PI6	220 to 240 V	36 W
97176900	RC531B LED19S/940 W8L145 PCV ELP3 PI6	220 to 240 V	17.8 W
97179000	RC531B LED31S/940 W8L145 PCV ELP3 PI6	220 to 240 V	29 W
97175200	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	220 to 240 V	17.8 W

Order Code	Full Product Name	Input Voltage	Power Consumption
97199800	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	31.5 W
97201800	RC534B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V	38 W
97200100	RC534B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	32 W
97203200	RC535B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V	38 W
97202500	RC535B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	32 W
97157800	RC530B LED40S/940 POE W8L120 VPC U3	51 to 54 V	28 W
97190500	RC532B LED43S/940 SRD W8L145 PCV U4 W	220 to 240 V	30 W
97155400	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	220 to 240 V	24 W
97151600	RC530B LED34S/930 SRD W8L120 VPC U4 W	220 to 240 V	25.5 W
97152300	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	220 to 240 V	25.5 W
97148600	RC530B LED25S/930 SRD W8L120 VPC U4 W	220 to 240 V	18.8 W
97162200	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	220 to 240 V	30 W
97321300	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	220 to 240 V	35.5 W
97324400	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	220 to 240 V	27.5 W
97325100	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	220 to 240 V	35.5 W
97326800	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	220 to 240 V	27 W
97327500	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	220 to 240 V	35.5 W
97156100	RC530B LED40S/940 POE W8L120 VPC U0	51 to 54 V	28 W

Approval and Application

Order Code	Full Product Name	Protection class IEC
97161500	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	Safety class I
97185100	RC532B LED25S/940 PSD W8L113 VPC PI5	Safety class I
97173800	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	Safety class I
97146200	RC530B LED15S/940 PSD W8L113 PCV PI5	Safety class I
97150900	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	Safety class I
97182000	RC532B LED19S/940 PSD W8L141 PCV PI5	Safety class I
97149300	RC530B LED31S/940 PSD W8L141 PCV PI5	Safety class I
97193600	RC533B LED15S/940 PSD W8L113 PCV PI5	Safety class I
97159200	RC530B LED43S/940 PSD W8L141 PCV PI5	Safety class I
97172100	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	Safety class I
97170700	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	Safety class I
97166000	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	Safety class I

Order Code	Full Product Name	Protection class IEC
97147900	RC530B LED19S/940 PSD W8L141 PCV PI5	Safety class I
97153000	RC530B LED34S/940 PSD W8L113 PCV PI5	Safety class I
97169100	RC531B LED15S/930 PSD W8L113 PCV PI5	Safety class I
97171400	RC531B LED15S/940 PSD W8L113 PCV PI5	Safety class I
97181300	RC532B LED15S/940 PSD W8L113 PCV PI5	Safety class I
97184400	RC532B LED25S/940 PSD W8L113 PCV PI5	Safety class I
97178300	RC531B LED31S/940 PSD W8L141 PCV PI5	Safety class I
97197400	RC533B LED31S/940 PSD W8L141 PCV PI5	Safety class I
97165300	RC530B LED50S/940 PSD W8L141 PCV PI5	Safety class I
97174500	RC531B LED19S/940 PSD W8L141 PCV PI5	Safety class I
97194300	RC533B LED19S/940 PSD W8L141 PCV PI5	Safety class I
97158500	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	Safety class I

Order Code	Full Product Name	Protection class IEC
97154700	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	Safety class I
97320600	RC530B LED34S/TW9 DIA W8L113 PCV PI5	Safety class I
97322000	RC530B LED40S/TW9 DIA W8L113 PCV PI5	Safety class I
97323700	RC530B LED50S/TW9 DIA W8L145 PCV PI5	Safety class I
97328200	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	Safety class I
97329900	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	Safety class I
97186800	RC532B LED31S/940 PSD W8L141 PCV PI5	Safety class I
97188200	RC532B LED43S/940 PSD W8L141 PCV PI5	Safety class I
97180600	RC531B LED31S/940 W8L150 VPC ELP3 PI6	Safety class I
97177600	RC531B LED19S/940 W8L150 VPC ELP3 PI6	Safety class I
97168400	RC530B LED50S/940 W8L150 VPC ELP3 PI6	Safety class I
97164600	RC530B LED43S/940 W8L150 VPC ELP3 PI6	Safety class I
97160800	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	Safety class I
97163900	RC530B LED43S/940 W8L145 PCV ELP3 PI6	Safety class I
97167700	RC530B LED50S/940 W8L145 PCV ELP3 PI6	Safety class I
97176900	RC531B LED19S/940 W8L145 PCV ELP3 PI6	Safety class I
97179000	RC531B LED31S/940 W8L145 PCV ELP3 PI6	Safety class I
97175200	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	Safety class I

Order Code	Full Product Name	Protection class IEC
97199800	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	Safety class I
97201800	RC534B LED50S/940 PSD W8L141 PCV PI5	Safety class I
97200100	RC534B LED43S/940 PSD W8L141 PCV PI5	Safety class I
97203200	RC535B LED50S/940 PSD W8L141 PCV PI5	Safety class I
97202500	RC535B LED43S/940 PSD W8L141 PCV PI5	Safety class I
97157800	RC530B LED40S/940 POE W8L120 VPC U3	Safety class III
97190500	RC532B LED43S/940 SRD W8L145 PCV U4 W	Safety class I
97155400	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	Safety class I
97151600	RC530B LED34S/930 SRD W8L120 VPC U4 W	Safety class I
97152300	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	Safety class I
97148600	RC530B LED25S/930 SRD W8L120 VPC U4 W	Safety class I
97162200	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	Safety class I
97321300	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	Safety class I
97324400	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	Safety class I
97325100	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	Safety class I
97326800	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	Safety class I
97327500	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	Safety class I
97156100	RC530B LED40S/940 POE W8L120 VPC U0	Safety class III

