



Philips TrueLine recessed: True line of light

TrueLine, recessed

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, recessed

Features

- Highly-uniform lighting with excellent glare control (UGR<19, L65<3000cd/m²)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI>90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine recessed-RC532B L1130




TrueLine Recessed-U3




TrueLine Recessed-U0

Dimensional drawing



TrueLine, recessed

Dimensional drawing



Product details

TrueLine_recessed-
RC530B_PCV_L1130-DP.tif



TrueLine-
RC530_RC531_RC534B_VPC-
DPP.tif



TrueLine, recessed

Product details



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-1DPP.tif



TrueLine-
RC530_RC531_RC532_RC533B_P
CV-2DPP.tif



TrueLine-
RC530_RC531_RC534B_VPC_PI5-
DPP.tif



TrueLine-
RC534B_SM534C_SP534P-DPP.tif



TrueLine_Recessed-U3



TrueLine_Recessed-U0

General Information

CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Color rendering index (CRI)	≥90
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Operating and Electrical

Line Frequency	50 to 60 Hz
----------------	-------------

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Application Conditions

Maximum dim level	1%
Suitable for random switching	No

General Information

Order Code	Full Product Name	Embedded control	Product family code
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	-	RC530B
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	-	RC532B
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	-	RC531B
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	-	RC530B
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	-	RC530B
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	-	RC532B
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	-	RC530B
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	-	RC533B
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	-	RC530B
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	-	RC531B
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	-	RC531B
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	-	RC530B
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	-	RC530B
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	-	RC530B
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	-	RC531B
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	-	RC531B
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	-	RC532B
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	-	RC532B
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	-	RC531B
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	-	RC533B
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	-	RC530B
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	-	RC531B
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	-	RC533B
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	-	RC530B
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	-	RC530B
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	-	RC530B
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	-	RC530B
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	-	RC530B
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	-	RC530B
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	-	RC530B
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	-	RC532B
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	-	RC532B
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	-	RC531B
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	-	RC531B
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	-	RC530B
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	-	RC530B
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	-	RC530B
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	-	RC530B
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	-	RC530B
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	-	RC531B
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	-	RC531B
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	-	RC531B
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	-	RC534B
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	-	RC534B
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	-	RC534B
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	-	RC535B
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	-	RC535B
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	Interact Ready light source with multi-sensor (upgradable)	RC530B

Order Code	Full Product Name	Embedded control	Product family code
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	Upgradable sensor slot with SNS210 sensor	RC532B
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	Upgradable sensor slot with SNS210 sensor	RC530B
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	Upgradable sensor slot with SNS210 sensor	RC530B
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	Upgradable sensor slot with SNS210 sensor	RC530B
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	Upgradable sensor slot with SNS210 sensor	RC530B
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	Upgradable sensor slot with SNS210 sensor	RC530B
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	Upgradable sensor slot with SNS210 sensor	RC530B
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	Upgradable sensor slot with SNS210 sensor	RC530B
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	Upgradable sensor slot with SNS210 sensor	RC530B
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	Upgradable sensor slot with SNS210 sensor	RC534B
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	Upgradable sensor slot with SNS210 sensor	RC530B
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	Upgradable sensor slot empty with cover	RC530B

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	- degree(s)	4000 K	144 lm/W	4,300 lm	910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	139 lm/W	1,900 lm
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	- degree(s)	4000 K	139 lm/W	2,500 lm	910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	148 lm/W	3,100 lm
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	- degree(s)	3000 K	104 lm/W	1,900 lm	910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	127 lm/W	1,500 lm
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	127 lm/W	1,500 lm	910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	- degree(s)	3000 K	133 lm/W	3,400 lm	910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	106 lm/W	1,500 lm

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	- degree(s)	3000 K	99 lm/W	1,500 lm
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	139 lm/W	1,900 lm
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	145 lm/W	3,400 lm
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	- degree(s)	3000 K	99 lm/W	1,500 lm
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	106 lm/W	1,500 lm
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	127 lm/W	1,500 lm
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	- degree(s)	4000 K	139 lm/W	2,500 lm
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	1,900 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	140 lm/W	4,000 lm
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	145 lm/W	3,400 lm
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	120 degree(s)	Tunable white 2700-6500 K	124 lm/W	3,400 lm
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,000 lm
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	120 degree(s)	Tunable white 2700-6500 K	120 lm/W	5,000 lm
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	120 degree(s)	4000 K	145 lm/W	3,400 lm
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	120 degree(s)	4000 K	145 lm/W	3,400 lm
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	148 lm/W	3,100 lm
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	110 lm/W	1,900 lm

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	- degree(s)	4000 K	130 lm/W	4,000 lm
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	132 lm/W	5,000 lm
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	138 lm/W	4,300 lm
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	132 lm/W	5,000 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	- degree(s)	4000 K	138 lm/W	4,300 lm
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	- degree(s)	4000 K	143 lm/W	4,000 lm
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	- degree(s)	4000 K	143 lm/W	4,300 lm
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	- degree(s)	4000 K	142 lm/W	3,400 lm
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	- degree(s)	3000 K	133 lm/W	3,400 lm
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	- degree(s)	3000 K	133 lm/W	3,400 lm
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	- degree(s)	3000 K	133 lm/W	2,500 lm
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	- degree(s)	4000 K	143 lm/W	4,300 lm
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	120 degree(s)	Tunable white 2700-6500 K	124 lm/W	3,400 lm
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	120 degree(s)	Tunable white 2700-6500 K	93 lm/W	2,500 lm

TrueLine, recessed

Order Code	Full Product Name	Beam	Correlated	Luminous	Luminous Flux
		angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm

Order Code	Full Product Name	Beam	Correlated	Luminous	Luminous Flux
		angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	- degree(s)	4000 K	143 lm/W	4,000 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	Wide beam
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	Wide beam
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	Wide beam
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	Wide beam
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	Wide beam
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	Wide beam
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	Wide beam
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	Wide beam
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	Wide beam
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	Wide beam
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	Wide beam
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	Wide beam
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	Wide beam
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	Wide beam
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	Wide beam
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	Wide beam
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Wide beam
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	Wide beam
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	Wide beam
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	Wide beam
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	Wide beam
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	Wide beam
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	Wide beam
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	Wide beam
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	Wide beam
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	Wide beam
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	Wide beam
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	Wide beam
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	Wide beam
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	Wide beam

Order Code	Full Product Name	Optic type
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	Wide beam
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	Wide beam
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	Wide beam
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	Wide beam
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	Wide beam
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	Wide beam
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	Wide beam
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	Wide beam
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	Wide beam
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	Wide beam
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	Wide beam
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	Wide beam
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	Asymmetrical mirror
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	Asymmetrical mirror
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	Wide beam
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	Wide beam
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	Wide beam
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	Wide beam
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	Wide beam
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	Wide beam
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	Wide beam
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	Wide beam
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	Wide beam
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	Wide beam
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	Wide beam
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	Wide beam
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	220 to 240 V	30.5 W
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	220 to 240 V	18 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	220 to 240 V	17.8 W
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	12.2 W

TrueLine, recessed

Order Code	Full Product Name	Input Voltage	Power	
			Consumption	
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	220 to 240 V	24.5 W	
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	14 W	
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	21 W	
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	14.6 W	
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	30.5 W	
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	14.6 W	
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	220 to 240 V	14.6 W	
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	220 to 240 V	36 W	
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	14 W	
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	220 to 240 V	24.5 W	
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	220 to 240 V	14.6 W	
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	14.6 W	
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	12.2 W	
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	220 to 240 V	18 W	
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	29 W	
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	29 W	
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V	36 W	
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	17.8 W	
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	220 to 240 V	17.8 W	
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	29 W	
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	24.5 W	
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	220 to 240 V	27.5 W	
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	220 to 240 V	33 W	
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	220 to 240 V	41.5 W	
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	220 to 240 V	24.5 W	

Order Code	Full Product Name	Input Voltage	Power	
			Consumption	
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	220 to 240 V	24.5 W	
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	220 to 240 V	21 W	
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	30.5 W	
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	220 to 240 V	29 W	
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	220 to 240 V	17.8 W	
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	220 to 240 V	36 W	
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	220 to 240 V	30.5 W	
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	220 to 240 V	30.5 W	
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	220 to 240 V	30.5 W	
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	220 to 240 V	36 W	
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	220 to 240 V	17.8 W	
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	220 to 240 V	29 W	
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	220 to 240 V	17.8 W	
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	220 to 240 V	31.5 W	
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V	38 W	
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	32 W	
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	220 to 240 V	38 W	
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	220 to 240 V	32 W	
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	51 to 54 V	28 W	
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	220 to 240 V	30 W	
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	220 to 240 V	24 W	
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	220 to 240 V	25.5 W	
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	220 to 240 V	25.5 W	
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	220 to 240 V	18.8 W	
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	220 to 240 V	30 W	

TrueLine, recessed

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	220 to 240 V	35.5 W
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	220 to 240 V	27.5 W
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	220 to 240 V	35.5 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	220 to 240 V	27 W
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	220 to 240 V	35.5 W
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	51 to 54 V	28 W

Approval and Application

Order Code	Full Product Name	Protection class IEC
910505103101	RC530B LED43S/940 PSD W8L150 VPC PI5 IP	Safety class I
910505103102	RC532B LED25S/940 PSD W8L113 VPC PI5	Safety class I
910505103103	RC531B LED19S/930 PSD W8L150 VPC PI5 IP	Safety class I
910505103104	RC530B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103105	RC530B LED34S/930 PSD W8L120 VPC PI5 IP	Safety class I
910505103106	RC532B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103107	RC530B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103109	RC533B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103110	RC530B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103111	RC531B LED15S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103112	RC531B LED15S/930 PSD W8L120 VPC PI5 IP	Safety class I
910505103113	RC530B LED50S/940 PSD W8L150 VPC PI5 IP	Safety class I
910505103114	RC530B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103115	RC530B LED34S/940 PSD W8L113 PCV PI5	Safety class I
910505103116	RC531B LED15S/930 PSD W8L113 PCV PI5	Safety class I
910505103117	RC531B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Safety class I
910505103119	RC532B LED25S/940 PSD W8L113 PCV PI5	Safety class I
910505103121	RC531B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103126	RC533B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103127	RC530B LED50S/940 PSD W8L141 PCV PI5	Safety class I
910505103129	RC531B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103131	RC533B LED19S/940 PSD W8L141 PCV PI5	Safety class I
910505103149	RC530B LED40S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103150	RC530B LED34S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103284	RC530B LED34S/TW9 DIA W8L113 PCV PI5	Safety class I
910505103286	RC530B LED40S/TW9 DIA W8L113 PCV PI5	Safety class I
910505103287	RC530B LED50S/TW9 DIA W8L145 PCV PI5	Safety class I
910505103292	RC530B LED34S/940 PSD W8L113 PCV PI5 SC	Safety class I
910505103293	RC530B LED34S/940 PSD W8L120 VPCPI5 IPSC	Safety class I

Order Code	Full Product Name	Protection class IEC
910505103122	RC532B LED31S/940 PSD W8L141 PCV PI5	Safety class I
910505103124	RC532B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103138	RC531B LED31S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103140	RC531B LED19S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103141	RC530B LED50S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103144	RC530B LED43S/940 W8L150 VPC ELP3 PI6	Safety class I
910505103154	RC530B LED43S/940 PSD W8L150 VPC ELD3PI6	Safety class I
910505103135	RC530B LED43S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103136	RC530B LED50S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103139	RC531B LED19S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103145	RC531B LED31S/940 W8L145 PCV ELP3 PI6	Safety class I
910505103153	RC531B LED19S/940 PSD W8L145 PCV ELD3PI6	Safety class I
910505103120	RC534B LED40S/940 PSD W8L120 VPC PI5 IP	Safety class I
910505103123	RC534B LED50S/940 PSD W8L141 PCV PI5	Safety class I
910505103128	RC534B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103125	RC535B LED50S/940 PSD W8L141 PCV PI5	Safety class I
910505103130	RC535B LED43S/940 PSD W8L141 PCV PI5	Safety class I
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	Safety class III
910505103155	RC532B LED43S/940 SRD W8L145 PCV U4 W	Safety class I
910505103156	RC530B LED34S/940 SRD W8L120 VPC U4PI3SC	Safety class I
910505103157	RC530B LED34S/930 SRD W8L120 VPC U4 W	Safety class I
910505103158	RC530B LED34S/930 SRD W8L120 VPC U4 W SC	Safety class I
910505103159	RC530B LED25S/930 SRD W8L120 VPC U4 W	Safety class I
910505103160	RC530B LED43S/940 SRD W8L145 PCV U4 PI3	Safety class I
910505103285	RC530B LED43S/TW9 SIA W8L145 PCV U4 PI3	Safety class I
910505103288	RC530B LED34S/TW9 SIA W8L120 VPC U4 PI3	Safety class I
910505103289	RC530B LED43S/TW9 SIA W8L145VPC U4 PI3SC	Safety class I
910505103290	RC531B LED25S/TW9 SIA W8L120 VPC U4 PI3	Safety class I
910505103291	RC530B LED43S/TW9 SIA W8L145PCV U4 PI3SC	Safety class I
910505103147	RC530B LED40S/940 POE W8L120 VPC U0	Safety class III

TrueLine, recessed



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com

2024, March 8 - data subject to change