



# TrueLine, suspended - True line of light: elegant, energy- efficient and compliant with office lighting norms

## TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. TrueLine, suspended is able to meet both sets of requirements. TrueLine is also available in recessed and surface-mounted versions.

### Benefits

- The most uniform exit window
- Extremely high efficacy for a line luminaire
- Luminaire housing dimensions most favored by architects

# TrueLine, suspended

## Features

- Luminous efficacy > 100 lm/W
- Complies with office lighting norms
- Stand-alone and continuous lines
- Recessed version also available
- Direct and indirect light
- Homogeneous exit window
- Future-proof: PoE

## Application

- General lighting for mid- and high-end office buildings

## Specifications

<b>Type</b>	SP530P (office compliant direct-light version)
	SP531P (non-office compliant direct-light version)
	SP532P (office compliant direct/indirect-light version)
	SP533P (non-office compliant direct/indirect-light version)
<b>Light source</b>	Non-replaceable LED module

<b>Power</b>	Office compliant (OC), 1130 and 1170 mm, 4000 K versions:
	10 W (direct 1500 lm)
	17.5 W (direct 2500 lm)
	24 W (direct 3400 lm)
	29 W (direct 4000 lm)
	15.2 W (direct 1500 lm, indirect 660 lm, total 2160 lm)
	25.5 W (direct 2500 lm, indirect 1100 lm, total 3600 lm)
	35.5 W (direct 3400 lm, indirect 1550 lm, total 4950 lm)
	42.5 W (direct 4000 lm, indirect 1850 lm, total 5850 lm)
	Non-office compliant (NOC) 1130 and 1170 mm, 4000 K versions:
	14.6 W (direct 1500 lm)
	24.5 W (direct 2500 lm)
	21 W (direct 1500 lm, indirect 940 lm, total 2440 lm)
	36 W (direct 2500 lm, indirect 1600 lm, total 4100 lm)
	Office compliant (OC) 1410 and 1450 mm, 4000 K versions:
	12.4 W (direct 1900 lm)
	21.5 W (direct 3100 lm)
	32 W (direct 4300 lm)
	38.5 W (direct 5000 lm)
	19.2 W (direct 1900 lm, indirect 1000 lm, total 2900 lm)
	34 W (direct 3100 lm, indirect 1650 lm, total 4750 lm)
	50 W (direct 4300 lm, indirect 2300 lm, total 6600 lm)
	60 W (direct 5000 lm, indirect 2700 lm, total 7700 lm)
	Non-office compliant (OC) 1410 and 1450 mm, 4000 K versions:
	17.8 W (direct 1900 lm)
	32 W (direct 3100 lm)
	29 W (direct 1900 lm, indirect 1400 lm, total 3300 lm)
	51 W (direct 3100 lm, indirect 2300 lm, total 5400 lm)
	Office compliant (OC) 1130 and 1170 mm, 3000 K versions:
	10.6 W (direct 1500 lm)
	18.2W (direct 2500 lm)
	25.5 W (direct 3400 lm)
	30.5 W (direct 4000 lm)
	16 W (direct 1500, indirect 660, total 2160 lm)
	26.5 W (direct 2500, indirect 1100, total 3600 lm)
	37.5 W (direct 3400, indirect 1550, total 4950 lm)
	44.5 W (direct 4000, indirect 1850, total 5850 lm)

## TrueLine, suspended

	Non-office compliant (NOC) 1130 and 1170mm, 3000 K:
	15.6 W (direct 1500 lm)
	26 W (direct 2500 lm)
	22 W (direct 1500 lm, indirect 940 lm, total 2440 lm)
	38.5 W (direct 2500 lm, indirect 1600 lm, total 4100 lm)
	Office compliant (OC) 1410 and 1450 mm, 3000 K versions:
	13 W (direct 1900 lm)
	23 W (direct 3100 lm)
	34 W (direct 4300 lm)
	40.5 W (direct 5000 lm)
	20 W (direct 1900 lm, indirect 1000 lm, total 2900 lm)
	36 W (direct 3100 lm, indirect 1650 lm, total 4750 lm)
	53 W (direct 4300 lm, indirect 2300 lm, total 6600 lm)
	64 W (direct 5000 lm, indirect 2700 lm, total 7700 lm)
	Non-office compliant (OC) 1410 and 1450 mm, 3000 K versions:
	18.8 W (direct 1900 lm)
	34 W (direct 3100 lm)
	31 W (direct 1900 lm, indirect 1400 lm, total 3300 lm)
	55 W (direct 3100 lm, indirect 2300 lm, total 5400 lm)
<b>Beam angle</b>	80 ° (OC), 110 ° (NOC)
<b>Luminous flux</b>	1500 to 7700 lm (4000 K)
<b>Correlated Color</b>	3000 or 4000 K
<b>Temperature</b>	
<b>Color Rendering Index</b>	>80
<b>Median useful life</b>	70,000 hours
<b>L70B50</b>	
<b>Median useful life</b>	50,000 hours
<b>L80B50</b>	
<b>Median useful life</b>	25,000 hours
<b>L90B50</b>	
<b>Driver failure rate</b>	1% per 5000 hours

<b>Average ambient temperature</b>	+25 °C
<b>Operating temperature range</b>	+10 to +40 °C
<b>Driver</b>	Built-in
<b>Power/Data supply</b>	PDS-60 24 V; supply for indoor and outdoor applications
<b>Mains voltage</b>	220-240 V / 50-60 Hz
<b>Dimming</b>	Compatible with many commercial available ELV dimmers
<b>Controls system input</b>	0-16 V, DALI
<b>Options</b>	Central battery
<b>Material</b>	Housing: anodized aluminum Driver box: steel Cover: PMMA or polycarbonate
<b>Color</b>	Aluminum (ALU)
<b>Optical cover</b>	Office compliant: PMMA, semi-transparent Non-office compliant: polycarbonate, opal
<b>Connection</b>	Push-in connector (PI) or with pull relief (PIP)
<b>Maintenance</b>	Optical module replaceable, no internal cleaning required
<b>Installation</b>	Fixation by means of brackets Individual or in line; suspended mounting with three different options: SM2 (one 2-wire bag, one Reutlinger for ceiling side, one ceiling cap) SW2 (one 2-wire bag, one (for LF1) or two (for BV/LE1) Reutlingers, one tool to fix the alignment profile (for LF1)) SMTT (one 2-wire bag, one (for LF1) or two (for BV/LE1) T-bar ceiling clips, one (for LF1) or two (for BV/LE1) Reutlingers, one tool to fix the alignment profile (for LF1)) Through-wiring possible
<b>Remarks</b>	Suspension set to be delivered with the luminaire

## Versions



**Truline suspended SP530B luminaire, office-compliant version with direct lighting, 1.2 m**



**Truline suspended SP531B luminaire, non-office compliant version with direct lighting, 1.2 m**

# TrueLine, suspended

## Versions



Trueline suspended SP530B luminaire, office-compliant version with direct lighting and ActiLume, 1.2 m



Trueline suspended SP532B luminaire, line end, office-compliant version with direct/indirect lighting, 1.2 m



TrueLine DIRECT/INDIRECT NOC - LED Module, system flux 2400 lm - 1170 mm



TrueLine Suspended DIRECT Asym

## Product details

Office-compliant luminaire, view from below



Suspended stand-alone luminaire, office-compliant; suspended light-line, office-compliant, with ACL sensor; suspended stand-alone luminaire, non-office-compliant, with blind plate.

TrueLine\_suspended-SP530P\_SP531P\_SP532P\_SP533P\_SM2\_ALU-DP17



TrueLine\_suspended-SP530P\_SP532P\_L1130\_ALU-DP02

# TrueLine, suspended

## Product details



TrueLine\_suspended-  
SP531P\_SP533P\_L1130\_ALU-DP01



TrueLine\_suspended-  
SP530P\_SP532P\_ACL\_L1170\_ALU  
-DP03



TrueLine, suspended SP530P  
SP532P LE1 LF1 ALU Detail photo  
11



TrueLine, suspended SP530P  
SP532P LE1 LF1 ALU Detail photo



TrueLine, suspended SP530P  
SP531P SP532P SP533P LF1 SMTT  
Detail photo



TrueLine, suspended SP530P  
SP531P SP532P SP533P LF1 SW2  
Detail photo



TrueLine-SP534\_SM534P-DPP.tif



TrueLine-  
RC534B\_SM534C\_SP534P-DPP.tif

## Application Conditions

Ambient temperature range	+10 to +40 °C
Maximum dim level	1%

## Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP40

## Controls and Dimming

Dimmable	Yes
----------	-----

## General Information

Cap-Base	-
CE mark	CE mark
Optical cover/lens type	Polymethyl methacrylate bowl/cover
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 5 s
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	1 pc
Optic type	-
UL mark	-

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## Application Conditions

Order Code	Full Product Name	Suitable for random switching
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	No
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	No
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	No
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	No
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	No
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	No
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	No
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	No
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	No
910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	No
910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	No
910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	No
910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	No
910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	No
910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	No
910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	No
910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	No
910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	No
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	No
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	No
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	No
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	No
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	No
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	No
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	No
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	No
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	No
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	No
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	No
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	No
910504105503	SP532P LED77S/840 PSD PI5 SM2 L1410 9003	No
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	No
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	No
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	No
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	No
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	No
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	No
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	No
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	No
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	No
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	No
910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	No
910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	No
910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	No
910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	No
910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	No
910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	No
910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	No
910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	No
910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	No
910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	No

Order Code	Full Product Name	Suitable for random switching
910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	No
910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	No
910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	No
910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	No
910504101103	SP533P LED33S/830 PSD PI5 SM2 L1410 ALU	No
910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	No
910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	No
910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	No
910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	No
910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	No
910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	No
910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	No
910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	No
910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	No
910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	No
910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	No
910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	No
910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	No
910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	No
910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	No
910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	Yes
910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	Yes
910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	Yes
910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	Yes
910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	Yes
910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	Yes
910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	Yes
910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	Yes
910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	Yes
910504105803	SP532P LED47S/840 PSD ACL SM2 L1450 ALU	Yes
910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	Yes
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	Yes
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	Yes
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	No
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	No
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	No
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	No
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	No
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	No
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	No
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	No
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	No
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	No
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	No
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	No
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	No
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	No
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	No
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	No
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	No
910504103703	SP533P LED24S/840 PSD ACL PI5 SM2 L1170	Yes
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	Yes

Order Code	Full Product Name	Suitable for random switching
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	No
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	No
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	No
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	No
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	No
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	No
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	No

**Operating and Electrical**

Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	220-240 V	910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	220-240 V
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	220-240 V	910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	220-240 V
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	220-240 V	910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	220-240 V
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	220-240 V	910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	220-240 V
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	220-240 V	910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	220-240 V
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	220 to 240 V	910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	220-240 V
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	220 to 240 V	910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	220-240 V
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	220 to 240 V	910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	220-240 V
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	220 to 240 V	910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	220-240 V
910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	220 to 240 V	910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	220-240 V
910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	51 to 54 V	910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	220-240 V
910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	51 to 54 V	910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	220-240 V
910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	51 to 54 V	910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	220 to 240 V
910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	220-240 V	910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	220 to 240 V
910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	220-240 V	910504101103	SP533P LED33S/830 PSD PI5 SM2 L1410 ALU	220 to 240 V
910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	220-240 V	910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	51 to 54 V
910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	220-240 V	910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	51 to 54 V
910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	220-240 V	910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	51 to 54 V
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	220-240 V	910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	220-240 V
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	220-240 V	910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	220-240 V
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	220-240 V	910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	220-240 V
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	220-240 V	910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	220-240 V
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	220-240 V	910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	220-240 V
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	220-240 V	910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	220-240 V
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	220-240 V	910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	220-240 V
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	220-240 V	910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	220-240 V
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	220-240 V	910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	220-240 V
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	220-240 V	910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	220-240 V
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	220-240 V	910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	220-240 V
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	220-240 V	910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	220-240 V
910504105503	SP532P LED77S/840 PSD PI5 SM2 L1410 9003	220 to 240 V	910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	220-240 V
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	220-240 V	910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	220-240 V
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	220-240 V	910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	220 to 240 V
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	220-240 V	910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	220 to 240 V
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	220-240 V	910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	51 to 54 V
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	220-240 V	910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	220-240 V
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	220-240 V	910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	220-240 V
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	220-240 V	910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	220-240 V
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	220-240 V	910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	220-240 V
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	220-240 V	910504105803	SP532P LED47S/840 PSD ACL SM2 L1450 ALU	220-240 V
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	220-240 V	910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	220-240 V



## TrueLine, suspended

Order Code	Full Product Name	Input Voltage
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	220-240 V
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	220-240 V
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	220-240 V
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	220-240 V
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	220-240 V
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	220 to 240 V
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	220 to 240 V
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	220 to 240 V
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	220-240 V
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	220-240 V
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	220-240 V
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	220-240 V
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	220 to 240 V
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	220 to 240 V

Order Code	Full Product Name	Input Voltage
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	220 to 240 V
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	220 to 240 V
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	220-240 V
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	220-240 V
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	220-240 V
910504103703	SP533P LED24S/840 PSD ACL PI5 SM2 L1170	220-240 V
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	220-240 V
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	220-240 V
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	220-240 V
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	220-240 V
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	220-240 V
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	220 to 240 V
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	220 to 240 V
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	220-240 V

### General Information (1/2)

Order Code	Full Product Name	Beam angle of light	Protection class	ENEC	Gear
		source	IEC	mark	
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	- °	Safety class I	ENEC plus mark	GRT
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	- °	Safety class I	ENEC plus mark	GRT
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	GRT
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	-
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	GRT
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	- °	Safety class I	ENEC plus mark	GRT
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	- °	Safety class I	ENEC plus mark	GRT
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	-	Safety class III	ENEC plus mark	GRT
910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	-	Safety class III	ENEC plus mark	GRT
910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	- °	Safety class III	ENEC plus mark	GRT
910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	GRT
910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	GRT

Order Code	Full Product Name	Beam angle of light	Protection class	ENEC	Gear
		source	IEC	mark	
910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	GRT
910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	GRT
910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	-	Safety class I	ENEC plus mark	GRT
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	-	Safety class I	ENEC plus mark	GRT
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	-	Safety class I	ENEC plus mark	GRT
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	-	Safety class I	ENEC plus mark	GRT
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	-	Safety class I	ENEC plus mark	GRT
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	-	Safety class I	ENEC plus mark	GRT
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	-	Safety class I	ENEC plus mark	GRT

## TrueLine, suspended

Order Code	Full Product Name	Beam angle of light		Protection class IEC	ENEC mark	Gear
		source				
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	GRT
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	-
910504105503	SP532P LED77S/840 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	GRT
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	GRT
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	120 °		Safety class I	ENEC mark	GRT
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	120 °		Safety class I	ENEC mark	GRT
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	120 °		Safety class I	ENEC mark	GRT
910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	120 °		Safety class I	ENEC mark	GRT
910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	120 °		Safety class I	ENEC mark	GRT
910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT
910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	120 °		Safety class I	ENEC mark	GRT
910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT
910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	120 °		Safety class I	ENEC mark	GRT
910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	120 °		Safety class I	ENEC mark	GRT
910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	120 °		Safety class I	ENEC mark	GRT
910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	120 °		Safety class I	ENEC mark	GRT

Order Code	Full Product Name	Beam angle of light		Protection class IEC	ENEC mark	Gear
		source				
910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	-		Safety class I	ENEC plus mark	GRT
910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	-		Safety class I	ENEC plus mark	GRT
910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	-		Safety class I	ENEC plus mark	GRT
910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	-		Safety class I	ENEC plus mark	GRT
910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	-		Safety class I	ENEC plus mark	-
910504101103	SP533P LED33S/830 PSD PI5 SM2 L1410 ALU	-		Safety class I	ENEC plus mark	GRT
910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	-		Safety class III	ENEC plus mark	GRT
910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	-		Safety class III	ENEC plus mark	GRT
910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	-		Safety class III	ENEC plus mark	GRT
910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	-		Safety class I	ENEC plus mark	GRT
910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	-		Safety class I	ENEC plus mark	GRT
910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	-		Safety class I	ENEC plus mark	GRT
910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	-		Safety class I	ENEC plus mark	GRT
910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	GRT
910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	GRT
910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	-
910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	-		Safety class I	ENEC plus mark	GRT
910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT
910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	120 °		Safety class I	ENEC mark	GRT
910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	120 °		Safety class I	ENEC mark	GRT
910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT
910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	- °		Safety class I	ENEC plus mark	GRT

## TrueLine, suspended

Order Code	Full Product Name	Beam angle of light		Protection class IEC	ENEC mark	Gear
		source				
910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	-		Safety class I	ENEC plus mark	GRT
910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	- °		Safety class I	ENEC plus mark	GRT
910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	-		Safety class I	ENEC plus mark	GRT
910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	-		Safety class III	ENEC plus mark	GRT
910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	-		Safety class I	ENEC plus mark	GRT
910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	-		Safety class I	ENEC plus mark	GRT
910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	-		Safety class I	ENEC plus mark	GRT
910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	-		Safety class I	ENEC plus mark	GRT
910504105803	SP532P LED47S/840 PSD ACL SM2 L1450 ALU	-		Safety class I	ENEC plus mark	GRT
910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	-		Safety class I	ENEC plus mark	GRT
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	-		Safety class I	ENEC plus mark	GRT
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	-		Safety class I	ENEC plus mark	GRT
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	-		Safety class I	ENEC plus mark	GRT
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	-		Safety class I	ENEC plus mark	GRT
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	-		Safety class I	ENEC plus mark	GRT
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	-		Safety class I	ENEC plus mark	GRT

Order Code	Full Product Name	Beam angle of light		Protection class IEC	ENEC mark	Gear
		source				
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	-		Safety class I	ENEC plus mark	GRT
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	-		Safety class I	ENEC plus mark	-
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	-		Safety class I	ENEC plus mark	-
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	-		Safety class I	ENEC plus mark	-
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	-		Safety class I	ENEC plus mark	-
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	-
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	-
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	-
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	-
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	120 °		Safety class I	ENEC mark	GRT
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	120 °		Safety class I	ENEC mark	GRT
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	120 °		Safety class I	ENEC mark	GRT
910504103703	SP533P LED24S/840 PSD ACL PI5 SM2 L1170	-		Safety class I	ENEC plus mark	GRT
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	-		Safety class I	ENEC plus mark	GRT
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	-		Safety class I	ENEC plus mark	GRT
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	-		Safety class I	ENEC plus mark	-
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	-		Safety class I	ENEC plus mark	-
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	120 °		Safety class I	ENEC mark	GRT

### General Information (2/2)

# TrueLine, suspended

Order Code	Full Product Name	Lamp family		Product Family	Standard RAL		Type description
		code	Embedded control		Code	color	
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	LED34S	-	SP530P	-	-	Office compliant version
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	LED40S	-	SP530P	-	-	Office compliant version
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	LED49S	-	SP532P	-	-	Office compliant version
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	LED58S	-	SP532P	-	-	Office compliant version
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	LED49S	-	SP532P	-	-	Office compliant version
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	LED43S	-	SP530P	-	-	Office compliant version
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	LED50S	-	SP530P	-	-	Office compliant version
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	LED66S	-	SP532P	-	-	Office compliant version
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	LED66S	-	SP532P	-	-	Office compliant version
910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	LED77S	-	SP532P	-	-	Office compliant version
910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	LED25S	-	SP530P	-	-	Office compliant version
910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	LED21S	-	SP532P	-	-	Office compliant version
910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	LED34S	-	SP530P	-	-	Office compliant version
910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	LED21S	-	SP532P	-	-	Office compliant version
910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	LED21S	-	SP532P	-	-	Office compliant version
910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	LED36S	-	SP532P	-	-	Office compliant version
910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	LED36S	-	SP532P	-	-	Office compliant version
910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	LED58S	-	SP532P	-	-	Office compliant version
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	LED36S	-	SP532P	Signal white	-	Office compliant version
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	LED29S	-	SP532P	-	-	Office compliant version
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	LED29S	-	SP532P	-	-	Office compliant version
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	LED47S	-	SP532P	-	-	Office compliant version
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	LED47S	-	SP532P	-	-	Office compliant version
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	LED77S	-	SP532P	-	-	Office compliant version
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	LED29S	-	SP532P	Signal white	-	Office compliant version
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	LED29S	-	SP532P	Signal white	-	Office compliant version
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	LED47S	-	SP532P	Signal white	-	Office compliant version
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	LED47S	-	SP532P	Signal white	-	Office compliant version
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	LED66S	-	SP532P	Signal white	-	Office compliant version
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	LED66S	-	SP532P	Signal white	-	Office compliant version
910504105503	SP532P LED77S/840 PSD PI5 SM2 L1410 9003	LED77S	-	SP532P	Signal white	-	Office compliant version
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	LED77S	-	SP532P	Signal white	-	Office compliant version
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	LED29S	-	SP532P	-	-	Office compliant version
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	LED29S	-	SP532P	-	-	Office compliant version
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	LED47S	-	SP532P	-	-	Office compliant version
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	LED36S	-	SP532P	-	Yes	-
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	LED47S	-	SP532P	-	Yes	-
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	LED77S	-	SP532P	-	Yes	-
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	LED34S	-	SP530P	-	Yes	-
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	LED58S	-	SP532P	-	Yes	-
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	LED43S	-	SP530P	-	Yes	-
910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	LED77S	-	SP532P	-	Yes	-
910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	LED36S	-	SP532P	-	Yes	-
910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	LED15S	-	SP531P	-	Yes	-
910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	LED29S	-	SP532P	Signal white	Yes	-
910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	LED49S	-	SP532P	-	Yes	-
910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	LED36S	-	SP532P	-	Yes	-
910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	LED50S	-	SP530P	-	Yes	-
910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	LED40S	-	SP530P	-	Yes	-
910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	LED50S	-	SP530P	-	Yes	-
910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	LED15S	-	SP531P	-	-	Non office compliant version

Order Code	Full Product Name	Lamp family		Product Family	Standard RAL		Service tag	Type description
		code	Embedded control		Code	color		
910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	LED41S	-	SP533P	-	-	-	Non office compliant version
910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	LED24S	-	SP533P	-	-	-	Non office compliant version
910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	LED19S	-	SP531P	-	-	-	Non office compliant version
910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	LED54S	-	SP533P	-	-	-	Non office compliant version
910504101103	SP533P LED33S/830 PSD PI5 SM2 L1410 ALU	LED33S	-	SP533P	-	-	-	Non office compliant version
910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	LED15S	-	SP531P	-	-	-	Non office compliant version
910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	LED25S	-	SP531P	-	-	-	Non office compliant version
910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	LED24S	-	SP533P	-	-	-	Non office compliant version
910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	LED24S	-	SP533P	-	-	-	Non office compliant version
910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	LED41S	-	SP533P	-	-	-	Non office compliant version
910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	LED33S	-	SP533P	-	-	-	Non office compliant version
910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	LED54S	-	SP533P	-	-	-	Non office compliant version
910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	LED33S	-	SP533P	Signal white	-	-	Non office compliant version
910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	LED33S	-	SP533P	Signal white	-	-	Non office compliant version
910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	LED54S	-	SP533P	Signal white	-	-	Non office compliant version
910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	LED54S	-	SP533P	Signal white	-	-	Non office compliant version
910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	LED41S	-	SP533P	-	Yes	-	-
910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	LED33S	-	SP533P	-	Yes	-	-
910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	LED33S	-	SP533P	Signal white	Yes	-	-
910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	LED24S	-	SP533P	-	Yes	-	-
910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	LED40S	ActiLume	SP530P	-	-	-	Office compliant version
910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	LED58S	ActiLume	SP532P	-	-	-	Office compliant version
910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	LED50S	ActiLume	SP530P	-	-	-	Office compliant version
910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	LED77S	ActiLume	SP532P	-	-	-	Office compliant version
910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	LED36S	ActiLume	SP532P	-	-	-	Office compliant version
910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	LED21S	ActiLume	SP532P	-	-	-	Office compliant version
910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	LED36S	ActiLume	SP532P	-	-	-	Office compliant version
910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	LED49S	ActiLume	SP532P	-	-	-	Office compliant version
910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	LED29S	ActiLume	SP532P	-	-	-	Office compliant version
910504105803	SP532P LED47S/840 PSD ACL SM2 L1450 ALU	LED47S	ActiLume	SP532P	-	-	-	Office compliant version
910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	LED66S	ActiLume	SP532P	-	-	-	Office compliant version
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	LED33S	ActiLume	SP533P	-	-	-	Non office compliant version
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	LED54S	ActiLume	SP533P	-	-	-	Non office compliant version
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	LED36S	-	SP532P	-	-	-	Office compliant version
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	LED36S	-	SP532P	-	-	-	Office compliant version
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	LED36S	-	SP532P	-	-	-	Office compliant version
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	LED47S	-	SP532P	-	-	-	Office compliant version
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	LED47S	-	SP532P	-	-	-	Office compliant version
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	LED47S	-	SP532P	-	-	-	Office compliant version
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	LED34S	-	SP534P	-	-	-	Office compliant version
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	LED34S	-	SP534P	-	-	-	Office compliant version
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	LED40S	-	SP534P	-	-	-	Office compliant version
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	LED40S	-	SP534P	-	-	-	Office compliant version
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	LED43S	-	SP534P	-	-	-	Office compliant version
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	LED43S	-	SP534P	-	-	-	Office compliant version
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	LED50S	-	SP534P	-	-	-	Office compliant version
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	LED50S	-	SP534P	-	-	-	Office compliant version
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	LED43S	-	SP534P	-	Yes	-	-
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	LED43S	-	SP534P	-	Yes	-	-
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	LED34S	-	SP534P	-	Yes	-	-
910504103703	SP533P LED24S/840 PSD ACL PI5 SM2 L1170	LED24S	ActiLume	SP533P	-	-	-	Non office compliant version

Order Code	Full Product Name	Lamp family		Product Family	Standard RAL		Service tag	Type description
		code	Embedded control		Code	color		
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	LED41S	ActiLume	SP533P	-	-	-	Non office compliant version
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	LED33S	-	SP533P	-	-	-	Non office compliant version
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	LED54S	-	SP533P	-	-	-	Non office compliant version
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	LED33S	-	SP533P	-	-	-	Non office compliant version
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	LED54S	-	SP533P	-	-	-	Non office compliant version
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	LED40S	-	SP534P	-	-	-	Office compliant version
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	LED50S	-	SP534P	-	-	-	Office compliant version
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	LED40S	-	SP534P	-	-	Yes	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Init. Color	Initial LED	Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Init. Color	Initial LED
			Color Temperature	Rendering Index	luminaire efficacy				Color Temperature	Rendering Index	luminaire efficacy
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	142 lm/W	910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38)	4000 K	≥80	128 lm/W
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	138 lm/W	910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	147 lm/W
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	132 lm/W	910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	159 lm/W
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	138 lm/W	910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	142 lm/W
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	(0.43, 0.40)	3000 K	≥80	132 lm/W	910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	142 lm/W
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38)	4000 K	≥80	134 lm/W	910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	(0.43, 0.40)	3000 K	≥80	142 lm/W
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38)	4000 K	≥80	130 lm/W	910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38)	4000 K	≥80	141 lm/W
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38)	4000 K	≥80	132 lm/W	910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	(0.43, 0.40)	3000 K	≥80	136 lm/W
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	(0.43, 0.40)	3000 K	≥80	125 lm/W	910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	(0.43, 0.40)	3000 K	≥80	131 lm/W

## TrueLine, suspended

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	(0.38, 0.38) SDCM <3	4000 K	≥80	141 lm/W
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	151 lm/W
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	(0.43, 0.40) SDCM <3	3000 K	≥80	145 lm/W
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	140 lm/W
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	(0.43, 0.40) SDCM <3	3000 K	≥80	132 lm/W
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	(0.43, 0.40) SDCM <3	3000 K	≥80	120 lm/W
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	(0.38, 0.38) SDCM <3	4000 K	≥80	151 lm/W
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	(0.43, 0.40) SDCM <3	3000 K	≥80	145 lm/W
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	(0.38, 0.38) SDCM <3	4000 K	≥80	140 lm/W
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	(0.43, 0.40) SDCM <3	3000 K	≥80	132 lm/W
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	(0.38, 0.38) SDCM <3	4000 K	≥80	132 lm/W
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	(0.43, 0.40) SDCM <3	3000 K	≥80	125 lm/W
910504105503	SP532P LED77S/840	(0.38, 0.38) SDCM <3	4000 K	≥80	128 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PSD PI5 SM2 L1410 9003				
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	(0.43, 0.40) SDCM <3	3000 K	≥80	120 lm/W
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	151 lm/W
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	151 lm/W
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	140 lm/W
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	147 lm/W
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	148 lm/W
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	140 lm/W
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	148 lm/W
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	143 lm/W
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	152 lm/W
910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	3000 K	≥90	136 lm/W
910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	(0.38, 0.38) SDCM <3	4000 K	≥90	147 lm/W

## TrueLine, suspended

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	107 lm/W
910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	(0.38, 0.38) SDCM <3	4000 K	≥90	151 lm/W
910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	3000 K	≥90	113 lm/W
910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	(0.38, 0.38) SDCM <3	4000 K	≥90	147 lm/W
910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	148 lm/W
910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	(0.38, 0.38) SDCM <3	4000 K	≥90	145 lm/W
910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	(0.38, 0.38) SDCM <3	4000 K	≥90	148 lm/W
910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	103 lm/W
910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	114 lm/W
910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	(0.43, 0.40) SDCM <3	3000 K	≥80	109 lm/W
910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	107 lm/W
910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	106 lm/W
910504101103	SP533P LED33S/830 SDCM <3	(0.43, 0.40) SDCM <3	3000 K	≥80	106 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PSD PI5 SM2 L1410 ALU				
910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	109 lm/W
910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	100 lm/W
910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	122 lm/W
910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	116 lm/W
910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	(0.43, 0.40) SDCM <3	3000 K	≥80	106 lm/W
910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	114 lm/W
910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	(0.43, 0.40) SDCM <3	3000 K	≥80	98 lm/W
910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	(0.38, 0.38) SDCM <3	4000 K	≥80	114 lm/W
910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	(0.43, 0.40) SDCM <3	3000 K	≥80	106 lm/W
910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	(0.38, 0.38) SDCM <3	4000 K	≥80	106 lm/W
910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	(0.43, 0.40) SDCM <3	3000 K	≥80	98 lm/W
910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	126 lm/W



## TrueLine, suspended

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	3000 K	≥90	126 lm/W
910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	(0.38, 0.38) SDCM <3	3000 K	≥90	126 lm/W
910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	120 lm/W
910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	133 lm/W
910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	134 lm/W
910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	127 lm/W
910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	126 lm/W
910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	138 lm/W
910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	(0.38, 0.38) SDCM <3	4000 K	≥80	133 lm/W
910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	(0.38, 0.38) SDCM <3	4000 K	≥80	136 lm/W
910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	(0.38, 0.38) SDCM <3	4000 K	≥80	136 lm/W
910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	144 lm/W
910504105803	SP532P LED47S/840	(0.38, 0.38) SDCM <3	4000 K	≥80	136 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PSD ACL SM2 L1450 ALU				
910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	129 lm/W
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	(0.38, 0.38) SDCM <3	4000 K	≥80	110 lm/W
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	(0.38, 0.38) SDCM <3	4000 K	≥80	104 lm/W
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	(0.38, 0.38) SDCM <3	4000 K	≥80	141 lm/W
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	(0.38, 0.38) SDCM <3	4000 K	≥80	141 lm/W
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	(0.38, 0.38) SDCM <3	4000 K	≥80	141 lm/W
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	140 lm/W
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	140 lm/W
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	140 lm/W
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	(0.38, 0.38) SDCM <3	4000 K	≥80	121 lm/W
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	(0.38, 0.38) SDCM <3	4000 K	≥80	121 lm/W
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	(0.38, 0.38) SDCM <3	4000 K	≥80	116 lm/W

## TrueLine, suspended

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	(0.38, 0.38) SDCM <3	4000 K	≥80	116 lm/W
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	121 lm/W
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	121 lm/W
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	118 lm/W
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	118 lm/W
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥90	127 lm/W
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥90	127 lm/W
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	(0.38, 0.38) SDCM <3	4000 K	≥90	124 lm/W
910504103703	SP533P LED24S/840	(0.38, 0.38) SDCM <3	4000 K	≥80	111 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	PSD ACL PI5 SM2 L1170				
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	(0.38, 0.38) SDCM <3	4000 K	≥80	111 lm/W
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	114 lm/W
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	106 lm/W
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	114 lm/W
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	(0.38, 0.38) SDCM <3	4000 K	≥80	106 lm/W
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	116 lm/W
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	(0.38, 0.38) SDCM <3	4000 K	≥80	118 lm/W
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	(0.38, 0.38) SDCM <3	4000 K	≥90	125 lm/W

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	3400 lm	24 W
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	4000 lm	29 W
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	4950 lm	35.5 W
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	5850 lm	42.5 W
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	4950 lm	37.5 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	4300 lm	32 W
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	5000 lm	38.5 W
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	6600 lm	50 W
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	6600 lm	53 W
910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	7700 lm	60 W

## TrueLine, suspended

Order Code	Full Product Name	Initial luminous flux	Initial input power
910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	2500 lm	17 W
910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	2160 lm	13.6 W
910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	3400 lm	24 W
910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	2160 lm	15.2 W
910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	2160 lm	15.2 W
910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	3600 lm	25.5 W
910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	3600 lm	26.5 W
910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	5850 lm	44.5 W
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	3600 lm	25.5 W
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	2900 lm	19.2 W
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	2900 lm	20 W
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	4750 lm	34 W
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	4750 lm	36 W
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	7700 lm	64 W
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	2900 lm	19.2 W
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	2900 lm	20 W
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	4750 lm	34 W
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	4750 lm	36 W
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	6600 lm	50 W
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	6600 lm	53 W
910504105503	SP532P LED77S/840 PSD PI5 SM2 L1410 9003	7700 lm	60 W
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	7700 lm	64 W
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	2900 lm	19.2 W
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	2900 lm	19.2 W
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	4750 lm	34 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	3600 lm	24.5 W
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	4700 lm	31.8 W
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	7700 lm	55 W
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	3400 lm	23 W
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	5800 lm	40.5 W
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	4300 lm	28.3 W
910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	7700 lm	56.7 W
910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	3600 lm	24.5 W
910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	1500 lm	14 W
910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	2900 lm	19.2 W
910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	4900 lm	43.5 W
910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	3600 lm	24.5 W
910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	5000 lm	33.9 W
910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	4000 lm	27.5 W
910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	5000 lm	33.9 W
910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	1500 lm	14.6 W
910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	4100 lm	36 W
910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	2440 lm	22 W
910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	1900 lm	17.8 W
910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	5400 lm	51 W
910504101103	SP533P LED33S/830 PSD PI5 SM2 L1410 ALU	3300 lm	31 W
910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	1500 lm	13.8 W
910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	2500 lm	25 W
910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	2440 lm	20 W
910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	2440 lm	21 W

## TrueLine, suspended

Order Code	Full Product Name	Initial luminous flux	Initial input power
910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	4100 lm	38.5 W
910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	3300 lm	29 W
910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	5400 lm	55 W
910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	3300 lm	29 W
910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	3300 lm	31 W
910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	5400 lm	51 W
910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	5400 lm	55 W
910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	4100 lm	32.5 W
910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	3300 lm	26 W
910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	3300 lm	26 W
910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	2400 lm	20 W
910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	4000 lm	30 W
910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	5850 lm	43.5 W
910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	5000 lm	39.5 W
910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	7700 lm	61 W
910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	3600 lm	26 W
910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	2160 lm	16.2 W
910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	3600 lm	26.5 W
910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	4950 lm	36.5 W
910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	2900 lm	20.2 W
910504105803	SP532P LED47S/840 PSD ACL SM2 L1450 ALU	4750 lm	35.5 W
910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	6600 lm	51 W
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	3300 lm	30 W
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	5400 lm	52 W
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	3600 lm	25.5 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	3600 lm	25.5 W
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	3600 lm	25.5 W
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	4750 lm	34 W
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	4750 lm	34 W
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	4750 lm	34 W
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	3400 lm	28 W
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	3400 lm	28 W
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	4000 lm	34.5 W
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	4000 lm	34.5 W
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	4300 lm	35.5 W
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	4300 lm	35.5 W
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	5000 lm	42.5 W
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	5000 lm	42.5 W
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	4300 lm	33.9 W
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	4300 lm	33.9 W
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	3400 lm	27.5 W
910504103703	SP533P LED24S/840 PSD ACL PI5 SM2 L1170	2440 lm	22 W
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	4100 lm	37 W
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	3300 lm	29 W
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	5400 lm	51 W
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	3300 lm	29 W
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	5400 lm	51 W
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	4000 lm	34.5 W
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	5000 lm	42.5 W
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	4000 lm	32 W

### Mechanical and Housing

## TrueLine, suspended

Order Code	Full Product Name	Color
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	Aluminum
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	Aluminum
910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	Aluminum
910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	Aluminum
910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	Aluminum
910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	Aluminum
910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	Aluminum
910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	Aluminum
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	White
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	Aluminum
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	Aluminum
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	Aluminum
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	White
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	White
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	Aluminum
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	White
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910504105503	SP532P LED77S/840 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	Aluminum
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	Aluminum
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	Aluminum
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	Aluminum
910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	Aluminum
910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	White RAL 9003
910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	White RAL 9003
910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	Aluminum
910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	Aluminum
910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	Aluminum

Order Code	Full Product Name	Color
910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	Aluminum
910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	Aluminum
910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	Aluminum
910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504101103	SP533P LED33S/830 PSD PI5 SM2 L1410 ALU	Aluminum
910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	Aluminum
910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	Aluminum
910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	Aluminum
910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	Aluminum
910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	Aluminum
910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	RAL standard (to be defined)
910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	Aluminum
910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	White RAL 9003
910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	Aluminum
910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	Aluminum
910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	Aluminum
910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	Aluminum
910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	Aluminum
910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	Aluminum
910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	Aluminum
910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	Aluminum
910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	Aluminum
910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	Aluminum
910504105803	SP532P LED47S/840 PSD ACL SM2 L1450 ALU	Aluminum
910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	Aluminum
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	Aluminum
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	Aluminum
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	Aluminum
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	Aluminum
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	Aluminum
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	Aluminum
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	Aluminum
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	Aluminum
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	Aluminum
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	Aluminum
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	Aluminum
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	Aluminum
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	Aluminum
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	Aluminum

## TrueLine, suspended

Order Code	Full Product Name	Color
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	Aluminum
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	Aluminum
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	Aluminum
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	Aluminum
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	Aluminum
910504103703	SP533P LED24S/840 PSD ACL PI5 SM2 L1170	Aluminum
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	Aluminum

Order Code	Full Product Name	Color
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	Aluminum
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	Aluminum
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	Aluminum
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	Aluminum
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	Aluminum
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	Aluminum
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	Aluminum

### Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median	Median
		useful life	useful life
		L80B50	L90B50
910504097203	SP530P LED34S/840 PSD PI5 SM2 L1130 ALU	-	-
910504097303	SP530P LED40S/840 PSD PI5 SM2 L1130 ALU	-	-
910504097403	SP532P LED49S/840 PSD PI5 SM2 L1130 ALU	-	-
910504097503	SP532P LED58S/840 PSD PI5 SM2 L1130 ALU	-	-
910504098203	SP532P LED49S/830 PSD PI5 SM2 L1130 ALU	-	-
910504099903	SP530P LED43S/840 PSD PI5 SM2 L1410 ALU	-	-
910504100003	SP530P LED50S/840 PSD PI5 SM2 L1410 ALU	-	-
910504100303	SP532P LED66S/840 PSD PI5 SM2 L1410 ALU	-	-
910504100403	SP532P LED66S/830 PSD PI5 SM2 L1410 ALU	-	-
910504100503	SP532P LED77S/840 PSD PI5 SM2 L1410 ALU	-	-
910504101403	SP530P LED25S/840 POE SW2 L1130 ALU	-	-
910504101503	SP532P LED21S/840 POE SW2 L1130 ALU	-	-
910504101603	SP530P LED34S/840 POE SW2 L1130 ALU	-	-
910504102503	SP532P LED21S/840 PSD PI5 SM2 L1130 ALU	-	-
910504102603	SP532P LED21S/830 PSD PI5 SM2 L1130 ALU	-	-
910504102703	SP532P LED36S/840 PSD PI5 SM2 L1130 ALU	-	-
910504102803	SP532P LED36S/830 PSD PI5 SM2 L1130 ALU	-	-
910504102903	SP532P LED58S/830 PSD PI5 SM2 L1130 ALU	-	-
910504104303	SP532P LED36S/840 PSD PI5 SM2 L1130 9003	-	-
910504104403	SP532P LED29S/840 PSD PI5 SM2 L1410 ALU	-	-

Order Code	Full Product Name	Median	Median
		useful life	useful life
		L80B50	L90B50
910504104503	SP532P LED29S/830 PSD PI5 SM2 L1410 ALU	-	-
910504104603	SP532P LED47S/840 PSD PI5 SM2 L1410 ALU	-	-
910504104703	SP532P LED47S/830 PSD PI5 SM2 L1410 ALU	-	-
910504104803	SP532P LED77S/830 PSD PI5 SM2 L1410 ALU	-	-
910504104903	SP532P LED29S/840 PSD PI5 SM2 L1410 9003	-	-
910504105003	SP532P LED29S/830 PSD PI5 SM2 L1410 9003	-	-
910504105103	SP532P LED47S/840 PSD PI5 SM2 L1410 9003	-	-
910504105203	SP532P LED47S/830 PSD PI5 SM2 L1410 9003	-	-
910504105303	SP532P LED66S/840 PSD PI5 SM2 L1410 9003	-	-
910504105403	SP532P LED66S/830 PSD PI5 SM2 L1410 9003	-	-
910504105503	SP532P LED77S/840 PSD PI5 SM2 L1410 9003	-	-
910504105603	SP532P LED77S/830 PSD PI5 SM2 L1410 9003	-	-
910504106003	SP532P LED29S/840 PSD LE1 PI5 SM2 L1410	-	-
910504106103	SP532P LED29S/840 PSD LF1 PI5 SM2 L1410	-	-
910504106203	SP532P LED47S/840 PSD LF1 PI5 SM2 L1410	-	-
910505100103	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	50000 h	25000 h
910505100111	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	50000 h	25000 h
910505100114	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	50000 h	25000 h
910505100120	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	50000 h	25000 h

## TrueLine, suspended

Order Code	Full Product Name	Median	Median
		useful life L80B50	useful life L90B50
910505100123	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	50000 h	25000 h
910505100124	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	50000 h	25000 h
910505100129	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	50000 h	25000 h
910505100136	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	50000 h	25000 h
910505100139	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	50000 h	25000 h
910505100140	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	50000 h	25000 h
910505100153	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	50000 h	25000 h
910505100161	SP532P LED36S/940 PSD LF1 PI7 SMTT L1130	50000 h	25000 h
910505100163	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	50000 h	25000 h
910505100169	SP530P LED40S/940 PSD ACL PI5 SM2 L1170	50000 h	25000 h
910505100173	SP530P LED50S/940 PSD ACL PI5 SM2 L1450	50000 h	25000 h
910504097603	SP531P LED15S/840 PSD PI5 SM2 L1130 ALU	-	-
910504097703	SP533P LED41S/840 PSD PI5 SM2 L1130 ALU	-	-
910504098303	SP533P LED24S/830 PSD PI5 SM2 L1130 ALU	-	-
910504100203	SP531P LED19S/840 PSD PI5 SM2 L1410 ALU	-	-
910504101003	SP533P LED54S/840 PSD PI5 SM2 L1410 ALU	-	-
910504101103	SP533P LED33S/830 PSD PI5 SM2 L1410 ALU	-	-
910504101803	SP531P LED15S/840 POE SW2 L1130 ALU	-	-
910504101903	SP531P LED25S/840 POE SW2 L1130 ALU	-	-
910504102003	SP533P LED24S/840 POE SW2 L1130 ALU	-	-
910504103503	SP533P LED24S/840 PSD PI5 SM2 L1130 ALU	-	-
910504103603	SP533P LED41S/830 PSD PI5 SM2 L1130 ALU	-	-
910504106303	SP533P LED33S/840 PSD PI5 SM2 L1410 ALU	-	-
910504106403	SP533P LED54S/830 PSD PI5 SM2 L1410 ALU	-	-
910504106503	SP533P LED33S/840 PSD PI5 SM2 L1410 9003	-	-
910504106603	SP533P LED33S/830 PSD PI5 SM2 L1410 9003	-	-

Order Code	Full Product Name	Median	Median
		useful life L80B50	useful life L90B50
910504106703	SP533P LED54S/840 PSD PI5 SM2 L1410 9003	-	-
910504106803	SP533P LED54S/830 PSD PI5 SM2 L1410 9003	-	-
910505100117	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	50000 h	25000 h
910505100119	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	50000 h	25000 h
910505100175	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	50000 h	25000 h
910505100183	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	50000 h	25000 h
910504097803	SP530P LED40S/840 PSD ACL SM2 L1170 ALU	-	-
910504097903	SP532P LED58S/840 PSD ACL SM2 L1170 ALU	-	-
910504100103	SP530P LED50S/840 PSD ACL SM2 L1450 ALU	-	-
910504100603	SP532P LED77S/840 PSD ACL SM2 L1450 ALU	-	-
910504101703	SP532P LED36S/840 POE ACL SW2 L1170 ALU	-	-
910504103003	SP532P LED21S/840 PSD ACL PI5 SM2 L1170	-	-
910504103103	SP532P LED36S/840 PSD ACL PI5 SM2 L1170	-	-
910504103203	SP532P LED49S/840 PSD ACL PI5 SM2 L1170	-	-
910504105703	SP532P LED29S/840 PSD ACL SM2 L1450 ALU	-	-
910504105803	SP532P LED47S/840 PSD ACL SM2 L1450 ALU	-	-
910504105903	SP532P LED66S/840 PSD ACL SM2 L1450 ALU	-	-
910504106903	SP533P LED33S/840 PSD ACL PI5 SM2 L1450	-	-
910504107003	SP533P LED54S/840 PSD ACL PI5 SM2 L1450	-	-
910504098003	SP532P LED36S/840 PSD LE1 PI7 SM2 L1130	-	-
910504098103	SP532P LED36S/840 PSD LF1 PI7 SMTT L1130	-	-
910504098403	SP532P LED36S/840 PSD LF1 PI7 SW2 L1130	-	-
910504100703	SP532P LED47S/840 PSD LE1 PI5 SM2 L1410	-	-
910504100803	SP532P LED47S/840 PSD LF1 PI5 SMTT L1410	-	-
910504100903	SP532P LED47S/840 PSD LF1 PI5 SW2 L1410	-	-

## TrueLine, suspended

Order Code	Full Product Name	Median	Median
		useful life L80B50	useful life L90B50
910504113003	SP534P LED34S/840 PSD LE1 PI5 SM2 L1130	-	-
910504113103	SP534P LED34S/840 PSD LF1 PI5 SM2 L1130	-	-
910504113203	SP534P LED40S/840 PSD LE1 PI5 SM2 L1130	-	-
910504113303	SP534P LED40S/840 PSD LF1 PI5 SM2 L1130	-	-
910504113403	SP534P LED43S/840 PSD LE1 PI5 SM2 L1410	-	-
910504113503	SP534P LED43S/840 PSD LF1 PI5 SM2 L1410	-	-
910504113603	SP534P LED50S/840 PSD LE1 PI5 SM2 L1410	-	-
910504113703	SP534P LED50S/840 PSD LF1 PI5 SM2 L1410	-	-
910505100137	SP534P LED43S/940 PSD LF1 PI5 SM2 L1410	50000 h	25000 h
910505100147	SP534P LED43S/940 PSD LE1 PI5 SM2 L1410	50000 h	25000 h

Order Code	Full Product Name	Median	Median
		useful life L80B50	useful life L90B50
910505100188	SP534P LED34S/940 PSD LE1 PI5 SM2 L1130	50000 h	25000 h
910504103703	SP533P LED24S/840 PSD ACL PI5 SM2 L1170	-	-
910504103803	SP533P LED41S/840 PSD ACL PI5 SM2 L1170	-	-
910504107103	SP533P LED33S/840 PSD LE1 PI5 SM2 L1410	-	-
910504107203	SP533P LED54S/840 PSD LE1 PI5 SM2 L1410	-	-
910504107303	SP533P LED33S/840 PSD LF1 PI5 SM2 L1410	-	-
910504107403	SP533P LED54S/840 PSD LF1 PI5 SM2 L1410	-	-
910504112803	SP534P LED40S/840 PSD PI5 SM2 L1130 ALU	-	-
910504112903	SP534P LED50S/840 PSD PI5 SM2 L1410 ALU	-	-
910505100185	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	50000 h	25000 h

