



# Create a warm, welcoming ambience with superior-quality lighting

## MASTER LEDspot ExpertColor MV

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV and LEDspot Par lamps.

### Benefits

- Create warm and comfortable ambience
- Interior decor, furnishings and fabrics look great
- Hassle-free retrofit solution for greater energy efficiency and sustainability

### Features

- Customised colour spectrum replicates halogen light colour
- Trimless design with beautiful V-groove lens
- Best-in-class colour realisation CRI97, R9>85
- Deep and smooth dimming
- Retrofittable with main-voltage GU10 halogen lamps

# MASTER LEDspot ExpertColor MV


## Application

- Hospitality: hotel guest rooms, corridors, lobbies, reception areas, restaurants, bars, cafes
- Home: living room, bedrooms, hallway
- Retail: exhibitions, display cabinets, shops, dressing rooms


## Versions



## Dimensional drawing




Product	D	C
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	50 mm	54 mm




MASTER LEDspot ExpertColor MV

Accent Diagrams



MASTER LEDspot ExpertColor MV 50W GU10  
927 25D

Beam Diagrams



MASTER LEDspot ExpertColor MV 50W GU10  
927 25D

