



性能和可持续性俱佳

MASTER LEDspot ExpertColor MV

MASTER LEDspot ExpertColor 可定制光谱，具有高 CRI 并配备大范围调光功能，可为酒店场所、家庭和餐厅营造温馨舒适的氛围，带来出众的照明体验。此外，此款灯具采用不带装饰的创新型透镜设计，外观简约，几乎适合所有室内装修风格。MASTER LEDspot ExpertColor 融合了 ExpertColor 系列的所有产品功能，包括 LEDspot MR16、LEDspot AR111 和 LEDspot PAR 灯。该款产品节能效果出众，最大限度地降低了维护成本，而灯光质量和使用寿命丝毫不减，因此住宅和企业所有者能够在短时间内获得投资回报。

优点

- 使用 MASTER LED GU10 营造温馨舒适的氛围
- 可通过轻松的改造方案实现更高能效和可持续性
- 让室内装修、家具和织物更添靓丽

特点


- 可定制光谱，还原卤素灯光色
- 卓越的色彩呈现力，CRI 为 97，R9>85
- 可改造以兼容主电压 GU10 卤素灯
- 广泛兼容各类变压器，调光范围大、变化流畅

应用

- 酒店照明
- 商场照明
- 住宅

MASTER LEDspot ExpertColor MV

二维绘图



Product	D	C
MAS LED ExpertColor 5.5-50W GU10 927 24D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 24D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 25D	50 mm	54 mm
MAS LED ExpertColor 5.5-50W GU10 940 36D	50 mm	54 mm

一般信息	
底盖	GU10
切换循环	50,000
标称使用寿命	40,000 小时
灯技术	
显色指数 (CRI)	97
标称使用寿命结束时灯的光通维持率 (标称)	70 %
操作和电气	
输入频率	50 至 60 Hz
线频率	50 to 60 Hz
功耗	5.5 W
启动时间 (标称)	0.5 s
瓦数相当	50 W
温度	
最大外壳温度 (标称)	80 °C
机械和外壳	
灯泡外形	PAR16
审批和申请	
能耗 kWh/1000 h	6 kWh

灯技术 (1/2)

Order Code	Full Product Name	光束角度 (标称)	相关色温 (标称)	颜色代码	光通量
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	24 °	2700 K	927	385 lm
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	24 °	3000 K	930	405 lm
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	25 °	4000 K	940	400 lm
929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	36 °	2700 K	927	385 lm
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	36 °	3000 K	930	405 lm
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	36 °	4000 K	940	400 lm

灯技术 (2/2)


Order Code	Full Product Name	发光强度 (标称)	Order Code	Full Product Name	发光强度 (标称)
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	1,000 cd	929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	800 cd
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	1,000 cd	929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	800 cd
929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	1,050 cd	929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	800 cd

控制和调光



Order Code	Full Product Name	可调光	Order Code	Full Product Name	可调光
929001347008	MAS LED ExpertColor 5.5-50W GU10 927 24D	是	929001347202	MAS LED ExpertColor 5.5-50W GU10 940 25D	仅限于使用特定调光器
929001347108	MAS LED ExpertColor 5.5-50W GU10 930 24D	是	929001347308	MAS LED ExpertColor 5.5-50W GU10 927 36D	是

MASTER LEDspot ExpertColor MV


Order Code	Full Product Name	可调光
929001347408	MAS LED ExpertColor 5.5-50W GU10 930 36D	是
929001347502	MAS LED ExpertColor 5.5-50W GU10 940 36D	仅限于使用特定调光器




MASTER LEDspot ExpertColor MV




Accent Diagrams




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 927 24D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 930 24D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 25D



Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 927 36D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 930 36D




Accent Diagram - MAS LED ExpertColor
5.5-50W GU10 940 36D


Beam Diagrams




Beam diagram - MAS LED ExpertColor 5.5-50W GU10 927 24D




Beam diagram - MAS LED ExpertColor 5.5-50W GU10 930 24D




Beam diagram - MAS LED ExpertColor 5.5-50W GU10 940 25D



Beam diagram - MAS LED ExpertColor 5.5-50W GU10 927 36D



Beam diagram - MAS LED ExpertColor 5.5-50W GU10 930 36D



Beam diagram - MAS LED ExpertColor 5.5-50W GU10 940 36D

