



Setting the standard in Surface-mounted LED Downlight

GreenSpace Surface-mounted

Philips GreenSpace Surface-mounted LED Downlight delivers a superior LED alternative that's up to 66% more energy efficient than the conventional downlight retrofits. Blending seamlessly into its environment, GreenSpace Surface-mounted LED Downlight mimics the form of conventional recessed downlights minus the associated high energy and maintenance costs. Philips GreenSpace Surface-mounted LED Downlight is also ideal for all commercial lighting applications as well as public indoor space where there is limited space in the ceiling.

Benefits

- Lumen output: Different lumens in different sizes and mounting heights with options of 1000lm, 2000lm, 3800lm & 6600lm.
- Superior light performance: Colours rendered accurately (CRI > 80) and high system efficacy (100lm/w)
- Varieties: IP20, IP65 version with choice of different lumen output, and option of black housing through tailor-made
- Long lifetime: 50,000 hour lifetime ensures more savings in the long run

Features

- System efficacy: 100lm/W, energy saving up to 66% vs conventional downlights
- Reliable performance: Lifetime 50,000 hours (L70B50@Ta25°C)
- Excellent light quality - CRI >= 80 @ 3000K, 4000K and 6500K
- Integral lightweight design - Installation cost is significantly reduced

GreenSpace Surface-mounted

Application

- Shopping mall
- Station concourse
- Canopy
- Airport public area
- Stadium public area

Versions



SM291C/SM293C



SM295C LED68

Application Conditions	
Ambient temperature range	-20 to +40 °C
Suitable for random switching	No
Approval and Application	
Mech. impact protection code	IK02
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
Protection class IEC	Safety class I (I)
Optical cover/lens type	Reflector
Driver included	Yes
Glow-wire test	750/5
Light source replaceable	No
Number of gear units	1 unit
Optic type	C
Initial Performance (IEC Compliant)	
Init. Colour Rendering Index	>80
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L80B50	40000 h
Median useful life L90B50	20000 h

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401509231	SM291C LED10/840 PSU BK	-
911401509831	SM293C LED20/840 PSU BK	-
911401510431	SM294C LED40/840 PSU BK	-
911401847199	SM291C LED10/830 PSU WH GM	-
911401847299	SM291C LED10/840 PSU WH GM	-
911401847399	SM291C LED10/865 PSU WH GM	-
911401847499	SM293C LED20/830 PSU WH GM	-
911401847599	SM293C LED20/840 PSU WH GM	-
911401847699	SM293C LED20/865 PSU WH GM	-
911401847799	SM295C LED70/840 PSU WP WH GM	-
911401847899	SM295C LED70/830 PSU WP WH GM	-
911401847999	SM294C LED40/840 PSU WP WH GM	-
911401848099	SM295C LED70/865 PSU WP WH GM	-
911401848299	SM294C LED40/865 PSU WP WH GM	-
911401848399	SM294C LED40/830 PSU WP WH GM	-
911401848499	SM295C LED70/830 PSU WH GM	-
911401848599	SM294C LED40/830 PSU WH GM	-
911401848699	SM294C LED40/840 PSU WH GM	-
911401848799	SM294C LED40/865 PSU WH GM	-
911401848899	SM295C LED70/840 PSU WH GM	-
911401511031	SM295C LED68/840 PSU BK	Not applicable
911401512231	SM295C LED68/840 PSU WP BK	Not applicable

GreenSpace Surface-mounted

Approval and Application

Order Code	Full Product Name	Ingress protection code
911401509231	SM291C LED10/840 PSU BK	IP20
911401509831	SM293C LED20/840 PSU BK	IP20
911401510431	SM294C LED40/840 PSU BK	IP65
911401847199	SM291C LED10/830 PSU WH GM	IP20
911401847299	SM291C LED10/840 PSU WH GM	IP20
911401847399	SM291C LED10/865 PSU WH GM	IP20
911401847499	SM293C LED20/830 PSU WH GM	IP20
911401847599	SM293C LED20/840 PSU WH GM	IP20
911401847699	SM293C LED20/865 PSU WH GM	IP20
911401847799	SM295C LED70/840 PSU WP WH GM	IP65
911401847899	SM295C LED70/830 PSU WP WH GM	IP65

Order Code	Full Product Name	Ingress protection code
911401847999	SM294C LED40/840 PSU WP WH GM	IP65
911401848099	SM295C LED70/865 PSU WP WH GM	IP65
911401848299	SM294C LED40/865 PSU WP WH GM	IP65
911401848399	SM294C LED40/830 PSU WP WH GM	IP65
911401848499	SM295C LED70/830 PSU WH GM	IP20
911401848599	SM294C LED40/830 PSU WH GM	IP20
911401848699	SM294C LED40/840 PSU WH GM	IP20
911401848799	SM294C LED40/865 PSU WH GM	IP20
911401848899	SM295C LED70/840 PSU WH GM	IP20
911401511031	SM295C LED68/840 PSU BK	IP65
911401512231	SM295C LED68/840 PSU WP BK	IP65

General Information

Order Code	Full Product Name	Beam angle of light source	ENEC		Flammability
			CE mark	mark	mark
911401509231	SM291C LED10/840 PSU BK	-	CE mark	-	-
911401509831	SM293C LED20/840 PSU BK	-	CE mark	-	-
911401510431	SM294C LED40/840 PSU BK	-	CE mark	-	-
911401847199	SM291C LED10/830 PSU WH GM	-°	CE mark	-	NO
911401847299	SM291C LED10/840 PSU WH GM	-°	CE mark	-	NO
911401847399	SM291C LED10/865 PSU WH GM	-°	CE mark	-	NO
911401847499	SM293C LED20/830 PSU WH GM	-°	CE mark	-	NO
911401847599	SM293C LED20/840 PSU WH GM	-°	CE mark	-	NO
911401847699	SM293C LED20/865 PSU WH GM	-°	CE mark	-	NO
911401847799	SM295C LED70/840 PSU WP WH GM	-°	CE mark	-	NO
911401847899	SM295C LED70/830 PSU WP WH GM	-°	CE mark	-	NO

Order Code	Full Product Name	Beam angle of light source	ENEC		Flammability
			CE mark	mark	mark
911401847999	SM294C LED40/840 PSU WP WH GM	-°	CE mark	-	NO
911401848099	SM295C LED70/865 PSU WP WH GM	-°	CE mark	-	NO
911401848299	SM294C LED40/865 PSU WP WH GM	-°	CE mark	-	NO
911401848399	SM294C LED40/830 PSU WP WH GM	-°	CE mark	-	NO
911401848499	SM295C LED70/830 PSU WH GM	-°	CE mark	-	NO
911401848599	SM294C LED40/830 PSU WH GM	-°	CE mark	-	NO
911401848699	SM294C LED40/840 PSU WH GM	-°	CE mark	-	NO
911401848799	SM294C LED40/865 PSU WH GM	-°	CE mark	-	NO
911401848899	SM295C LED70/840 PSU WH GM	-°	CE mark	-	NO
911401511031	SM295C LED68/840 PSU BK	-	-	-	-
911401512231	SM295C LED68/840 PSU WP BK	-	-	-	-

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Initial LED	Initial
			Colour Temperature	luminaire efficacy	luminous flux
911401509231	SM291C LED10/840 PSU BK	(0.38, 0.38) SDCM <5	4000 K	100.000 lm/W	1000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr.	Initial LED	Initial
			Colour Temperature	luminaire efficacy	luminous flux
911401509831	SM293C LED20/840 PSU BK	(0.38, 0.38) SDCM <5	4000 K	105.000 lm/W	2000 lm

GreenSpace Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401510431	SM294C LED40/840 PSU BK	(0.38, 0.38)	4000 K	105.000 lm/W	3800 lm
911401847199	SM291C LED10/830 PSU WH GM	(0.44, 0.40)	3000 K	100.000 lm/W	1000 lm
911401847299	SM291C LED10/840 PSU WH GM	(0.38, 0.38)	4000 K	100.000 lm/W	1000 lm
911401847399	SM291C LED10/865 PSU WH GM	(0.31, 0.32)	6500 K	100.000 lm/W	1000 lm
911401847499	SM293C LED20/830 PSU WH GM	(0.44, 0.40)	3000 K	105.000 lm/W	2000 lm
911401847599	SM293C LED20/840 PSU WH GM	(0.38, 0.38)	4000 K	105.000 lm/W	2000 lm
911401847699	SM293C LED20/865 PSU WH GM	(0.31, 0.32)	6500 K	105.000 lm/W	2000 lm
911401847799	SM295C LED70/840 PSU WP WH GM	(0.38, 0.38)	4000 K	100.000 lm/W	6600 lm
911401847899	SM295C LED70/830 PSU WP WH GM	(0.44, 0.40)	3000 K	100.000 lm/W	6600 lm
911401847999	SM294C LED40/840 PSU WP WH GM	(0.38, 0.38)	4000 K	105.000 lm/W	3800 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401848099	SM295C LED70/865 PSU WP WH GM	(0.31, 0.32)	6500 K	100.000 lm/W	6600 lm
911401848299	SM294C LED40/865 PSU WP WH GM	(0.31, 0.32)	6500 K	105.000 lm/W	3800 lm
911401848399	SM294C LED40/830 PSU WP WH GM	(0.44, 0.40)	3000 K	105.000 lm/W	3800 lm
911401848499	SM295C LED70/830 PSU WH GM	(0.44, 0.40)	3000 K	100.000 lm/W	6600 lm
911401848599	SM294C LED40/830 PSU WH GM	(0.44, 0.40)	3000 K	100.000 lm/W	3800 lm
911401848699	SM294C LED40/840 PSU WH GM	(0.38, 0.38)	4000 K	100.000 lm/W	3800 lm
911401848799	SM294C LED40/865 PSU WH GM	(0.31, 0.32)	6500 K	100.000 lm/W	3800 lm
911401848899	SM295C LED70/840 PSU WH GM	(0.38, 0.38)	4000 K	100.000 lm/W	6600 lm
911401511031	SM295C LED68/840 PSU BK	(0.38, 0.38)	4000 K	100 lm/W	6600 lm
911401512231	SM295C LED68/840 PSU WP BK	(0.38, 0.38)	4000 K	100 lm/W	6600 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
911401509231	SM291C LED10/840 PSU BK	10 W
911401509831	SM293C LED20/840 PSU BK	19 W
911401510431	SM294C LED40/840 PSU BK	36 W
911401847199	SM291C LED10/830 PSU WH GM	10 W
911401847299	SM291C LED10/840 PSU WH GM	10 W
911401847399	SM291C LED10/865 PSU WH GM	10 W
911401847499	SM293C LED20/830 PSU WH GM	19 W
911401847599	SM293C LED20/840 PSU WH GM	19 W
911401847699	SM293C LED20/865 PSU WH GM	19 W
911401847799	SM295C LED70/840 PSU WP WH GM	66 W
911401847899	SM295C LED70/830 PSU WP WH GM	66 W

Order Code	Full Product Name	Initial input power
911401847999	SM294C LED40/840 PSU WP WH GM	36 W
911401848099	SM295C LED70/865 PSU WP WH GM	66 W
911401848299	SM294C LED40/865 PSU WP WH GM	36 W
911401848399	SM294C LED40/830 PSU WP WH GM	36 W
911401848499	SM295C LED70/830 PSU WH GM	66 W
911401848599	SM294C LED40/830 PSU WH GM	38 W
911401848699	SM294C LED40/840 PSU WH GM	38 W
911401848799	SM294C LED40/865 PSU WH GM	38 W
911401848899	SM295C LED70/840 PSU WH GM	66 W
911401511031	SM295C LED68/840 PSU BK	66 W
911401512231	SM295C LED68/840 PSU WP BK	66 W

Mechanical and Housing

GreenSpace Surface-mounted

Order Code	Full Product Name	Colour
911401509231	SM291C LED10/840 PSU BK	White
911401509831	SM293C LED20/840 PSU BK	White
911401510431	SM294C LED40/840 PSU BK	White
911401847199	SM291C LED10/830 PSU WH GM	White
911401847299	SM291C LED10/840 PSU WH GM	White
911401847399	SM291C LED10/865 PSU WH GM	White
911401847499	SM293C LED20/830 PSU WH GM	White
911401847599	SM293C LED20/840 PSU WH GM	White
911401847699	SM293C LED20/865 PSU WH GM	White
911401847799	SM295C LED70/840 PSU WP WH GM	White
911401847899	SM295C LED70/830 PSU WP WH GM	White

Order Code	Full Product Name	Colour
911401847999	SM294C LED40/840 PSU WP WH GM	White
911401848099	SM295C LED70/865 PSU WP WH GM	White
911401848299	SM294C LED40/865 PSU WP WH GM	White
911401848399	SM294C LED40/830 PSU WP WH GM	White
911401848499	SM295C LED70/830 PSU WH GM	White
911401848599	SM294C LED40/830 PSU WH GM	White
911401848699	SM294C LED40/840 PSU WH GM	White
911401848799	SM294C LED40/865 PSU WH GM	White
911401848899	SM295C LED70/840 PSU WH GM	White
911401511031	SM295C LED68/840 PSU BK	black
911401512231	SM295C LED68/840 PSU WP BK	black

