



# Warmes, einladendes Ambiente mit herausragender Lichtqualität

## MASTER LEDspot MR16 ExpertColor

MASTER LEDspot LV ExpertColor schafft ein warmes und komfortables Ambiente im Gastgewerbe, Eigenheim und Restaurant. Es erreicht dieses Ambiente durch überragendes Licht mit angepasstem Spektrum, hohem CRI-Wert und leistungsstarker Dimm-Funktion. Das Ergebnis? Eine wunderschöne Beleuchtung. Darüber hinaus ist das innovative Linsendesign ohne Einfassung durch ihr sauberes und klares Aussehen für nahezu jede Inneneinrichtung geeignet. Sie können außerdem die gesamte ExpertColor-Familie nutzen, die auch Lampen der Serien LEDspot MV und LEDspot Par einschließt.

### Vorteile

- Warmes und komfortables Ambiente
- Fantastisches Aussehen für Inneneinrichtung, Möbel und Stoffe
- Nachrüstlösung ohne Aufwand für größere Energieeffizienz und Nachhaltigkeit

### Merkmale


- Angepasstes Farbspektrum gibt Halogen-Lichtfarben wieder
- Design ohne Verkleidung mit wunderschöner V-förmiger Linse
- Branchenführende Farbumsetzung CRI97, R9>85
- Dunkles und sanftes Dimmen mit hoher Transformatorenkompatibilität
- Nachrüstung von MR16 Niedervolt-Halogenlampen mit GU5.3-Sockel

# MASTER LEDspot MR16 ExpertColor

## Anwendung


- Gastgewerbe: Hotelzimmer, Flure, Lobbys, Empfangsbereiche, Restaurants, Bars, Cafés
- Zuhause: Wohnzimmer, Schlafzimmer, Flure
- Einzelhandel: Ausstellungen, Vitrinenschränke, Geschäfte, Umkleieräume

## Versions



# MASTER LEDspot MR16 ExpertColor

## Abmessungsskizzen



| Product   | D       | C     |
|---|---------|-------|
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 927 60D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 10D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 940 10D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 927 10D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 940 60D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 60D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 927 24D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 927 36D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 24D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 36D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 940 24D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 940 36D | 51 mm   | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 927 24D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 940 24D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 927 36D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 940 36D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 930 36D | 50,5 mm | 46 mm |
| MASTER LED ExpertColor LED ExpertColor 7.5-43W MR16 930 24D | 50,5 mm | 46 mm |

# MASTER LEDspot MR16 ExpertColor

| Dimmen                     |                    |
|----------------------------|--------------------|
| Dimmbar                    | Ja                 |
| Elektrische Kenndaten      |                    |
| Spannung (nom.)            | ac electronic 12 V |
| Startzeit (nom.)           | 0,5 s              |
| Allgemeine Eigenschaften   |                    |
| Sockel                     | GU5.3              |
| Nennlebensdauer (nom.)     | 40000 h            |
| Nennlebensdauer (Std.)     | 40000 h            |
| Schaltzyklus               | 50000X             |
| Lichttechnische Daten      |                    |
| Restlichtstrom am Ende der | 70 %               |
| Nennlebensdauer (nom.)     |                    |
| Mechanische Kenndaten      |                    |
| Kolbenform                 | MR16               |

## Zulassungen und Anwendungseigenschaften

| Order Code | Full Product Name  | Energieverbrauch kWh/1.000 Std. | Energieeffizienz-Label (EEL) |
|------------|--|---------------------------------|------------------------------|
| 75751200   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 60D | 8 kWh                           | A                            |
| 75753600   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 60D | 8 kWh                           | A+                           |
| 75755000   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 60D | 8 kWh                           | A+                           |
| 73877100   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 24D | 8 kWh                           | A                            |
| 73879500   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 24D | 8 kWh                           | A+                           |
| 73881800   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 24D | 8 kWh                           | A+                           |
| 73883200   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 36D | 8 kWh                           | A                            |
| 73885600   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 36D | 8 kWh                           | A+                           |
| 73887000   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 36D | 8 kWh                           | A+                           |
| 73871900   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 10D | 8 kWh                           | A                            |
| 73873300   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 10D | 8 kWh                           | A                            |
| 73875700   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 10D | 8 kWh                           | A+                           |
| 73538100   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 927 24D | 9 kWh                           | A                            |
| 73540400   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 930 24D | 9 kWh                           | A                            |
| 73542800   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 940 24D | 9 kWh                           | A                            |
| 73544200   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 927 36D | 9 kWh                           | A                            |
| 73546600   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 930 36D | 9 kWh                           | A                            |
| 73548000   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 940 36D | 9 kWh                           | A                            |

## Elektrische Kenndaten

| Order Code | Full Product Name  | Äquivalente Leistung | Nennleistung (nom.) | Order Code | Full Product Name  | Äquivalente Leistung | Nennleistung (nom.) |
|------------|--|----------------------|---------------------|------------|--|----------------------|---------------------|
| 75751200   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 60D | 35 W                 | 6.5 W               | 73879500   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 24D | 35 W                 | 6.5 W               |
| 75753600   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 60D | 35 W                 | 6.5 W               | 73881800   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 24D | 35 W                 | 6.5 W               |
| 75755000   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 60D | 35 W                 | 6.5 W               | 73883200   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 36D | 35 W                 | 6.5 W               |
| 73877100   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 24D | 35 W                 | 6.5 W               | 73885600   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 36D | 35 W                 | 6.5 W               |

# MASTER LEDspot MR16 ExpertColor

| Order Code | Full Product Name  | Äquivalente Leistung | Nennleistung (nom.) |
|------------|--|----------------------|---------------------|
| 73887000   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 36D | 35 W                 | 6.5 W               |
| 73871900   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 10D | 35 W                 | 6.5 W               |
| 73873300   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 10D | 35 W                 | 6.5 W               |
| 73875700   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 10D | 35 W                 | 6.5 W               |
| 73538100   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 927 24D | 43 W                 | 7.5 W               |

| Order Code | Full Product Name  | Äquivalente Leistung | Nennleistung (nom.) |
|------------|--|----------------------|---------------------|
| 73540400   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 930 24D | 43 W                 | 7.5 W               |
| 73542800   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 940 24D | 43 W                 | 7.5 W               |
| 73544200   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 927 36D | 43 W                 | 7.5 W               |
| 73546600   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 930 36D | 43 W                 | 7.5 W               |
| 73548000   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 940 36D | 43 W                 | 7.5 W               |

## Lichttechnische Daten (1/2)

| Order Code | Full Product Name  | Ausstrahlungswinkel (nom.) | Ähnlichste |                       |                      | Order Code | Full Product Name                   | Ausstrahlungswinkel (nom.) | Ähnlichste |                       |                      |
|------------|--|----------------------------|------------|-----------------------|----------------------|------------|-------------------------------------|----------------------------|------------|-----------------------|----------------------|
|            |  |                            | Farbcode   | Farbtemperatur (nom.) | Farbwiedergab (nom.) |            |                                     |                            | Farbcode   | Farbtemperatur (nom.) | Farbwiedergab (nom.) |
| 75751200   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 927 60D | 60 °                       | 927        | 2700 K                | 97                   |            | ExpertColor 6.5-35W<br>MR16 940 36D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73871900   | MASTER LED<br>ExpertColor LED       | 10 °                       | 927        | 2700 K                | 97                   |
| 75753600   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 930 60D | 60 °                       | 930        | 3000 K                | 97                   |            | ExpertColor 6.5-35W<br>MR16 927 10D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73873300   | MASTER LED<br>ExpertColor LED       | 10 °                       | 930        | 3000 K                | 97                   |
| 75755000   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 940 60D | 60 °                       | 940        | 4000 K                | 97                   |            | ExpertColor 6.5-35W<br>MR16 930 10D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73875700   | MASTER LED<br>ExpertColor LED       | 10 °                       | 940        | 4000 K                | 97                   |
| 73877100   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 927 24D | 24 °                       | 927        | 2700 K                | 97                   |            | ExpertColor 6.5-35W<br>MR16 940 10D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73538100   | MASTER LED<br>ExpertColor LED       | 24 °                       | 927        | 2700 K                | 92                   |
| 73879500   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 930 24D | 24 °                       | 930        | 3000 K                | 97                   |            | ExpertColor 7.5-43W<br>MR16 927 24D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73540400   | MASTER LED<br>ExpertColor LED       | 24 °                       | 930        | 3000 K                | 92                   |
| 73881800   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 940 24D | 24 °                       | 940        | 4000 K                | 97                   |            | ExpertColor 7.5-43W<br>MR16 930 24D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73542800   | MASTER LED<br>ExpertColor LED       | 24 °                       | 940        | 4000 K                | 92                   |
| 73883200   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 927 36D | 36 °                       | 927        | 2700 K                | 97                   |            | ExpertColor 7.5-43W<br>MR16 940 24D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73544200   | MASTER LED<br>ExpertColor LED       | 36 °                       | 927        | 2700 K                | 92                   |
| 73885600   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 930 36D | 36 °                       | 930        | 3000 K                | 97                   |            | ExpertColor 7.5-43W<br>MR16 927 36D |                            |            |                       |                      |
|            |  |                            |            |                       |                      | 73546600   | MASTER LED<br>ExpertColor LED       | 36 °                       | 930        | 3000 K                | 92                   |
| 73887000   | MASTER LED<br>ExpertColor LED  | 36 °                       | 940        | 4000 K                | 97                   |            | ExpertColor 7.5-43W<br>MR16 930 36D |                            |            |                       |                      |

# MASTER LEDspot MR16 ExpertColor

| Order Code | Full Product Name             | Ausstrahlungswinkel (nom.) | Ähnlichste |                       |                | Order Code                          | Full Product Name | Ausstrahlungswinkel (nom.) | Ähnlichste      |                      |
|------------|-------------------------------|----------------------------|------------|-----------------------|----------------|-------------------------------------|-------------------|----------------------------|-----------------|----------------------|
|            |                               |                            | Farbcode   | Farbtemperatur (nom.) | Farbwie (nom.) |                                     |                   |                            | Farbcode (nom.) | Farbwiedergab (nom.) |
| 73548000   | MASTER LED<br>ExpertColor LED | 36 °                       | 940        | 4000 K                | 92             | ExpertColor 7.5-43W<br>MR16 940 36D |                   |                            |                 |                      |







## Lichttechnische Daten (2/2)

| Order Code | Full Product Name  | Lichtstrom (nom.) | Nennlichtstrom (nom.) | Lichtstärke (nom.) | Nenn-Abstrahlungswinkel | Order Code | Full Product Name  | Lichtstrom (nom.) | Nennlichtstrom (nom.) | Lichtstärke (nom.) | Nenn-Abstrahlungswinkel |
|------------|--|-------------------|-----------------------|--------------------|-------------------------|------------|--|-------------------|-----------------------|--------------------|-------------------------|
| 75751200   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 927 60D | 400 lm            | 400 lm                | 410 cd             | 60 °                    |            | ExpertColor 6.5-35W<br>MR16 927 10D                                  |                   |                       |                    |                         |
| 75753600   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 930 60D | 440 lm            | 440 lm                | 440 cd             | 60 °                    | 73873300   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 930 10D | 430 lm            | 430 lm                | 5000 cd            | 10 °                    |
| 75755000   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 940 60D | 440 lm            | 440 lm                | 440 cd             | 60 °                    | 73875700   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 940 10D | 440 lm            | 440 lm                | 5000 cd            | 10 °                    |
| 73877100   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 927 24D | 420 lm            | 420 lm                | 2200 cd            | 24 °                    | 73538100   | MASTER LED<br>ExpertColor LED<br>ExpertColor 7.5-43W<br>MR16 927 24D | 485 lm            | 485 lm                | 2400 cd            | 24 °                    |
| 73879500   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 930 24D | 440 lm            | 440 lm                | 2350 cd            | 24 °                    | 73540400   | MASTER LED<br>ExpertColor LED<br>ExpertColor 7.5-43W<br>MR16 930 24D | 500 lm            | 500 lm                | 2600 cd            | 24 °                    |
| 73881800   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 940 24D | 460 lm            | 460 lm                | 2350 cd            | 24 °                    | 73542800   | MASTER LED<br>ExpertColor LED<br>ExpertColor 7.5-43W<br>MR16 940 24D | 520 lm            | 520 lm                | 2800 cd            | 24 °                    |
| 73883200   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 927 36D | 420 lm            | 420 lm                | 1300 cd            | 36 °                    | 73544200   | MASTER LED<br>ExpertColor LED<br>ExpertColor 7.5-43W<br>MR16 927 36D | 485 lm            | 485 lm                | 1400 cd            | 36 °                    |
| 73885600   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 930 36D | 440 lm            | 440 lm                | 1400 cd            | 36 °                    | 73546600   | MASTER LED<br>ExpertColor LED<br>ExpertColor 7.5-43W<br>MR16 930 36D | 500 lm            | 500 lm                | 1550 cd            | 36 °                    |
| 73887000   | MASTER LED<br>ExpertColor LED<br>ExpertColor 6.5-35W<br>MR16 940 36D | 460 lm            | 460 lm                | 1400 cd            | 36 °                    | 73548000   | MASTER LED<br>ExpertColor LED<br>ExpertColor 7.5-43W<br>MR16 940 36D | 520 lm            | 520 lm                | 1650 cd            | 36 °                    |
| 73871900   | MASTER LED<br>ExpertColor LED  | 410 lm            | 410 lm                | 4600 cd            | 10 °                    |            |  |                   |                       |                    |                         |



## Temperaturkenndaten

# MASTER LEDspot MR16 ExpertColor




| Order Code | Full Product Name  | Gehäusetemperatur (max.) |
|------------|--|--------------------------|
| 75751200   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 60D | 90 °C                    |
| 75753600   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 60D | 90 °C                    |
| 75755000   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 60D | 90 °C                    |
| 73877100   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 24D | 90 °C                    |
| 73879500   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 24D | 90 °C                    |
| 73881800   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 24D | 90 °C                    |
| 73883200   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 36D | 90 °C                    |
| 73885600   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 36D | 90 °C                    |
| 73887000   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 36D | 90 °C                    |
| 73871900   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 927 10D | 90 °C                    |
| 73873300   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 930 10D | 90 °C                    |
| 73875700   | MASTER LED ExpertColor LED<br>ExpertColor 6.5-35W MR16 940 10D | 90 °C                    |
| 73538100   | MASTER LED ExpertColor LED<br>ExpertColor 7.5-43W MR16 927 24D | 93 °C                    |
| 73540400   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 930 24D | 93 °C                    |
| 73542800   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 940 24D | 93 °C                    |
| 73544200   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 927 36D | 93 °C                    |
| 73546600   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 930 36D | 93 °C                    |
| 73548000   | MASTER LED ExpertColor LED ExpertColor<br>7.5-43W MR16 940 36D | 93 °C                    |



# MASTER LEDspot MR16 ExpertColor



## Accent Diagrams



Master LEDspot ExpertColor LV 50W GU5.3 927  
60D


Master LEDspot ExpertColor LV 50W GU5.3 930  
60D

Master LEDspot ExpertColor LV 50W GU5.3 940  
60D




# MASTER LEDspot MR16 ExpertColor


## Accent Diagrams




LEDSpot MR16 7W 927 430lm 10D




LEDSpots MR16 7W 930 460lm 10D




LEDSpots MR16 7W 940 460lm 10D




LEDSpots MR16 7W 927 430lm 25D




LEDSpots MR16 7W 930 460lm 25D




LEDSpots MR16 7W 940 460lm 25D




LEDSpots MR16 7W 927 430lm 35D




LEDSpots MR16 7W 930 460lm 35D




LEDSpots MR16 7W 940 460lm 35D



MAS LEDspotLV 43W GU5-3 927 24D MR16




MAS LEDspotLV 43W GU5-3 930 24D MR16




MAS LEDspotLV 43W GU5-3 940 24D MR16

# MASTER LEDspot MR16 ExpertColor


## Accent Diagrams



MAS LEDspotLV 43W GU5-3 927 36D MR16




MAS LEDspotLV 43W GU5-3 930 36D MR16




MAS LEDspotLV 43W GU5-3 940 36D MR16


## Beam Diagrams




Master LEDspot ExpertColor LV 50W GU5.3 927 60D




Master LEDspot ExpertColor LV 50W GU5.3 930 60D




Master LEDspot ExpertColor LV 50W GU5.3 940 60D



LEDSpot MR16 7W 927 430lm 10D




LEDSpots MR16 7W 930 460lm 10D




LEDSpots MR16 7W 940 460lm 10D

# MASTER LEDspot MR16 ExpertColor


## Beam Diagrams




LEDSpots MR16 7W 927 430lm 25D




LEDSpots MR16 7W 930 460lm 25D




LEDSpots MR16 7W 940 460lm 25D




LEDSpots MR16 7W 927 430lm 35D




LEDSpots MR16 7W 930 460lm 35D




LEDSpots MR16 7W 940 460lm 35D




MAS LEDspotLV 43W GU5-3 927 24D MR16




MAS LEDspotLV 43W GU5-3 930 24D MR16




MAS LEDspotLV 43W GU5-3 940 24D MR16



MAS LEDspotLV 43W GU5-3 927 36D MR16



MAS LEDspotLV 43W GU5-3 930 36D MR16



MAS LEDspotLV 43W GU5-3 940 36D MR16

# MASTER LEDspot MR16 ExpertColor

