



Architectural and landscape LED spotlight with solid white light

eW Burst Powercore gen2

eW Burst Powercore gen2 is a high-output, exterior-rated LED lighting luminaire designed for accent and site lighting. Architectural and Landscape versions deliver high-quality white light output in a warm 2,700 K and a neutral 4,000 K to support a range of uplighting, floodlighting and decorative lighting applications.

Benefits

- High-quality solid white light
- Versatile light positioning
- Cost-effective, easy to install, and long lifetime

eW Burst Powercore gen2

Features

- Expands customisation with a wide range of new Philips accessory options.
- In addition to the native 6° lens, six different diffuser lenses can customise the luminaire to produce 10°, 20°, 40°, 60°, 80°, and 10° x 40° (asymmetric) beam angles.
- Four housing colour choices (black, grey, white, and bronze)—plus the option to add a louver, full glare shield, and half glare shield—create new aesthetic possibilities for designers and architects.
- Meets ASTM G85 corrosion resistance and ANSI C136.31-2010 standard with a 3G vibration rating.
- Improves durability with new flat lens that prevents water from pooling into the luminaire, keeping the LEDs protected and secure over the course of a luminaire's lifetime.
- Universal power input range of 100 to 277 VAC.
- Precision Dimming— Smooth dimming down to 1% with optional Data Enabler Pro and digital control interface.

Application

- Facades, Surfaces, Iconic Structures & Bridges

Versions



Product details



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture

eW Burst Powercore gen2

Product details



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture

eW Burst Powercore gen2

Product details



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Landscape fixture

eW Burst Powercore gen2

Product details



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture



ColorBurst Powercore gen2 LED
spotlight Architectural fixture

