



# An innovative way of communicating dimming signals over mains wiring

## Coded Mains

### Application

- **Road and street** - for use in conjunction with remote light management system for retrofit group dimming application.
- **Tunnels** - for use in conjunction with tunnel control system for retrofit tunnel stage control.
- **Sports** - for use in conjunction with local GUI to control sports field lighting.
- **Area lighting** - for use to control parking lots, industrial areas, etc.

### Versions



LFC7710/00 Coded Mains Transmitter



LCU7725/00 Coded Mains Transformer LN



Coded Mains

Versions



Product details

Coded Mains Transmitter



Coded Mains Receiver LN

