



# Versatile and cost-efficient LED lighting

## ClearWay gen2

ClearWay gen2 enables you to enjoy the benefits of LED technology right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimize your Total Cost of Ownership. ClearWay gen2 significantly improves the most important aspects of the street lighting experience compared to conventional lighting. Ideal for new streets and for renovating existing installations, this affordable range of lighting solutions combines clean, high quality light with significant energy and maintenance savings. In short, ClearWay gen2 means good quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design, which makes it easier to install.

### Benefits

- All benefits packaged in one single luminaire architecture
- Easy to install
- Low initial cost
- Reasonable Total Cost of Ownership
- Easy luminaire is uniquely identifiable thanks to Philips Service tag

### Features

- One flexible design variant offering different options depending on the needs of the application
- Compact and efficient design
- Tilt regulation without needing to open cover
- ClearWay gen2 is also equipped with a dedicated light recipes that preserves a dark night sky.

## Application

- Urban and residential roads
- Bicycle and pedestrian paths
- Minor roads

## Specifications

<b>Type</b>	BGP307
<b>Light source</b>	Integral LED-module
<b>Power</b>	5,9 to 82W (depending on the version)
<b>Luminous flux</b>	Core version from 2 250 to 9 460lm (system) Performer version: from 700 to 10 920lm (system)
<b>Luminaire efficacy</b>	Up to 150 lm/W (depending on the version)
<b>Correlated Color</b>	Core:
<b>Temperature</b>	Neutral white (NW): 4000 K Performer Warm white (WW): 3000 K Neutral white (NW): 4000 K
<b>Color Rendering Index</b>	NW: 70 WW: 80
<b>Lumen maintenance at median useful life* 100000 h</b>	Performer: up to L97 Core: min L80
<b>Control gear failure rate at median useful life 100000 h</b>	10%
<b>Performance Ambient Temperature Tq</b>	+25 °C
<b>Operating temperature range</b>	-30 to +35°C (wider range upon request)
<b>Driver</b>	Built-in (self-ballasted LED-module)
<b>Mains voltage</b>	220-240 V / 50-60 Hz
<b>Dimming</b>	LightWave CityTouch LineSwitch CodedMains LumiStep DynaDimmer MainsDimming
<b>Options</b>	System Ready Interface Nema Socket 5 PIN Nema Socket 7 PIN Constant light output (CLO) External cable 4, 6, 8, 10, 12, 15, 22 m Surge protection device (up to 10 kV) Backlight louver (BL1 and BL2) for some optics

<b>Optic</b>	Core version: Distribution Medium (DM) or Distribution Wide (DW) Performer version: Distribution Narrow (DN10), Distribution Medium (DM10, DM11, DM12, DM50), Distribution Wide (DW10) Other premium optics for performer upon request
<b>Material</b>	Housing: die-cast aluminum, high-pressure Cover: glass, thermally hardened, 5 mm
<b>Color</b>	Standard light grey, (RAL7035), other colors upon request
<b>Connection</b>	Screw connection block or cable or as option an external IP connector
<b>Maintenance</b>	Opening cover with 2 screws The Philips Service tag will help to identify the product and share all product information on the spot
<b>Installation</b>	Side entry mounting: Ø 32-48 or 48-60 mm Post-top mounting: Ø 32-48, 48-60 or 76 mm Optional spigot insert (reducer) Recommended mounting height: 4-18 m Standard tilt angle post top: +0 to 15° Standard tilt angle side entry: +15 to -90° Max SCx: 0,0203 m²
<b>SR compatibility</b>	Luminaire prepared for SR drivers and socket, offering a standardized futureproof platform for connectivity and sensors. For SR based luminaires only SR Certified components/sensors are to be used (see also: <a href="http://www.lighting.philips.co.uk/oem-emea/products/driving-connected-lighting">http://www.lighting.philips.co.uk/oem-emea/products/driving-connected-lighting</a> ). Functional compatibility of 2 (SR certified) components/sensors to be used in combination as well as override possibility of any lineswitch function used in a SR based luminaire, is to be released by the master component/sensor supplier. For the use of NEMA 7pin socket on a SR based luminaire a full system verification is required. Not following these advises can/will cause risk of damage and non-compliance for which Signify cannot take any responsibility.

# ClearWay gen2

## Versions



ClearWay gen2 - LED Module  
2500 lm - 740 neutral white -  
Safety class I - Distribution  
medium - Universal for diameter  
48 to 60 mm adjustable



ClearWay gen2 - LED module 1800  
lm - 740 neutral white - Safety  
class I - Distribution medium 50 -  
Universal for diameter 48 to 60  
mm adjustable

### Approval and Application

Mech. impact protection code IK08

### General Information

CE mark CE mark

Optical cover/lens type Flat glass

Driver included Yes

ENEC mark ENEC mark

Flammability mark -

Light source replaceable Yes

Number of gear units 1 unit

Product Family Code BGP307

### Light Technical

Standard tilt angle side entry 0°

Standard tilt angle posttop 0°

Upward light output ratio 0

### Application Conditions

Order Code	Full Product Name	Maximum dim level
910925864560	BGP307 LED25/740 I DM 48/60S	Not applicable
910925864561	BGP307 LED30/740 I DM 48/60S	Not applicable
910925864562	BGP307 LED35/740 I DM 48/60S	Not applicable
910925864563	BGP307 LED40/740 I DM 48/60S	Not applicable
910925864564	BGP307 LED45/740 I DM 48/60S	Not applicable
910925864565	BGP307 LED54/740 I DM 48/60S	Not applicable
910925864566	BGP307 LED69/740 I DM 48/60S	Not applicable
910925864567	BGP307 LED84/740 I DM 48/60S	Not applicable
910925864568	BGP307 LED99/740 I DM 48/60S	Not applicable
910925864569	BGP307 LED109/740 I DM 48/60S	Not applicable
910925864572	BGP307 LED25/740 II DM 48/60S	Not applicable
910925864573	BGP307 LED30/740 II DM 48/60S	Not applicable
910925864574	BGP307 LED35/740 II DM 48/60S	Not applicable
910925864575	BGP307 LED40/740 II DM 48/60S	Not applicable
910925864576	BGP307 LED45/740 II DM 48/60S	Not applicable
910925864577	BGP307 LED54/740 II DM 48/60S	Not applicable
910925864578	BGP307 LED69/740 II DM 48/60S	Not applicable
910925864579	BGP307 LED84/740 II DM 48/60S	Not applicable
910925864580	BGP307 LED99/740 II DM 48/60S	Not applicable
910925864581	BGP307 LED109/740 II DM 48/60S	Not applicable
910925865375	BGP307 LED18/830 II DM11 C10	0% (digital)
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	0% (digital)
910925865378	BGP307 LED54/740 II DM11 C10	0% (digital)
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)

Order Code	Full Product Name	Maximum dim level
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	0% (digital)
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	0% (digital)
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Not applicable
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Not applicable
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	Not applicable
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	Not applicable
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	Not applicable
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	Not applicable
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	Not applicable
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	Not applicable
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	Not applicable
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	Not applicable
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	Not applicable
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	Not applicable
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	Not applicable
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	Not applicable
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	Not applicable
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	Not applicable
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	Not applicable
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	Not applicable
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	Not applicable
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	Not applicable
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	Not applicable
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	Not applicable
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	Not applicable
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	Not applicable
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	Not applicable
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	Not applicable
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	0% (digital)
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	0% (digital)
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	Not applicable
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	Not applicable
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	Not applicable
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	Not applicable
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	0% (digital)
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	0% (digital)
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	0% (digital)
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	0% (digital)
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	0% (digital)
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	0% (digital)
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	0% (digital)
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	0% (digital)
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	0% (digital)

Order Code	Full Product Name	Maximum dim level
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	0% (digital)
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	0% (digital)
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	0% (digital)
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865405	BGP307 LED69/740 II DM11 C10	0% (digital)
910925865406	BGP307 LED84/740 II DM11 C10	0% (digital)
910925865407	BGP307 LED99/740 II DM11 C10	0% (digital)
910925865408	BGP307 LED109/740 II DM11 C10	0% (digital)

Order Code	Full Product Name	Maximum dim level
910925865409	BGP307 LED120/740 II DM11 C10	0% (digital)
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	0% (digital)
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	0% (digital)
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	0% (digital)
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	0% (digital)
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	0% (digital)
910925865690	BGP307 LED18/830 II DM11 SR C10	0% (digital)
910925865691	BGP307 LED54/830 II DM11 SRT C10	0% (digital)
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	0% (digital)
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	0% (digital)
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	0% (digital)
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	0% (digital)
910925865696	BGP307 LED18/740 II DM11 SR C10	0% (digital)
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	0% (digital)
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	0% (digital)
910925865699	BGP307 LED69/740 II DM11 SR C10	0% (digital)
910925865701	BGP307 LED84/740 II DM11 SR C10	0% (digital)
910925865702	BGP307 LED99/740 II DM11 SR C10	0% (digital)
910925865703	BGP307 LED109/740 II DM11 SR C10	0% (digital)
910925865704	BGP307 LED120/740 II DM11 SR C10	0% (digital)
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	0% (digital)
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	0% (digital)
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	0% (digital)
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	0% (digital)
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	0% (digital)
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	0% (digital)
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	0% (digital)
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	0% (digital)
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	0% (digital)
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	0% (digital)
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	0% (digital)
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	0% (digital)

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925864560	BGP307 LED25/740 I DM 48/60S	Philips standard surge protection level
910925864561	BGP307 LED30/740 I DM 48/60S	Philips standard surge protection level
910925864562	BGP307 LED35/740 I DM 48/60S	Philips standard surge protection level
910925864563	BGP307 LED40/740 I DM 48/60S	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925864564	BGP307 LED45/740 I DM 48/60S	Philips standard surge protection level
910925864565	BGP307 LED54/740 I DM 48/60S	Philips standard surge protection level
910925864566	BGP307 LED69/740 I DM 48/60S	Philips standard surge protection level
910925864567	BGP307 LED84/740 I DM 48/60S	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925864568	BGP307 LED99/740 I DM 48/60S	Philips standard surge protection level
910925864569	BGP307 LED109/740 I DM 48/60S	Philips standard surge protection level
910925864572	BGP307 LED25/740 II DM 48/60S	Philips standard surge protection level
910925864573	BGP307 LED30/740 II DM 48/60S	Philips standard surge protection level
910925864574	BGP307 LED35/740 II DM 48/60S	Philips standard surge protection level
910925864575	BGP307 LED40/740 II DM 48/60S	Philips standard surge protection level
910925864576	BGP307 LED45/740 II DM 48/60S	Philips standard surge protection level
910925864577	BGP307 LED54/740 II DM 48/60S	Philips standard surge protection level
910925864578	BGP307 LED69/740 II DM 48/60S	Philips standard surge protection level
910925864579	BGP307 LED84/740 II DM 48/60S	Philips standard surge protection level
910925864580	BGP307 LED99/740 II DM 48/60S	Philips standard surge protection level
910925864581	BGP307 LED109/740 II DM 48/60S	Philips standard surge protection level
910925865375	BGP307 LED18/830 II DM11 C10	Philips standard surge protection level
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05ZIZI-	Philips standard surge protection level
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05ZIZI-	Philips standard surge protection level
910925865378	BGP307 LED54/740 II DM11 C10	Philips standard surge protection level
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05ZIZI-	Philips standard surge protection level
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05ZIZI-	Philips standard surge protection level
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05ZIZI-	Philips standard surge protection level
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Philips standard surge protection level
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05ZIZI-	Philips standard surge protection level
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	Philips standard surge protection level
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	Philips standard surge protection level



Order Code	Full Product Name	Surge Protection (Common/Differential)
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	Philips standard surge protection level
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	Philips standard surge protection level
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	Philips standard surge protection level
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Philips standard surge protection level
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Philips standard surge protection level
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Philips standard surge protection level
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Philips standard surge protection level
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Philips standard surge protection level
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Philips standard surge protection level
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	Philips standard surge protection level
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	Philips standard surge protection level
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	Philips standard surge protection level
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	Philips standard surge protection level
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Philips standard surge protection level
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Philips standard surge protection level
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Philips standard surge protection level
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Philips standard surge protection level
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Philips standard surge protection level
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Philips standard surge protection level
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	Philips standard surge protection level
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	Philips standard surge protection level
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	Philips standard surge protection level
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	Philips standard surge protection level
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	Philips standard surge protection level
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level



Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	Philips standard surge protection level
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Philips standard surge protection level
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Philips standard surge protection level
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865405	BGP307 LED69/740 II DM11 C10	Philips standard surge protection level
910925865406	BGP307 LED84/740 II DM11 C10	Philips standard surge protection level
910925865407	BGP307 LED99/740 II DM11 C10	Philips standard surge protection level
910925865408	BGP307 LED109/740 II DM11 C10	Philips standard surge protection level
910925865409	BGP307 LED120/740 II DM11 C10	Philips standard surge protection level
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Philips standard surge protection level
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Philips standard surge protection level
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Philips standard surge protection level
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Philips standard surge protection level
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Philips standard surge protection level
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865690	BGP307 LED18/830 II DM11 SR C10	Philips standard surge protection level
910925865691	BGP307 LED54/830 II DM11 SRT C10	Philips standard surge protection level
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Philips standard surge protection level
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865696	BGP307 LED18/740 II DM11 SR C10	Philips standard surge protection level
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Philips standard surge protection level
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865699	BGP307 LED69/740 II DM11 SR C10	Philips standard surge protection level
910925865701	BGP307 LED84/740 II DM11 SR C10	Philips standard surge protection level
910925865702	BGP307 LED99/740 II DM11 SR C10	Philips standard surge protection level
910925865703	BGP307 LED109/740 II DM11 SR C10	Philips standard surge protection level
910925865704	BGP307 LED120/740 II DM11 SR C10	Philips standard surge protection level
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Philips standard surge protection level

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Philips standard surge protection level
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Philips standard surge protection level
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Philips standard surge protection level
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Philips standard surge protection level
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Philips standard surge protection level
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Philips standard surge protection level
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Philips standard surge protection level

## Controls and Dimming

Order Code	Full Product Name	Dimmable
910925864560	BGP307 LED25/740 I DM 48/60S	No
910925864561	BGP307 LED30/740 I DM 48/60S	No
910925864562	BGP307 LED35/740 I DM 48/60S	No
910925864563	BGP307 LED40/740 I DM 48/60S	No
910925864564	BGP307 LED45/740 I DM 48/60S	No
910925864565	BGP307 LED54/740 I DM 48/60S	No
910925864566	BGP307 LED69/740 I DM 48/60S	No
910925864567	BGP307 LED84/740 I DM 48/60S	No
910925864568	BGP307 LED99/740 I DM 48/60S	No
910925864569	BGP307 LED109/740 I DM 48/60S	No
910925864572	BGP307 LED25/740 II DM 48/60S	No
910925864573	BGP307 LED30/740 II DM 48/60S	No
910925864574	BGP307 LED35/740 II DM 48/60S	No
910925864575	BGP307 LED40/740 II DM 48/60S	No
910925864576	BGP307 LED45/740 II DM 48/60S	No
910925864577	BGP307 LED54/740 II DM 48/60S	No
910925864578	BGP307 LED69/740 II DM 48/60S	No
910925864579	BGP307 LED84/740 II DM 48/60S	No
910925864580	BGP307 LED99/740 II DM 48/60S	No
910925864581	BGP307 LED109/740 II DM 48/60S	No
910925865375	BGP307 LED18/830 II DM11 C10	Yes
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	Yes
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	Yes
910925865378	BGP307 LED54/740 II DM11 C10	Yes
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes

Order Code	Full Product Name	Dimmable
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Yes
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	Yes
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	No
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Yes
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	No
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	No
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	No
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	No
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	No
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	No
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	No

Order Code	Full Product Name	Dimmable
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	No
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	No
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	No
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	No
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	No
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	No
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	No
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	No
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	No
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	No
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	No
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	No
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	No
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	No
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	No
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	No
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	No
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Yes
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Yes
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Yes
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Yes
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Yes
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Yes
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	No
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	No
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	No
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	No
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Yes
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Yes
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Yes
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Yes
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Yes
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Yes
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Yes
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	Yes
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	Yes
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	Yes
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	Yes
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	Yes
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Yes
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Yes
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	Yes
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	Yes
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Yes

Order Code	Full Product Name	Dimmable
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	Yes
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Yes
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	Yes
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	Yes
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Yes
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	Yes
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	Yes
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865405	BGP307 LED69/740 II DM11 C10	Yes
910925865406	BGP307 LED84/740 II DM11 C10	Yes
910925865407	BGP307 LED99/740 II DM11 C10	Yes
910925865408	BGP307 LED109/740 II DM11 C10	Yes
910925865409	BGP307 LED120/740 II DM11 C10	Yes
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Yes
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Yes
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Yes
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Yes
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Yes
910925865690	BGP307 LED18/830 II DM11 SR C10	Yes

Order Code	Full Product Name	Dimmable
910925865691	BGP307 LED54/830 II DM11 SRT C10	Yes
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Yes
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Yes
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Yes
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Yes
910925865696	BGP307 LED18/740 II DM11 SR C10	Yes
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Yes
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Yes
910925865699	BGP307 LED69/740 II DM11 SR C10	Yes
910925865701	BGP307 LED84/740 II DM11 SR C10	Yes
910925865702	BGP307 LED99/740 II DM11 SR C10	Yes
910925865703	BGP307 LED109/740 II DM11 SR C10	Yes
910925865704	BGP307 LED120/740 II DM11 SR C10	Yes

Order Code	Full Product Name	Dimmable
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Yes
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Yes
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Yes
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Yes
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Yes
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Yes
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Yes
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Yes
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Yes
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Yes
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Yes
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Yes

## General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light	Lamp	Lamp version
			source color	family code	
910925864560	BGP307 LED25/740 I DM 48/60S	42° x 44°	740 neutral white	LED25	-
910925864561	BGP307 LED30/740 I DM 48/60S	42° x 44°	740 neutral white	LED30	-
910925864562	BGP307 LED35/740 I DM 48/60S	42° x 44°	740 neutral white	LED35	-
910925864563	BGP307 LED40/740 I DM 48/60S	42° x 44°	740 neutral white	LED40	-
910925864564	BGP307 LED45/740 I DM 48/60S	42° x 44°	740 neutral white	LED45	-
910925864565	BGP307 LED54/740 I DM 48/60S	42° x 44°	740 neutral white	LED54	-
910925864566	BGP307 LED69/740 I DM 48/60S	42° x 44°	740 neutral white	LED69	-
910925864567	BGP307 LED84/740 I DM 48/60S	42° x 44°	740 neutral white	LED84	-
910925864568	BGP307 LED99/740 I DM 48/60S	42° x 44°	740 neutral white	LED99	-
910925864569	BGP307 LED109/740 I DM 48/60S	42° x 44°	740 neutral white	LED109	-
910925864572	BGP307 LED25/740 II DM 48/60S	42° x 44°	740 neutral white	LED25	-

Order Code	Full Product Name	Luminaire light beam spread	Light	Lamp	Lamp version
			source color	family code	
910925864573	BGP307 LED30/740 II DM 48/60S	42° x 44°	740 neutral white	LED30	-
910925864574	BGP307 LED35/740 II DM 48/60S	42° x 44°	740 neutral white	LED35	-
910925864575	BGP307 LED40/740 II DM 48/60S	42° x 44°	740 neutral white	LED40	-
910925864576	BGP307 LED45/740 II DM 48/60S	42° x 44°	740 neutral white	LED45	-
910925864577	BGP307 LED54/740 II DM 48/60S	42° x 44°	740 neutral white	LED54	-
910925864578	BGP307 LED69/740 II DM 48/60S	42° x 44°	740 neutral white	LED69	-
910925864579	BGP307 LED84/740 II DM 48/60S	42° x 44°	740 neutral white	LED84	-
910925864580	BGP307 LED99/740 II DM 48/60S	42° x 44°	740 neutral white	LED99	-
910925864581	BGP307 LED109/740 II DM 48/60S	42° x 44°	740 neutral white	LED109	-
910925865375	BGP307 LED18/830 II DM11 C10	160° - 42° x 54°	830 warm white	LED18	-
910925865376	BGP307 LED35-45/830 II DM11 CLO S05Z1Z1-	160° - 42° x 54°	830 warm white	LED35	-

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05ZIZI-	160° - 42° x 54°	830 warm white	LED45	-
910925865378	BGP307 LED54/740 II DM11 C10	160° - 42° x 54°	830 warm white	LED54	-
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED18	-
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED25	-
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED35	-
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED45	-
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED54	-
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED18	-
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED25	-
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED35	-
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED45	-
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED54	4S
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED18	-
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED25	-
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED35	-

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	160° - 42° x 54°	740 neutral white	LED45	-
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05ZIZI-	160° - 42° x 54°	740 neutral white	LED54	-
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED18	-
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED25	-
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED54	4S
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	160° - 42° x 54°	740 neutral white	LED130	4S
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED18	-
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED25	-
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED30	-
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED35	-
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED40	-
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED45	-
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED54	-
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED69	-
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED84	-
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED99	-

## ClearWay gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED109	-
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	154° - 31° x 54°	740 neutral white	LED120	-
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED18	-
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED25	-
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED30	-
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED35	-
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED40	4S
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	154° - 31° x 54°	740 neutral white	LED45	-
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED54	-
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED69	-
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED84	-
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED99	-
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED109	-
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	154° - 31° x 54°	740 neutral white	LED120	-
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	740 neutral white	LED18S	-
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	740 neutral white	LED30S	-

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	740 neutral white	LED35S	-
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	740 neutral white	LED54S	-
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	154° - 31° x 54°	740 neutral white	LED69S	-
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	154° - 31° x 54°	740 neutral white	LED120S	-
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	160° - 42° x 54°	740 neutral white	LED18	-
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	160° - 42° x 54°	740 neutral white	LED35	-
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	160° - 42° x 54°	740 neutral white	LED69	-
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	160° - 42° x 54°	740 neutral white	LED120	-
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	160° - 42° x 54°	830 warm white	LED25	-
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	830 warm white	LED25	-
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	830 warm white	LED25	-
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	160° - 42° x 54°	740 neutral white	LED25	-
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED25	-
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED54	-
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED25	-

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	LED18	-
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	LED25	-
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	LED35	-
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	LED45	-
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	160° - 42° x 54°	830 warm white	LED54	-
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED18	-
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED25	-
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED35	-
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED45	-
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	160° - 42° x 54°	830 warm white	LED54	-
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED18	-
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED25	-
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED35	-
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED45	-
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	160° - 42° x 54°	830 warm white	LED54	-

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED18	-
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED25	-
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED35	-
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED45	-
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED54	-
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED18	-
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED25	-
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED35	-
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED45	-
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED54	-
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED18	-
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED25	-
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED35	-
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED45	-
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED54	-



## ClearWay gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED69	-
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED84	-
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED99	-
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED109	-
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	160° - 42° x 54°	740 neutral white	LED120	-
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED69	-
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED84	-
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED99	-
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED109	-
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED120	-
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED69	-
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED84	-
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED99	-
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	740 neutral white	LED109	-
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	740 neutral white	LED120	-

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED35	-
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED45	-
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED54	-
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED18	-
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED25	-
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED35	-
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED45	-
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED54	-
910925865405	BGP307 LED69/740 II DM11 C10	160° - 42° x 54°	740 neutral white	LED69	-
910925865406	BGP307 LED84/740 II DM11 C10	160° - 42° x 54°	740 neutral white	LED84	-
910925865407	BGP307 LED99/740 II DM11 C10	160° - 42° x 54°	740 neutral white	LED99	-
910925865408	BGP307 LED109/740 II DM11 C10	160° - 42° x 54°	740 neutral white	LED109	-
910925865409	BGP307 LED120/740 II DM11 C10	160° - 42° x 54°	740 neutral white	LED120	-
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED69	-
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED84	-

## ClearWay gen2

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	160° - 42° x 54°	740 neutral white	LED99	-
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED109	-
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	160° - 42° x 54°	740 neutral white	LED120	-
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED69	-
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED84	-
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	160° - 42° x 54°	740 neutral white	LED99	-
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	740 neutral white	LED109	-
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	160° - 42° x 54°	740 neutral white	LED120	-
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED54	-
910925865690	BGP307 LED18/830 II DM11 SR C10	160° - 42° x 54°	830 warm white	LED18	-
910925865691	BGP307 LED54/830 II DM11 SRT C10	160° - 42° x 54°	830 warm white	LED54	-
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	160° - 42° x 54°	830 warm white	LED18	-
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	160° - 42° x 54°	830 warm white	LED54	-
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	160° - 42° x 54°	830 warm white	LED18	-
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	160° - 42° x 54°	830 warm white	LED54	-
910925865696	BGP307 LED18/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	LED18	-
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED18	-
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED18	-

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Lamp version
910925865699	BGP307 LED69/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	LED69	-
910925865701	BGP307 LED84/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	LED84	-
910925865702	BGP307 LED99/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	LED99	-
910925865703	BGP307 LED109/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	LED109	-
910925865704	BGP307 LED120/740 II DM11 SR C10	160° - 42° x 54°	740 neutral white	LED120	-
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED69	-
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED84	-
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED99	-
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED109	-
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	160° - 42° x 54°	740 neutral white	LED120	-
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED69	-
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED84	-
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED99	-
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED109	-
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	160° - 42° x 54°	740 neutral white	LED120	-
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	160° - 42° x 54°	830 warm white	LED35	-
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	160° - 42° x 54°	740 neutral white	LED45	-

General Information (2/2)

Order Code	Full Product Name	Optic type
910925864560	BGP307 LED25/740 I DM 48/60S	Distribution medium
910925864561	BGP307 LED30/740 I DM 48/60S	Distribution medium
910925864562	BGP307 LED35/740 I DM 48/60S	Distribution medium
910925864563	BGP307 LED40/740 I DM 48/60S	Distribution medium
910925864564	BGP307 LED45/740 I DM 48/60S	Distribution medium
910925864565	BGP307 LED54/740 I DM 48/60S	Distribution medium
910925864566	BGP307 LED69/740 I DM 48/60S	Distribution medium
910925864567	BGP307 LED84/740 I DM 48/60S	Distribution medium
910925864568	BGP307 LED99/740 I DM 48/60S	Distribution medium
910925864569	BGP307 LED109/740 I DM 48/60S	Distribution medium
910925864572	BGP307 LED25/740 II DM 48/60S	Distribution medium
910925864573	BGP307 LED30/740 II DM 48/60S	Distribution medium
910925864574	BGP307 LED35/740 II DM 48/60S	Distribution medium
910925864575	BGP307 LED40/740 II DM 48/60S	Distribution medium
910925864576	BGP307 LED45/740 II DM 48/60S	Distribution medium
910925864577	BGP307 LED54/740 II DM 48/60S	Distribution medium
910925864578	BGP307 LED69/740 II DM 48/60S	Distribution medium
910925864579	BGP307 LED84/740 II DM 48/60S	Distribution medium
910925864580	BGP307 LED99/740 II DM 48/60S	Distribution medium
910925864581	BGP307 LED109/740 II DM 48/60S	Distribution medium
910925865375	BGP307 LED18/830 II DM11 C10	Distribution medium 11
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	Distribution medium 11
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	Distribution medium 11
910925865378	BGP307 LED54/740 II DM11 C10	Distribution medium 11
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	Distribution medium 11
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	Distribution medium 11
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	Distribution medium 11
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	Distribution medium 11
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	Distribution medium 11
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	Distribution medium 11
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	Distribution medium 50
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	Distribution medium 50
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	Distribution medium 50
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	Distribution medium 50

Order Code	Full Product Name	Optic type
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	Distribution medium 50
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	Distribution medium 50
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	Distribution medium 50
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	Distribution medium 50
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	Distribution medium 50
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	Distribution medium 50
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	Distribution medium 50
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	Distribution medium 50
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	Distribution medium 50
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	Distribution medium 50
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	Distribution medium 50
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	Distribution medium 50
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	Distribution medium 50
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	Distribution medium 50
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	Distribution medium 50
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	Distribution medium 50
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	Distribution medium 50
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	Distribution medium 50
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	Distribution medium 50
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	Distribution medium 50
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	Distribution medium 50
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	Distribution medium 50
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	Distribution medium 50
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	Distribution medium 50
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	Distribution medium 50
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	Distribution medium 50
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	Distribution medium 11
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	Distribution medium 11
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	Distribution medium 11
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	Distribution medium 11
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	Distribution medium 11
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	Distribution medium 11
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	Distribution medium 11
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	Distribution medium 11
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	Distribution medium 11
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	Distribution medium 11
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	Distribution medium 11
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	Distribution medium 11
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	Distribution medium 11
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	Distribution medium 11
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	Distribution medium 11
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	Distribution medium 11
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11

Order Code	Full Product Name	Optic type
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	Distribution medium 11
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Distribution medium 11
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Distribution medium 11
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11

Order Code	Full Product Name	Optic type
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865405	BGP307 LED69/740 II DM11 C10	Distribution medium 11
910925865406	BGP307 LED84/740 II DM11 C10	Distribution medium 11
910925865407	BGP307 LED99/740 II DM11 C10	Distribution medium 11
910925865408	BGP307 LED109/740 II DM11 C10	Distribution medium 11
910925865409	BGP307 LED120/740 II DM11 C10	Distribution medium 11
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	Distribution medium 11
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	Distribution medium 11
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	Distribution medium 11
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	Distribution medium 11
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	Distribution medium 11
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	Distribution medium 11
910925865690	BGP307 LED18/830 II DM11 SR C10	Distribution medium 11
910925865691	BGP307 LED54/830 II DM11 SRT C10	Distribution medium 11
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	Distribution medium 11
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	Distribution medium 11
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	Distribution medium 11
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	Distribution medium 11
910925865696	BGP307 LED18/740 II DM11 SR C10	Distribution medium 11
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	Distribution medium 11
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	Distribution medium 11
910925865699	BGP307 LED69/740 II DM11 SR C10	Distribution medium 11
910925865701	BGP307 LED84/740 II DM11 SR C10	Distribution medium 11
910925865702	BGP307 LED99/740 II DM11 SR C10	Distribution medium 11
910925865703	BGP307 LED109/740 II DM11 SR C10	Distribution medium 11
910925865704	BGP307 LED120/740 II DM11 SR C10	Distribution medium 11
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	Distribution medium 11
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	Distribution medium 11
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	Distribution medium 11
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	Distribution medium 11
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	Distribution medium 11
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	Distribution medium 11
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	Distribution medium 11
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	Distribution medium 11
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	Distribution medium 11
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	Distribution medium 11
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	Distribution medium 11
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	Distribution medium 11

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925864560	BGP307 LED25/740 I DM 48/60S	4000 K	70	2250 lm
910925864561	BGP307 LED30/740 I DM 48/60S	4000 K	70	2700 lm
910925864562	BGP307 LED35/740 I DM 48/60S	4000 K	70	3150 lm
910925864563	BGP307 LED40/740 I DM 48/60S	4000 K	70	3600 lm
910925864564	BGP307 LED45/740 I DM 48/60S	4000 K	70	3960 lm
910925864565	BGP307 LED54/740 I DM 48/60S	4000 K	70	4680 lm
910925864566	BGP307 LED69/740 I DM 48/60S	4000 K	70	5760 lm
910925864567	BGP307 LED84/740 I DM 48/60S	4000 K	70	7200 lm
910925864568	BGP307 LED99/740 I DM 48/60S	4000 K	70	8460 lm
910925864569	BGP307 LED109/740 I DM 48/60S	4000 K	70	9000 lm
910925864572	BGP307 LED25/740 II DM 48/60S	4000 K	70	2250 lm
910925864573	BGP307 LED30/740 II DM 48/60S	4000 K	70	2700 lm
910925864574	BGP307 LED35/740 II DM 48/60S	4000 K	70	3150 lm
910925864575	BGP307 LED40/740 II DM 48/60S	4000 K	70	3600 lm
910925864576	BGP307 LED45/740 II DM 48/60S	4000 K	70	3960 lm
910925864577	BGP307 LED54/740 II DM 48/60S	4000 K	70	4680 lm
910925864578	BGP307 LED69/740 II DM 48/60S	4000 K	70	5760 lm
910925864579	BGP307 LED84/740 II DM 48/60S	4000 K	70	7200 lm
910925864580	BGP307 LED99/740 II DM 48/60S	4000 K	70	8460 lm
910925864581	BGP307 LED109/740 II DM 48/60S	4000 K	70	9000 lm
910925865375	BGP307 LED18/830 II DM11 C10	3000 K	80	1496 lm
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	2904 lm
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05ZIZI-	3000 K	80	3654 lm
910925865378	BGP307 LED54/740 II DM11 C10	4000 K	70	4350 lm
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	1496 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2001 lm
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2904 lm
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3654 lm
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	4400 lm
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	1496 lm
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2001 lm
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2904 lm
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	3654 lm
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	4400 lm
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	1496 lm
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	2024 lm
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	2904 lm
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	4000 K	70	3696 lm
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05ZIZI-	4000 K	70	4350 lm
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	1496 lm
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2024 lm
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4000 K	70	4350 lm
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	4000 K	70	10924 lm
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	4000 K	70	1584 lm
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	4000 K	70	2175 lm
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	4000 K	70	2610 lm
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	4000 K	70	3080 lm
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	4000 K	70	3520 lm
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	4000 K	70	3960 lm
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	4000 K	70	4698 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	4000 K	70	6160 lm
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	4000 K	70	7308 lm
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	4000 K	70	8600 lm
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	4000 K	70	9460 lm
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	4000 K	70	10200 lm
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	4000 K	70	1584 lm
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	4000 K	70	2175 lm
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	4000 K	70	2610 lm
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	4000 K	70	3080 lm
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	4000 K	70	3520 lm
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	4000 K	70	3960 lm
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	4000 K	70	4698 lm
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	4000 K	70	6160 lm
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	4000 K	70	7308 lm
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	4000 K	70	8600 lm
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	4000 K	70	9460 lm
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	4000 K	70	10200 lm
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	4000 K	70	1584 lm
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	4000 K	70	2610 lm
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	4000 K	70	3080 lm
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	4000 K	70	4698 lm
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	4000 K	70	6160 lm
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	4000 K	70	10200 lm
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	4000 K	70	1584 lm
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	4000 K	70	3080 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	4000 K	70	6160 lm
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	4000 K	70	10200 lm
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	3000 K	80	2001 lm
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	3000 K	80	2001 lm
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	3000 K	80	2001 lm
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	4000 K	70	2024 lm
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	4000 K	70	2024 lm
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	4000 K	70	4350 lm
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	4000 K	70	2024 lm
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	3000 K	80	1496 lm
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	3000 K	80	2001 lm
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	3000 K	80	2904 lm
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	3000 K	80	3654 lm
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	3000 K	80	4400 lm
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	1496 lm
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2001 lm
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	2904 lm
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	3654 lm
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	3000 K	80	4400 lm
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	1496 lm
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2001 lm
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	2904 lm
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	3654 lm
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	3000 K	80	4400 lm
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	4000 K	70	1496 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	4000 K	70	2024 lm
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	4000 K	70	2904 lm
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	4000 K	70	3696 lm
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	4000 K	70	4350 lm
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	1496 lm
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2024 lm
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2904 lm
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3696 lm
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	4350 lm
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	1496 lm
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2024 lm
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2904 lm
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	3696 lm
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	4350 lm
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	4000 K	70	5632 lm
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	4000 K	70	6786 lm
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	4000 K	70	7830 lm
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	4000 K	70	8428 lm
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	4000 K	70	9030 lm
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5632 lm
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	6786 lm
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	7830 lm
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	8428 lm
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	9030 lm
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	5632 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	6786 lm
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	7830 lm
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	8428 lm
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	9030 lm
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	2904 lm
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	3696 lm
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	4350 lm
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	1496 lm
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2024 lm
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	2904 lm
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	3696 lm
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	4350 lm
910925865405	BGP307 LED69/740 II DM11 C10	4000 K	70	5632 lm
910925865406	BGP307 LED84/740 II DM11 C10	4000 K	70	6786 lm
910925865407	BGP307 LED99/740 II DM11 C10	4000 K	70	7830 lm
910925865408	BGP307 LED109/740 II DM11 C10	4000 K	70	8428 lm
910925865409	BGP307 LED120/740 II DM11 C10	4000 K	70	9030 lm
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	5632 lm
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	6786 lm
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	4000 K	70	7830 lm
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	8428 lm
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	4000 K	70	9030 lm
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	5632 lm
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	6786 lm
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	4000 K	70	7830 lm



Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	8428 lm
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	4000 K	70	9030 lm
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	4000 K	70	4350 lm
910925865690	BGP307 LED18/830 II DM11 SR C10	3000 K	80	1496 lm
910925865691	BGP307 LED54/830 II DM11 SRT C10	3000 K	80	4400 lm
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	3000 K	80	1496 lm
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	3000 K	80	4400 lm
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	3000 K	80	1496 lm
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	3000 K	80	4400 lm
910925865696	BGP307 LED18/740 II DM11 SR C10	4000 K	70	1496 lm
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	4000 K	70	1496 lm
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	4000 K	70	1496 lm
910925865699	BGP307 LED69/740 II DM11 SR C10	4000 K	70	5632 lm
910925865701	BGP307 LED84/740 II DM11 SR C10	4000 K	70	6786 lm
910925865702	BGP307 LED99/740 II DM11 SR C10	4000 K	70	7830 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865703	BGP307 LED109/740 II DM11 SR C10	4000 K	70	8428 lm
910925865704	BGP307 LED120/740 II DM11 SR C10	4000 K	70	9030 lm
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	4000 K	70	5632 lm
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	4000 K	70	6786 lm
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	4000 K	70	7830 lm
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	4000 K	70	8428 lm
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	4000 K	70	9030 lm
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	4000 K	70	5632 lm
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	4000 K	70	6786 lm
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	4000 K	70	7830 lm
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	4000 K	70	8428 lm
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	4000 K	70	9030 lm
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	3000 K	80	2904 lm
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	4000 K	70	3696 lm

Mechanical and Housing

Order Code	Full Product Name	Supply cable length	Color
910925864560	BGP307 LED25/740 I DM 48/60S	-	Gray
910925864561	BGP307 LED30/740 I DM 48/60S	-	Gray
910925864562	BGP307 LED35/740 I DM 48/60S	-	Gray
910925864563	BGP307 LED40/740 I DM 48/60S	-	Gray
910925864564	BGP307 LED45/740 I DM 48/60S	-	Gray
910925864565	BGP307 LED54/740 I DM 48/60S	-	Gray
910925864566	BGP307 LED69/740 I DM 48/60S	-	Gray
910925864567	BGP307 LED84/740 I DM 48/60S	-	Gray
910925864568	BGP307 LED99/740 I DM 48/60S	-	Gray
910925864569	BGP307 LED109/740 I DM 48/60S	-	Gray
910925864572	BGP307 LED25/740 II DM 48/60S	-	Gray
910925864573	BGP307 LED30/740 II DM 48/60S	-	Gray
910925864574	BGP307 LED35/740 II DM 48/60S	-	Gray
910925864575	BGP307 LED40/740 II DM 48/60S	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925864576	BGP307 LED45/740 II DM 48/60S	-	Gray
910925864577	BGP307 LED54/740 II DM 48/60S	-	Gray
910925864578	BGP307 LED69/740 II DM 48/60S	-	Gray
910925864579	BGP307 LED84/740 II DM 48/60S	-	Gray
910925864580	BGP307 LED99/740 II DM 48/60S	-	Gray
910925864581	BGP307 LED109/740 II DM 48/60S	-	Gray
910925865375	BGP307 LED18/830 II DM11 C10	-	Gray
910925865376	BGP307 LED35-4S/830 II DM11 CLO S05Z1Z1-	-	Gray
910925865377	BGP307 LED45-4S/830 II DM11 CLO S05Z1Z1-	-	Gray
910925865378	BGP307 LED54/740 II DM11 C10	-	Gray
910925865379	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865380	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925865381	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865382	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865383	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865384	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865385	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865386	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865387	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865388	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	10 m	Gray
910925865389	BGP307 LED18-4S/740 II DM11 CLO S05Z1Z1-	-	Gray
910925865390	BGP307 LED25-4S/740 II DM11 CLO S05Z1Z1-	-	Gray
910925865391	BGP307 LED35-4S/740 II DM11 CLO S05Z1Z1-	-	Gray
910925865392	BGP307 LED45-4S/740 II DM11 CLL CLO S05Z	-	Gray
910925865393	BGP307 LED54-4S/740 II DM11 CLO S05Z1Z1-	-	Gray
910925865394	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865395	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865549	BGP307 LED54-4S/740 II DM11 CLO 48/60S	-	Aluminum
910925865551	BGP307 LED130-4S/740 I DM11 DDF2 D18 48/	-	Aluminum
910925864583	BGP307 LED18-4S/740 I DM50 48/60S	-	Gray
910925864584	BGP307 LED25-4S/740 I DM50 48/60S	-	Gray
910925864585	BGP307 LED30-4S/740 I DM50 48/60S	-	Gray
910925864586	BGP307 LED35-4S/740 I DM50 48/60S	-	Gray
910925864587	BGP307 LED40-4S/740 I DM50 48/60S	-	Gray
910925864588	BGP307 LED45-4S/740 I DM50 48/60S	-	Gray
910925864589	BGP307 LED54-4S/740 I DM50 48/60S	-	Gray
910925864590	BGP307 LED69-4S/740 I DM50 48/60S	-	Gray
910925864591	BGP307 LED84-4S/740 I DM50 48/60S	-	Gray
910925864592	BGP307 LED99-4S/740 I DM50 48/60S	-	Gray
910925864593	BGP307 LED109-4S/740 I DM50 48/60S	-	Gray
910925864594	BGP307 LED120-4S/740 I DM50 48/60S	-	Gray
910925864595	BGP307 LED18-4S/740 II DM50 48/60S	-	Gray
910925864596	BGP307 LED25-4S/740 II DM50 48/60S	-	Gray
910925864597	BGP307 LED30-4S/740 II DM50 48/60S	-	Gray
910925864598	BGP307 LED35-4S/740 II DM50 48/60S	-	Gray
910925864599	BGP307 LED40-4S/740 II DM50 48/60S	-	Gray
910925864601	BGP307 LED45-4S/740 II DM50 48/60A	-	Gray
910925864602	BGP307 LED54-4S/740 II DM50 48/60S	-	Gray
910925864603	BGP307 LED69-4S/740 II DM50 48/60S	-	Gray
910925864604	BGP307 LED84-4S/740 II DM50 48/60S	-	Gray
910925864605	BGP307 LED99-4S/740 II DM50 48/60S	-	Gray
910925864606	BGP307 LED109-4S/740 II DM50 48/60S	-	Gray
910925864607	BGP307 LED120-4S/740 II DM50 48/60S	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925865129	BGP307 LED18-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865130	BGP307 LED30-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865131	BGP307 LED35-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865132	BGP307 LED54-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865133	BGP307 LED69-4S/740 I DM50 DDF27 D18 48/	-	Gray
910925865134	BGP307 LED120-4S/740 I DM50 DDF27 D18 48	-	Gray
910925865150	BGP307 LED18-4S/740 I DM11 48/76S	-	Gray
910925865151	BGP307 LED35-4S/740 I DM11 48/76S	-	Gray
910925865152	BGP307 LED69-4S/740 I DM11 48/76S	-	Gray
910925865153	BGP307 LED120-4S/740 I DM11 48/76S	-	Gray
910925865202	BGP307 LED25/830 II DM11 CLL SR C10	-	Gray
910925865203	BGP307 LED25/830 II DM11 CLL DDF1 SR C10	-	Gray
910925865204	BGP307 LED25/830 II DM11 CLL DDF2 SR C10	-	Gray
910925865205	BGP307 LED25/740 II DM11 CLL SR C10	-	Gray
910925865207	BGP307 LED25/740 II DM11 CLL DDF1 SR C10	-	Gray
910925865208	BGP307 LED54/740 II DM11 DDF1 SR C10	-	Gray
910925865209	BGP307 LED25/740 II DM11 CLL DDF2 SR C10	-	Gray
910925865210	BGP307 LED18-4S/830 II DM11 CLO 48/60S	-	Gray
910925865211	BGP307 LED25-4S/830 II DM11 CLO 48/60S	-	Gray
910925865212	BGP307 LED35-4S/830 II DM11 CLO 48/60S	-	Gray
910925865213	BGP307 LED45-4S/830 II DM11 CLO 48/60S	-	Gray
910925865214	BGP307 LED54-4S/830 II DM11 CLO 48/60S	-	Gray
910925865215	BGP307 LED18-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865216	BGP307 LED25-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865217	BGP307 LED35-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865218	BGP307 LED45-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865219	BGP307 LED54-4S/830 II DM11 CLO-DDF1 D18	-	Gray
910925865220	BGP307 LED18-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865221	BGP307 LED25-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865222	BGP307 LED35-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865223	BGP307 LED45-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865224	BGP307 LED54-4S/830 II DM11 CLO-DDF2 D18	-	Gray
910925865225	BGP307 LED18-4S/740 II DM11 CLO 48/60S	-	Gray
910925865226	BGP307 LED25-4S/740 II DM11 CLO 48/60S	-	Gray
910925865227	BGP307 LED35-4S/740 II DM11 CLO 48/60S	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925865228	BGP307 LED45-4S/740 II DM11 CLO 48/60S	-	Gray
910925865229	BGP307 LED54-4S/740 II DM11 CLO 48/60S	-	Gray
910925865230	BGP307 LED18-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865231	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865232	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865233	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865234	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865235	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865236	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865237	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865238	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865239	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865240	BGP307 LED69-4S/740 II DM11 CLO 48/60S	-	Gray
910925865241	BGP307 LED84-4S/740 II DM11 CLO 48/60S	-	Gray
910925865242	BGP307 LED99-4S/740 II DM11 CLO 48/60S	-	Gray
910925865243	BGP307 LED109-4S/740 II DM11 CLO 48/60S	-	Gray
910925865244	BGP307 LED120-4S/740 II DM11 CLO 48/60S	-	Gray
910925865245	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865246	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865247	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865248	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865249	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865250	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865251	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865252	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865253	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865254	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865396	BGP307 LED35-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865397	BGP307 LED45-4S/740 II DM11 CLO-DDF1 D18	-	Gray

Order Code	Full Product Name	Supply cable length	Color
910925865398	BGP307 LED54-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865399	BGP307 LED18-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865401	BGP307 LED25-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865402	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865403	BGP307 LED45-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865404	BGP307 LED54-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865405	BGP307 LED69/740 II DM11 C10	-	Gray
910925865406	BGP307 LED84/740 II DM11 C10	-	Gray
910925865407	BGP307 LED99/740 II DM11 C10	-	Gray
910925865408	BGP307 LED109/740 II DM11 C10	-	Gray
910925865409	BGP307 LED120/740 II DM11 C10	-	Gray
910925865410	BGP307 LED69-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865411	BGP307 LED84-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865412	BGP307 LED99-4S/740 II DM11 CLO-DDF1 D18	-	Gray
910925865413	BGP307 LED109-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865414	BGP307 LED120-4S/740 II DM11 CLO-DDF1 D1	-	Gray
910925865415	BGP307 LED69-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865416	BGP307 LED84-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865417	BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18	-	Gray
910925865418	BGP307 LED109-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865522	BGP307 LED120-4S/740 II DM11 CLO-DDF2 D1	-	Gray
910925865689	BGP307 LED54/740 II DM11 DDF2 SR C10	-	Gray
910925865690	BGP307 LED18/830 II DM11 SR C10	-	Gray
910925865691	BGP307 LED54/830 II DM11 SRT C10	-	Gray
910925865692	BGP307 LED18/830 II DM11 DDF1 SR C10	-	Gray
910925865693	BGP307 LED54/830 II DM11 DDF1 SRT C10	-	Gray
910925865694	BGP307 LED18/830 II DM11 DDF2 SR C10	-	Gray
910925865695	BGP307 LED54/830 II DM11 DDF2 SR C10	-	Gray
910925865696	BGP307 LED18/740 II DM11 SR C10	-	Gray
910925865697	BGP307 LED18/740 II DM11 DDF1 SR C10	-	Gray
910925865698	BGP307 LED18/740 II DM11 DDF2 SR C10	-	Gray
910925865699	BGP307 LED69/740 II DM11 SR C10	-	Gray
910925865701	BGP307 LED84/740 II DM11 SR C10	-	Gray
910925865702	BGP307 LED99/740 II DM11 SR C10	-	Gray
910925865703	BGP307 LED109/740 II DM11 SR C10	-	Gray

## ClearWay gen2

Order Code	Full Product Name	Supply cable	
		length	Color
910925865704	BGP307 LED120/740 II DM11 SR C10	-	Gray
910925865705	BGP307 LED69/740 II DM11 DDF1 SR C10	-	Gray
910925865706	BGP307 LED84/740 II DM11 DDF1 SR C10	-	Gray
910925865707	BGP307 LED99/740 II DM11 DDF1 SR C10	-	Gray
910925865708	BGP307 LED109/740 II DM11 DDF1 SR C10	-	Gray
910925865709	BGP307 LED120/740 II DM11 DDF1 SR C10	-	Gray
910925865710	BGP307 LED69/740 II DM11 DDF2 SR C10	-	Gray

Order Code	Full Product Name	Supply cable	
		length	Color
910925865711	BGP307 LED84/740 II DM11 DDF2 SR C10	-	Gray
910925865712	BGP307 LED99/740 II DM11 DDF2 SR C10	-	Gray
910925865713	BGP307 LED109/740 II DM11 DDF2 SR C10	-	Gray
910925865714	BGP307 LED120/740 II DM11 DDF2 SR C10	-	Gray
910925865715	BGP307 LED35/830 II DM11 CLL SR C10	-	Gray
910925865722	BGP307 LED45/740 II DM11 CLL SR C10	-	Gray

