



# MileWide<sup>2</sup> – design meets efficiency

## MileWide<sup>2</sup> Pole

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide<sup>2</sup>, the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide<sup>2</sup> integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide<sup>2</sup> is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

### Benefits

- Consistency and continuity of family design
- Complete solution with dedicated masts and brackets
- Discreet solution with clean lines radiating a strong character

### Features

- Dedicated total solution based on clean-design, high-finish MileWide family
- Two different shapes to match different integration styles
- Different heights available – suitable for a wide range of applications
- "Plug-and-play"

### Application

- Residential streets
- Walking, cycling and running paths
- Main roads
- Motorways
- Car parks

Versions



YHP435 PLS-EMB CUR 4000 RAL48



YHP435 PLS-EMB CUR 6000 RAL60



YHP435 PLS-FLG CUR 4000 RAL48



YHP435 PLS-FLG CUR 6000 RAL60



YHP435 PLT-EMB CUR 6000 RAL60 48



YHP435 PLT-FLG CUR 6000 RAL60 48



YRP435 PLS-EMB CONE 4000 RAL48



YRP435 PLS-FLG CONE 4000 RAL48



YRP435 PLT-EMB CONE 6000 RAL60 48



YRP435 PLT-EMB CONE 6000 RAL60 60





YRP435 PLT-FLG CONE 6000 RAL60 48











YRP435 PLT-FLG CONE 6000 RAL60 60

Dimensional drawing





## Dimensional drawing



# MileWide<sup>2</sup> Pole


## Dimensional drawing



## Product details



MileWide2\_Bend pole.tif



MileWide2\_Slend pole.tif

