



Less hassle, More savings

Essential SmartBright G2 LED Floodlight

Essential SmartBright G2 LED floodlight comes with a compact and sturdy design. It is light weight with die-cast aluminium housing and corrosion-proof powder coating, suitable for general outdoor application. High efficiency designed with latest LED technology, achieves substantial energy savings comparing to conventional floodlights.

Benefits

- Ideal replacement for conventional halogen floodlights with substantial energy savings
- Uniform and less glare light output
- Reliable quality and brand promise guarantee hassle free for outdoor application

Features

- CCT: 3000K/4000K/6500K
- Power: 10w/20w/30w/50w/70w
- ~80lm/w system efficacy
- 15Khrs lifetime
- Operating temperature: $-40^{\circ}\text{C} < \text{Ta} < 45^{\circ}\text{C}$
- Complies IEC60598, EMC standards

Application

- Amenity/Security/Landscape/Plaza square/Parking/Architectural lighting

Essential SmartBright G2 LED Floodlight

Versions



Application Conditions	
Maximum dim level	Not applicable
Approval and Application	
Mech. impact protection code	IK06
Controls and Dimming	
Dimmable	No
General Information	
Luminaire light beam spread	100°
CE mark	CE mark
Optical cover/lens type	Polycarbonate bowl/cover flat
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Optic type	Symmetrical wide beam
Initial Performance (IEC Compliant)	
Init. Colour Rendering Index	>80
Mechanical and Housing	
Colour	Black

General Information

Order Code	Full Product Name	Light source colour
911401613204	BVP131 LED8/WW 10W 100-240V WB	830 warm white
911401613404	BVP131 LED8/CW 10W 100-240V WB	865 cool daylight
911401613504	BVP132 LED16/WW 20W 100-240V WB	830 warm white
911401613704	BVP132 LED16/CW 20W 100-240V WB	865 cool daylight
911401613804	BVP133 LED24/WW 30W 100-240V WB	830 warm white
911401614004	BVP133 LED24/CW 30W 100-240V WB	865 cool daylight
911401614104	BVP135 LED40/WW 50W 100-240V WB	830 warm white
911401614304	BVP135 LED40/CW 50W 100-240V WB	865 cool daylight

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401613204	BVP131 LED8/WW 10W 100-240V WB	3000 K	800 lm
911401613404	BVP131 LED8/CW 10W 100-240V WB	6500 K	800 lm
911401613504	BVP132 LED16/WW 20W 100-240V WB	3000 K	1600 lm
911401613704	BVP132 LED16/CW 20W 100-240V WB	6500 K	1600 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401613804	BVP133 LED24/WW 30W 100-240V WB	3000 K	2400 lm
911401614004	BVP133 LED24/CW 30W 100-240V WB	6500 K	2400 lm
911401614104	BVP135 LED40/WW 50W 100-240V WB	3000 K	4000 lm
911401614304	BVP135 LED40/CW 50W 100-240V WB	6500 K	4000 lm

Essential SmartBright G2 LED Floodlight

