



The easy way to connected lighting

MasterConnect LEDtube InstantFit T8

Philips MasterConnect LEDtube InstantFit T8 lamp, which is Interact Ready, enables an easy upgrade to a connected lighting system without re-wiring the fixtures. The 2.4GHz mesh networking technology allows integration with a variety of control device, such as sensor and switch. It also offers secure and reliable communication towards the Interact IoT platform or verified third party systems. The result? Greater energy savings, various control possibilities and a more adaptable space!

Benefits

- More than 50% energy saving compared to fluorescent lamps
- Flexible lighting controls to maximize productivity and comfort
- Works seamlessly with Interact IoT platform

Features

- Quick upgrade from fluorescent lamps with existing electronic ballast
- Superior lighting performance over product lifetime
- Easy to setup and control with mobile app
- Reliable and secure wireless communication within 2.4GHz mesh network

Application

- Office, education, retail and healthcare
- Parking, industry and warehouse

MasterConnect LEDtube InstantFit T8

Versions



EasySmart IR Programming Tool 10/1

