



The easy way to connected lighting

MasterConnect LEDtube InstantFit T8

Philips MasterConnect LEDtube InstantFit T8 lamp, which is Interact Ready, enables an easy upgrade to a connected lighting system without re-wiring the fixtures. The 2.4GHz mesh networking technology allows integration with a variety of control device, such as sensor and switch. It also offers secure and reliable communication towards the Interact IoT platform or verified third party systems. The result? Greater energy savings, various control possibilities and a more adaptable space!

Benefits

- More than 50% energy saving compared to fluorescent lamps
- Flexible lighting controls to maximize productivity and comfort
- Works seamlessly with Interact IoT platform

Features

- Quick upgrade from fluorescent lamps with existing electronic ballast
- Superior lighting performance over 50,000 hours lifetime
- Easy to commission and (re-)configure
- Reliable and secure wireless communication within 2.4GHz mesh network

Application

- Office, education, retail and healthcare
- Parking, industry and warehouse

MasterConnect LEDtube InstantFit T8

Versions



G13



EasySmart IR Programming Tool 10/1





G13



G13

MasterConnect LEDtube InstantFit T8

Dimensional drawing



Product	D1	D2	B	A1	D
15T8 LED/24-3000 IF 6U EasySmart 1PK	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
15T8 LED/24-5000 IF 6U EasySmart 1PK	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
15T8 LED/24-3500 IF 6U EasySmart 1PK	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
15T8 LED/24-4000 IF 6U EasySmart 1PK	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
15T8/24-850/IF21-6U/MAScon IA 10/1	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
15T8/24-830/IF20-6U/MAScon IA 10/1	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
15T8/24-840/IF21-6U/MAScon IA 10/1	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
15T8/24-835/IF20-6U/MAScon IA 10/1	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm

Product	D1	D2	A1	A2	A3
8T8 LED/24-5000 IF EasySmart 1PK	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
8T8 LED/24-3500 IF EasySmart 1PK	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
8T8 LED/24-4000 IF EasySmart 1PK	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
8T8 LED/24-3000 IF EasySmart 1PK	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
8T8/24-830/IF11/MAScon IA 10/1	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
14T8/48-830/IF20/ MAScon IA 10/1	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm
8T8/24-835/IF11/MAScon IA 10/1	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
8T8/24-850/IF12/MAScon IA 10/1	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
8T8/24-840/IF12/MAScon IA 10/1	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm
14T8/48-835/IF20/ MAScon IA 10/1	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm
14T8/48-850/IF21/ MAScon IA 10/1	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm
14T8/48-840/IF21/ MAScon IA 10/1	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm
14T8/48-5000 IF 10/1 EasySmart	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm
14T8/48-3000 IF 10/1 EasySmart	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm
14T8/48-4000 IF 10/1 EasySmart	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm

MasterConnect LEDtube InstantFit T8

Dimensional drawing

Product	D1	D2	A1	A2	A3
14T8/48-3500 IF 10/1 EasySmart	25.7 mm	26.3 mm	1198 mm	1205 mm	1212 mm

Approval and Application

Order Code	Full Product Name	Energy Efficiency Label (EEL)
929001281104	14T8/48-3000 IF 10/1 EasySmart	Not applicable
929001281164	14T8/48-830/IF20/MAScon IA 10/1	Not applicable
929001281204	14T8/48-3500 IF 10/1 EasySmart	Not applicable
929001281264	14T8/48-835/IF20/MAScon IA 10/1	Not applicable
929001281304	14T8/48-4000 IF 10/1 EasySmart	Not applicable
929001281364	14T8/48-840/IF21/MAScon IA 10/1	Not applicable
929001281404	14T8/48-5000 IF 10/1 EasySmart	Not applicable
929001281464	14T8/48-850/IF21/MAScon IA 10/1	Not applicable
929001390604	EasySmart IR Programming Tool 10/1	-
929001398004	15T8 LED/24-3000 IF 6U EasySmart 1PK	-
929001398064	15T8/24-830/IF20-6U/MAScon IA 10/1	-
929001398104	15T8 LED/24-3500 IF 6U EasySmart 1PK	-
929001398164	15T8/24-835/IF20-6U/MAScon IA 10/1	-

Order Code	Full Product Name	Energy Efficiency Label (EEL)
929001398204	15T8 LED/24-4000 IF 6U EasySmart 1PK	-
929001398264	15T8/24-840/IF21-6U/MAScon IA 10/1	-
929001398304	15T8 LED/24-5000 IF 6U EasySmart 1PK	-
929001398364	15T8/24-850/IF21-6U/MAScon IA 10/1	-
929001398404	8T8 LED/24-3000 IF EasySmart 1PK	-
929001398464	8T8/24-830/IF11/MAScon IA 10/1	-
929001398504	8T8 LED/24-3500 IF EasySmart 1PK	-
929001398564	8T8/24-835/IF11/MAScon IA 10/1	-
929001398604	8T8 LED/24-4000 IF EasySmart 1PK	-
929001398664	8T8/24-840/IF12/MAScon IA 10/1	-
929001398704	8T8 LED/24-5000 IF EasySmart 1PK	-
929001398764	8T8/24-850/IF12/MAScon IA 10/1	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001281104	14T8/48-3000 IF 10/1 EasySmart	Wireless Dim
929001281164	14T8/48-830/IF20/MAScon IA 10/1	Wireless Dim
929001281204	14T8/48-3500 IF 10/1 EasySmart	Wireless Dim
929001281264	14T8/48-835/IF20/MAScon IA 10/1	Wireless Dim
929001281304	14T8/48-4000 IF 10/1 EasySmart	Wireless Dim
929001281364	14T8/48-840/IF21/MAScon IA 10/1	Wireless Dim
929001281404	14T8/48-5000 IF 10/1 EasySmart	Wireless Dim
929001281464	14T8/48-850/IF21/MAScon IA 10/1	Wireless Dim
929001390604	EasySmart IR Programming Tool 10/1	-
929001398004	15T8 LED/24-3000 IF 6U EasySmart 1PK	Wireless Dim
929001398064	15T8/24-830/IF20-6U/MAScon IA 10/1	Wireless Dim
929001398104	15T8 LED/24-3500 IF 6U EasySmart 1PK	Wireless Dim
929001398164	15T8/24-835/IF20-6U/MAScon IA 10/1	Wireless Dim

Order Code	Full Product Name	Dimmable
929001398204	15T8 LED/24-4000 IF 6U EasySmart 1PK	Wireless Dim
929001398264	15T8/24-840/IF21-6U/MAScon IA 10/1	Wireless Dim
929001398304	15T8 LED/24-5000 IF 6U EasySmart 1PK	Wireless Dim
929001398364	15T8/24-850/IF21-6U/MAScon IA 10/1	Wireless Dim
929001398404	8T8 LED/24-3000 IF EasySmart 1PK	Wireless Dim
929001398464	8T8/24-830/IF11/MAScon IA 10/1	Wireless Dim
929001398504	8T8 LED/24-3500 IF EasySmart 1PK	Wireless Dim
929001398564	8T8/24-835/IF11/MAScon IA 10/1	Wireless Dim
929001398604	8T8 LED/24-4000 IF EasySmart 1PK	Wireless Dim
929001398664	8T8/24-840/IF12/MAScon IA 10/1	Wireless Dim
929001398704	8T8 LED/24-5000 IF EasySmart 1PK	Wireless Dim
929001398764	8T8/24-850/IF12/MAScon IA 10/1	Wireless Dim

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001281104	14T8/48-3000 IF 10/1 EasySmart	50 to 60 Hz	120-277, 347 V	14 W	0.5 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001281164	14T8/48-830/IF20/MAScon IA 10/1	50 to 60 Hz	120-277, 347 V	14 W	0.5 s

MasterConnect LEDtube InstantFit T8

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001281204	14T8/48-3500 IF 10/1 EasySmart	50 to 60 Hz	120-277, 347 V	14 W	0.5 s
929001281264	14T8/48-835/IF20/MAScon IA 10/1	50 to 60 Hz	120-277, 347 V	14 W	0.5 s
929001281304	14T8/48-4000 IF 10/1 EasySmart	50 to 60 Hz	120-277, 347 V	14 W	0.5 s
929001281364	14T8/48-840/IF21/MAScon IA 10/1	50 to 60 Hz	120-277, 347 V	14 W	0.5 s
929001281404	14T8/48-5000 IF 10/1 EasySmart	50 to 60 Hz	120-277, 347 V	14 W	0.5 s
929001281464	14T8/48-850/IF21/MAScon IA 10/1	50 to 60 Hz	120-277, 347 V	14 W	0.5 s
929001390604	EasySmart IR Programming Tool 10/1	-	-	1 W	-
929001398004	15T8 LED/24-3000 IF 6U EasySmart 1PK	40000-80000 Hz	160-380 V	15 W	0.5 s
929001398064	15T8/24-830/IF20-6U/MAScon IA 10/1	40000-80000 Hz	160-380 V	15 W	0.5 s
929001398104	15T8 LED/24-3500 IF 6U EasySmart 1PK	40000-80000 Hz	160-380 V	15 W	0.5 s
929001398164	15T8/24-835/IF20-6U/MAScon IA 10/1	40000-80000 Hz	160-380 V	15 W	0.5 s

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)	Starting Time (Nom)
929001398204	15T8 LED/24-4000 IF 6U EasySmart 1PK	40000-80000 Hz	160-380 V	15 W	0.5 s
929001398264	15T8/24-840/IF21-6U/MAScon IA 10/1	40000-80000 Hz	160-380 V	15 W	0.5 s
929001398304	15T8 LED/24-5000 IF 6U EasySmart 1PK	40000-80000 Hz	160-380 V	15 W	0.5 s
929001398364	15T8/24-850/IF21-6U/MAScon IA 10/1	40000-80000 Hz	160-380 V	15 W	0.5 s
929001398404	8T8 LED/24-3000 IF EasySmart 1PK	40000-85000 Hz	200-380 V	8 W	0.5 s
929001398464	8T8/24-830/IF11/MAScon IA 10/1	40000-85000 Hz	200-380 V	8 W	0.5 s
929001398504	8T8 LED/24-3500 IF EasySmart 1PK	40000-85000 Hz	200-380 V	8 W	0.5 s
929001398564	8T8/24-835/IF11/MAScon IA 10/1	40000-85000 Hz	200-380 V	8 W	0.5 s
929001398604	8T8 LED/24-4000 IF EasySmart 1PK	40000-85000 Hz	200-380 V	8 W	0.5 s
929001398664	8T8/24-840/IF12/MAScon IA 10/1	40000-85000 Hz	200-380 V	8 W	0.5 s
929001398704	8T8 LED/24-5000 IF EasySmart 1PK	40000-85000 Hz	200-380 V	8 W	0.5 s
929001398764	8T8/24-850/IF12/MAScon IA 10/1	40000-85000 Hz	200-380 V	8 W	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle
929001281104	14T8/48-3000 IF 10/1 EasySmart	G13	50000 h	50000 h	50000X
929001281164	14T8/48-830/IF20/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001281204	14T8/48-3500 IF 10/1 EasySmart	G13	50000 h	50000 h	50000X
929001281264	14T8/48-835/IF20/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001281304	14T8/48-4000 IF 10/1 EasySmart	G13	50000 h	50000 h	50000X
929001281364	14T8/48-840/IF21/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001281404	14T8/48-5000 IF 10/1 EasySmart	G13	50000 h	50000 h	50000X

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle
929001281464	14T8/48-850/IF21/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001390604	EasySmart IR Programming Tool 10/1	-	-	-	-
929001398004	15T8 LED/24-3000 IF 6U EasySmart 1PK	G13	50000 h	50000 h	50000X
929001398064	15T8/24-830/IF20-6U/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001398104	15T8 LED/24-3500 IF 6U EasySmart 1PK	G13	50000 h	50000 h	50000X
929001398164	15T8/24-835/IF20-6U/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001398204	15T8 LED/24-4000 IF 6U EasySmart 1PK	G13	50000 h	50000 h	50000X

MasterConnect LEDtube InstantFit T8

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle
929001398264	15T8/24-840/IF21-6U/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001398304	15T8 LED/24-5000 IF 6U EasySmart 1PK	G13	50000 h	50000 h	50000X
929001398364	15T8/24-850/IF21-6U/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001398404	8T8 LED/24-3000 IF EasySmart 1PK	G13	50000 h	50000 h	50000X
929001398464	8T8/24-830/IF11/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001398504	8T8 LED/24-3500 IF EasySmart 1PK	G13	50000 h	50000 h	50000X

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)	Rated Lifetime (Hours)	Switching Cycle
929001398564	8T8/24-835/IF11/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001398604	8T8 LED/24-4000 IF EasySmart 1PK	G13	50000 h	50000 h	50000X
929001398664	8T8/24-840/IF12/MAScon IA 10/1	G13	50000 h	50000 h	50000X
929001398704	8T8 LED/24-5000 IF EasySmart 1PK	G13	50000 h	50000 h	50000X
929001398764	8T8/24-850/IF12/MAScon IA 10/1	G13	50000 h	50000 h	50000X

Light Technical (1/2)

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color	Lmf At End Of		
					Rendering Index (Nom)	Nominal Lifetime (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001281104	14T8/48-3000 IF 10/1 EasySmart	-	830	3000 K	82	70 %	2000 lm	2000 lm
929001281164	14T8/48-830/IF20/MAScon IA 10/1	160 °	830	3000 K	82	70 %	2000 lm	2000 lm
929001281204	14T8/48-3500 IF 10/1 EasySmart	-	835	3500 K	82	70 %	2000 lm	2000 lm
929001281264	14T8/48-835/IF20/MAScon IA 10/1	160 °	835	3500 K	82	70 %	2000 lm	2000 lm
929001281304	14T8/48-4000 IF 10/1 EasySmart	-	840	4000 K	82	70 %	2100 lm	2100 lm
929001281364	14T8/48-840/IF21/MAScon IA 10/1	160 °	840	4000 K	82	70 %	2100 lm	2100 lm
929001281404	14T8/48-5000 IF 10/1 EasySmart	-	850	5000 K	82	70 %	2100 lm	2100 lm
929001281464	14T8/48-850/IF21/MAScon IA 10/1	160 °	850	5000 K	82	70 %	2100 lm	2100 lm
929001390604	EasySmart IR Programming Tool 10/1	-	-	-	-	-	-	-
929001398004	15T8 LED/24-3000 IF 6U EasySmart 1PK	160 °	830	3000 K	80	70 %	2000 lm	2000 lm
929001398064	15T8/24-830/IF20-6U/MAScon IA 10/1	160 °	830	3000 K	80	70 %	2000 lm	2000 lm
929001398104	15T8 LED/24-3500 IF 6U EasySmart 1PK	160 °	835	3500 K	80	70 %	2000 lm	2000 lm
929001398164	15T8/24-835/IF20-6U/MAScon IA 10/1	160 °	835	3500 K	80	70 %	2000 lm	2000 lm
929001398204	15T8 LED/24-4000 IF 6U EasySmart 1PK	160 °	840	4000 K	80	70 %	2100 lm	2100 lm
929001398264	15T8/24-840/IF21-6U/MAScon IA 10/1	160 °	840	4000 K	80	70 %	2100 lm	2100 lm
929001398304	15T8 LED/24-5000 IF 6U EasySmart 1PK	160 °	850	5000 K	80	70 %	2100 lm	2100 lm
929001398364	15T8/24-850/IF21-6U/MAScon IA 10/1	160 °	850	5000 K	80	70 %	2100 lm	2100 lm
929001398404	8T8 LED/24-3000 IF EasySmart 1PK	160 °	830	3000 K	80	70 %	1150 lm	1150 lm
929001398464	8T8/24-830/IF11/MAScon IA 10/1	160 °	830	3000 K	80	70 %	1150 lm	1150 lm
929001398504	8T8 LED/24-3500 IF EasySmart 1PK	160 °	835	3500 K	80	70 %	1150 lm	1150 lm
929001398564	8T8/24-835/IF11/MAScon IA 10/1	160 °	835	3500 K	80	70 %	1150 lm	1150 lm
929001398604	8T8 LED/24-4000 IF EasySmart 1PK	160 °	840	4000 K	80	70 %	1200 lm	1200 lm
929001398664	8T8/24-840/IF12/MAScon IA 10/1	160 °	840	4000 K	80	70 %	1200 lm	1200 lm
929001398704	8T8 LED/24-5000 IF EasySmart 1PK	160 °	850	5000 K	80	70 %	1200 lm	1200 lm

MasterConnect LEDtube InstantFit T8

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color	Llmf At End Of		
					Rendering Index (Nom)	Nominal Lifetime (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001398764	8T8/24-850/IF12/MAScon IA 10/1	160 °	850	5000 K	80	70 %	1200 lm	1200 lm

Light Technical (2/2)

Order Code	Full Product Name	Rated Beam Angle	Order Code	Full Product Name	Rated Beam Angle
929001281104	14T8/48-3000 IF 10/1 EasySmart	-	929001398204	15T8 LED/24-4000 IF 6U EasySmart 1PK	160 °
929001281164	14T8/48-830/IF20/MAScon IA 10/1	160 °	929001398264	15T8/24-840/IF21-6U/MAScon IA 10/1	160 °
929001281204	14T8/48-3500 IF 10/1 EasySmart	-	929001398304	15T8 LED/24-5000 IF 6U EasySmart 1PK	160 °
929001281264	14T8/48-835/IF20/MAScon IA 10/1	160 °	929001398364	15T8/24-850/IF21-6U/MAScon IA 10/1	160 °
929001281304	14T8/48-4000 IF 10/1 EasySmart	-	929001398404	8T8 LED/24-3000 IF EasySmart 1PK	160 °
929001281364	14T8/48-840/IF21/MAScon IA 10/1	160 °	929001398464	8T8/24-830/IF11/MAScon IA 10/1	160 °
929001281404	14T8/48-5000 IF 10/1 EasySmart	-	929001398504	8T8 LED/24-3500 IF EasySmart 1PK	160 °
929001281464	14T8/48-850/IF21/MAScon IA 10/1	160 °	929001398564	8T8/24-835/IF11/MAScon IA 10/1	160 °
929001390604	EasySmart IR Programming Tool 10/1	-	929001398604	8T8 LED/24-4000 IF EasySmart 1PK	160 °
929001398004	15T8 LED/24-3000 IF 6U EasySmart 1PK	160 °	929001398664	8T8/24-840/IF12/MAScon IA 10/1	160 °
929001398064	15T8/24-830/IF20-6U/MAScon IA 10/1	160 °	929001398704	8T8 LED/24-5000 IF EasySmart 1PK	160 °
929001398104	15T8 LED/24-3500 IF 6U EasySmart 1PK	160 °	929001398764	8T8/24-850/IF12/MAScon IA 10/1	160 °
929001398164	15T8/24-835/IF20-6U/MAScon IA 10/1	160 °			

Temperature

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Maximum (Nom)	T-Storage (Max)	T-Storage (Min)
929001281104	14T8/48-3000 IF 10/1 EasySmart	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001281164	14T8/48-830/IF20/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001281204	14T8/48-3500 IF 10/1 EasySmart	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001281264	14T8/48-835/IF20/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001281304	14T8/48-4000 IF 10/1 EasySmart	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001281364	14T8/48-840/IF21/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001281404	14T8/48-5000 IF 10/1 EasySmart	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001281464	14T8/48-850/IF21/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001390604	EasySmart IR Programming Tool 10/1	-	-	-	-	-
929001398004	15T8 LED/24-3000 IF 6U EasySmart 1PK	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398064	15T8/24-830/IF20-6U/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398104	15T8 LED/24-3500 IF 6U EasySmart 1PK	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398164	15T8/24-835/IF20-6U/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398204	15T8 LED/24-4000 IF 6U EasySmart 1PK	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398264	15T8/24-840/IF21-6U/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398304	15T8 LED/24-5000 IF 6U EasySmart 1PK	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398364	15T8/24-850/IF21-6U/MAScon IA 10/1	45 °C	-20 °C	40 °C	65 °C	-40 °C
929001398404	8T8 LED/24-3000 IF EasySmart 1PK	45 °C	-20 °C	35 °C	65 °C	-40 °C
929001398464	8T8/24-830/IF11/MAScon IA 10/1	45 °C	-20 °C	35 °C	65 °C	-40 °C
929001398504	8T8 LED/24-3500 IF EasySmart 1PK	45 °C	-20 °C	35 °C	65 °C	-40 °C
929001398564	8T8/24-835/IF11/MAScon IA 10/1	45 °C	-20 °C	35 °C	65 °C	-40 °C
929001398604	8T8 LED/24-4000 IF EasySmart 1PK	45 °C	-20 °C	35 °C	65 °C	-40 °C
929001398664	8T8/24-840/IF12/MAScon IA 10/1	45 °C	-20 °C	35 °C	65 °C	-40 °C
929001398704	8T8 LED/24-5000 IF EasySmart 1PK	45 °C	-20 °C	35 °C	65 °C	-40 °C
929001398764	8T8/24-850/IF12/MAScon IA 10/1	45 °C	-20 °C	35 °C	65 °C	-40 °C

MasterConnect LEDtube InstantFit T8

