



High quality light helps to save more energy

SmartBright Highbay G2

SmartBright Highbay G2 is a high efficient and reliable LED luminaire. Designed as the point to point replacement for HPI 250W/400W luminaires, it offers customers all the benefits of LED lighting – reduced energy consumption, longer service time and less maintenance. In addition, with using high quality of the optical plate, it provides an excellent quality of light, which effectively improves the comfort of your environment.

Benefits

- Energy saving up to 64% comparing to HPI-P system
- Comfort light quality
- Safe & Reliable
- Easy installation and retrofitting

Features

- High efficacy: 90 lumens per watt
- High quality optical plate ensure good uniformity
- Lifetime of 50,000 hours @ Ta35°C with end-to-end Philips production quality assurance
- Full family is in compliance with CB and EMC norms
- Suitable for pole and hook mounting

Application

- Industry area: Factories, warehouses, workshops, assembly lines, etc.
- High ceiling indoor: Shopping centres, airports, stadium, etc.

SmartBright Highbay G2

Versions



BY228P LED50/NW PSU

Product details

GreenUp Lowbay G2 BY288Z Hook



GreenUp Lowbay G2 BY288P Back



SmartBright Highbay G2

Accessories



BY218Z Hook

Ordercode 911401561721



Ordercode 911401822297

