



Less Hassle, More Savings

Essential SmartBright LED Downlight

Essential SmartBright G2 LED Downlight is value for money product with high efficacy, good quality and reliability. It offers multiple configurations from 300lm to 2000lm output, to replace conventional downlight. It can be used for shopping mall, retail store, residential and office. It's an ideal product family to distribute in trade market.

Benefits

- Reliability and safety: meets national and international regulation
- Energy saving: High system efficacy with lower power consumption
- Diversity: One stop shopping with multiple choices of recess round, square as well as surface-mount to fit your dedicated applications
- Easy to install with slim design

Features

- Long life time: 20Khrs to 30Khrs(L70B50@25°C)
- System efficiency: up to 85lm/W
- One family offers recess round, square and surface mount options
- Slim design: 33mm housing body height

Application

- Retail
- Office
- Residential


Essential SmartBright LED Downlight

Versions




Downlight DN027B G3 RD

Dimensional drawing




Essential SmartBright LED Downlight

Dimensional drawing



Essential SmartBright LED Downlight

Dimensional drawing



Essential SmartBright LED Downlight

General Information	
Light source replaceable	No
Light Technical	
Color rendering index (CRI)	80
Operating and Electrical	
Input Voltage	220 to 240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK03

General Information

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	-	-	-	-
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	-	-	-	-
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675238	DN027B G3 LED9/NW 9W	Yes	For mounting on normally	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
	220-240V L125 SQ		flammable surfaces		
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929003280517	DN020B G4 LED20/NW 20W	Yes	For mounting on normally	Temperature 650 °C, duration 30 s	1 unit

Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
	220-240V D200		flammable surfaces		
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Number of gear units
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	1 unit

Essential SmartBright LED Downlight

	Full Product	Driver	Flammability		Number
Order Code	Name	included	mark	Glow-wire test	of gear units
929002674138	DN027B G3	Yes	For mounting on	Temperature	1 unit
	LED15/CW		normally	650 °C,	
	15W 220-240		flammable	duration 30 s	
	D175 RD		surfaces		
929002674538	DN027B G3	Yes	For mounting on	Temperature	1 unit
	LED20/WW		normally	650 °C,	
	19W		flammable	duration 30 s	
	220-240V		surfaces		
929002674638	DN027B G3	Yes	For mounting on	Temperature	1 unit
	LED20/NW		normally	650 °C,	
	19W		flammable	duration 30 s	
	220-240V		surfaces		
929002674738	DN027B G3	Yes	For mounting on	Temperature	1 unit
	LED20/CW		normally	650 °C,	
	19W		flammable	duration 30 s	
	220-240V		surfaces		
929002675738	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED9/WW		normally	650 °C,	
	9W 220-240V		flammable	duration 30 s	
	D150		surfaces		
929002675838	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED9/NW 9W		normally	650 °C,	
	220-240V		flammable	duration 30 s	
	D150		surfaces		
929002675938	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED9/CW 9W		normally	650 °C,	
	220-240V		flammable	duration 30 s	
	D150		surfaces		
929002676038	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED12/WW		normally	650 °C,	
	12W		flammable	duration 30 s	
	220-240V		surfaces		
929002676138	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED12/NW		normally	650 °C,	
	12W		flammable	duration 30 s	
	220-240V		surfaces		
	D175				

Light Technical

		Correlated	Luminous		
	Full Product	Color	Efficacy		
Order Code	Name	Temperature	(rated)	Luminous	Optic
		(Nom)	(Nom)	Flux	type
929002511417	DN020B G3	6500 K	88.00 lm/W	400 lm	-
	LED4/CW 4.5W				

	Full Product	Driver	Flammability		Number
Order Code	Name	included	mark	Glow-wire test	of gear units
929002676238	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED12/CW		normally	650 °C,	
	12W		flammable	duration 30 s	
	220-240V		surfaces		
929002676338	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED15/WW		normally	650 °C,	
	15W		flammable	duration 30 s	
	220-240V		surfaces		
929002676438	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED15/NW		normally	650 °C,	
	15W		flammable	duration 30 s	
	220-240V		surfaces		
929002676538	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED15/CW		normally	650 °C,	
	15W		flammable	duration 30 s	
	220-240V		surfaces		
929002676638	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED20/WW		normally	650 °C,	
	19W		flammable	duration 30 s	
	220-240V		surfaces		
929002676738	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED20/NW		normally	650 °C,	
	19W		flammable	duration 30 s	
	220-240V		surfaces		
929002676838	DN027C G3	Yes	For mounting on	Temperature	1 unit
	LED20/CW		normally	650 °C,	
	19W		flammable	duration 30 s	
	220-240V		surfaces		
	D225				

Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	6500 K	85.00 lm/W	1,200 lm	-
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	4000 K	105.00 lm/W	950 lm	Beam angle 110°
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	4000 K	92 lm/W	1,200 lm	Beam angle 110°
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	4000 K	100 lm/W	2,000 lm	Beam angle 110°
929002671538	DN027B G3 LED6/WW 6W	3000 K	100.00 lm/W	600 lm	Beam angle 110°

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
	220-240V D90 RD				
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	4000 K	100.00 lm/W	600 lm	Beam angle 110°
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	6500 K	100.00 lm/W	600 lm	Beam angle 110°
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	3000 K	100.00 lm/W	600 lm	Beam angle 110°
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	4000 K	108.00 lm/W	650 lm	Beam angle 110°
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	6500 K	108.00 lm/W	650 lm	Beam angle 110°
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	3000 K	100.00 lm/W	900 lm	Beam angle 110°
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	4000 K	105.00 lm/W	950 lm	Beam angle 110°
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	6500 K	105.00 lm/W	950 lm	Beam angle 110°
929002673038	DN027B G3 LED9/WW 9W	3000 K	100.00 lm/W	900 lm	Beam angle 110°

Essential SmartBright LED Downlight

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
929002673138	220-240V D150 RD	4000 K	111.00 lm/W	1,000 lm	Beam angle 110°
	DN027B G3				
	LED9/NW 9W				
929002673238	220-240V D150 RD	6500 K	111.00 lm/W	1,000 lm	Beam angle 110°
	DN027B G3				
	LED9/CW 9W				
929002673338	220-240V D150 RD	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
	DN027B G3				
	LED12/WW 12W				
929002673438	220-240V D150 RD	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
	DN027B G3				
	LED12/NW 12W				
929002673538	220-240V D150 RD	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
	DN027B G3				
	LED12/CW 12W				
929002673638	220-240V D175 RD	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
	DN027B G3				
	LED12/WW 12W				
929002673738	220-240V D175 RD	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
	DN027B G3				
	LED12/NW 12W				
929002673838	220-240V D175 RD	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
	DN027B G3				
	LED12/CW 12W				
929002673938	220-240 D175 RD	3000 K	100.00 lm/W	1,500 lm	Beam angle 110°
	DN027B G3				
	LED15/WW 15W				
929002674038	220-240 D175 RD	4000 K	106.00 lm/W	1,600 lm	Beam angle 110°
	DN027B G3				
	LED15/NW 15W				
929002674138	220-240 D175 RD	6500 K	106.00 lm/W	1,600 lm	Beam angle 110°
	DN027B G3				
	LED15/CW 15W				
929002674538	220-240V D200 RD	3000 K	105.00 lm/W	2,000 lm	Beam angle 110°
	DN027B G3				
	LED20/WW 19W				

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
929002674638	DN027B G3	4000 K	110.00 lm/W	2,100 lm	Beam angle 110°
	LED20/NW 19W				
	220-240V D200 RD				
929002674738	DN027B G3	6500 K	110.00 lm/W	2,100 lm	Beam angle 110°
	LED20/CW 19W				
	220-240V D200 RD				
929002675738	DN027C G3	3000 K	100.00 lm/W	900 lm	Beam angle 110°
	LED9/WW 9W				
	220-240V D150				
929002675838	DN027C G3	4000 K	105.00 lm/W	950 lm	Beam angle 110°
	LED9/NW 9W				
	220-240V D150				
929002675938	DN027C G3	6500 K	105.00 lm/W	950 lm	Beam angle 110°
	LED9/CW 9W				
	220-240V D150				
929002676038	DN027C G3	3000 K	100.00 lm/W	1,200 lm	Beam angle 110°
	LED12/WW 12W				
	220-240V D175				
929002676138	DN027C G3	4000 K	108.00 lm/W	1,300 lm	Beam angle 110°
	LED12/NW 12W				
	220-240V D175				
929002676238	DN027C G3	6500 K	108.00 lm/W	1,300 lm	Beam angle 110°
	LED12/CW 12W				
	220-240V D175				
929002676338	DN027C G3	3000 K	100.00 lm/W	1,500 lm	Beam angle 110°
	LED15/WW 15W				
	220-240V D200				
929002676438	DN027C G3	4000 K	106.00 lm/W	1,600 lm	Beam angle 110°
	LED15/NW 15W				
	220-240V D200				
929002676538	DN027C G3	6500 K	106.00 lm/W	1,600 lm	Beam angle 110°
	LED15/CW 15W				
	220-240V D200				
929002676638	DN027C G3	3000 K	105.00 lm/W	2,000 lm	Beam angle 110°
	LED20/WW 19W				
	220-240V D225				
929002676738	DN027C G3	4000 K	110.00 lm/W	2,100 lm	Beam angle 110°
	LED20/NW 19W				
	220-240V D225				
929002676838	DN027C G3	6500 K	110.00 lm/W	2,100 lm	Beam angle 110°
	LED20/CW 19W				
	220-240V D225				

Essential SmartBright LED Downlight

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	50 or 60 Hz	4.5 W
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	50 or 60 Hz	14 W
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	50 or 60 Hz	6 W
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	50 or 60 Hz	6 W
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	50 or 60 Hz	6 W
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	50 or 60 Hz	9 W
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	50 or 60 Hz	9 W
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	50 or 60 Hz	9 W
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	50 or 60 Hz	12 W
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	50 or 60 Hz	12 W
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	50 or 60 Hz	12 W
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	-	13 W
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	-	20 W
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	50 or 60 Hz	6 W
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	50 or 60 Hz	6 W
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	50 or 60 Hz	6 W
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	50 or 60 Hz	6 W
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	50 or 60 Hz	6 W
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	50 or 60 Hz	6 W
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	50 or 60 Hz	6 W
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	50 or 60 Hz	6 W
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	50 or 60 Hz	6 W
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	50 or 60 Hz	9 W
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	50 or 60 Hz	9 W
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	50 or 60 Hz	9 W

Order Code	Full Product Name	Line Frequency	Power
			Consumption
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	50 or 60 Hz	9 W
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	50 or 60 Hz	9 W
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	50 or 60 Hz	9 W
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	50 or 60 Hz	12 W
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	50 or 60 Hz	12 W
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	50 or 60 Hz	12 W
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	50 or 60 Hz	12 W
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	50 or 60 Hz	12 W
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	50 or 60 Hz	12 W
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	50 or 60 Hz	15 W
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	50 or 60 Hz	15 W
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	50 or 60 Hz	15 W
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	50 or 60 Hz	19 W
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	50 or 60 Hz	19 W
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	50 or 60 Hz	19 W
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	50 or 60 Hz	9 W
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	50 or 60 Hz	9 W
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	50 or 60 Hz	9 W
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	50 or 60 Hz	12 W
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	50 or 60 Hz	12 W
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	50 or 60 Hz	12 W
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	50 or 60 Hz	15 W
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	50 or 60 Hz	15 W
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	50 or 60 Hz	15 W
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	50 or 60 Hz	19 W

Essential SmartBright LED Downlight

Order Code	Full Product Name	Power	
		Line Frequency	Consumption
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	50 or 60 Hz	19 W

Order Code	Full Product Name	Power	
		Line Frequency	Consumption
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	50 or 60 Hz	19 W

Temperature

Order Code	Full Product Name	Ambient temperature range
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	-20 to +40 °C
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	-20 to +40 °C
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	-20 to +40 °C
929002674938	DN027B G3 LED6/CW 6W 220-240V L100 SQ	-20 to +40 °C
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	-20 to +40 °C
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	-20 to +40 °C
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	-20 to +40 °C
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	-20 to +40 °C
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	-20 to +40 °C
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	-20 to +40 °C
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	-20 to +40 °C
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	-20 °C to 40 °C
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	-20 °C to 40 °C
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	-20 to +40 °C
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	-20 to +40 °C
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	-20 to +40 °C
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	-20 to +40 °C
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	-20 to +40 °C
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	-20 to +40 °C
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	-20 to +40 °C
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	-20 to +40 °C
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	-20 to +40 °C
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	-20 to +40 °C
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	-20 to +40 °C
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	-20 to +40 °C
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	-20 to +40 °C
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	-20 to +40 °C
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	-20 to +40 °C
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	-20 to +40 °C
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	-20 to +40 °C
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	-20 to +40 °C
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	-20 to +40 °C
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	-20 to +40 °C
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	-20 to +40 °C
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	-20 to +40 °C
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	-20 to +40 °C
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	-20 to +40 °C
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	-20 to +40 °C
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	-20 to +40 °C
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	-20 to +40 °C
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	-20 to +40 °C
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	-20 to +40 °C
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	-20 to +40 °C

Essential SmartBright LED Downlight

Order Code	Full Product Name	Ambient temperature range
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	-20 to +40 °C
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	-20 to +40 °C
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	-20 to +40 °C
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	-20 to +40 °C
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	-20 to +40 °C
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	-20 to +40 °C
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	-20 to +40 °C

Approval and Application

Order Code	Full Product Name	Ingress protection code
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	IP20
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	IP20
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	IP20/40
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	IP20/40
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	IP20/40
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	IP20/40
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	IP20/40
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	IP20/40
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	IP20/40
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	IP20/40
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	IP20/40
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	IP20
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	IP20
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	IP20/40
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	IP20/40
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	IP20/40
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	IP20/40
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	IP20/40
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	IP20/40
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	IP20/40
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	IP20/40
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	IP20/40
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	IP20/40
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	IP20/40
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	IP20/40
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	IP20/40

Order Code	Full Product Name	Ingress protection code
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	IP20/40
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	IP20/40
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	IP20/40
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	IP20/40
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	IP20/40
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	IP20/40
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	IP20/40
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	IP20/40
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	IP20/40
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	IP20/40
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	IP20/40
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	IP20/40
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	IP20/40
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	IP20/40
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	IP20/40
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	IP20/40
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	IP20/40
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	IP20/40
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	IP20/40
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	IP20/40
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	IP20/40
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	IP20/40
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	IP20/40
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	IP20/40
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	IP20/40
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	IP20/40

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	(0.3123, 0.3283) 6	-
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	(0.3123, 0.3283) 6	-
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%

Essential SmartBright LED Downlight

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	(X=, 0.3839 ; Y=, 0.3843) 5SDCM	+/-10%
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	(IEC3000K, 0.44, 0.403) < 5SDCM	+/-10%
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	(IEC4000K, 0.38, 0.38) < 5SDCM	+/-10%
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	(IEC6500K, 0.313, 0.337) < 5SDCM	+/-10%

Over Time Performance (IEC Compliant)

Essential SmartBright LED Downlight

Order Code	Full Product Name	Driver failure rate at 5000 h
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	1.6 %
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	1.6 %
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	0.012 %
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	0.012 %
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	0.012 %
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	0.012 %
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	0.012 %
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	0.012 %
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	0.012 %
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	0.012 %
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	0.012 %
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	1.2
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	1.2
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	0.012 %
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	0.012 %
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	0.012 %
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	0.012 %
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	0.012 %
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	0.012 %
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	0.012 %
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	0.012 %
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	0.012 %
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	0.012 %
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	0.012 %
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	0.012 %
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	0.012 %

Application Conditions



Order Code	Full Product Name	Suitable for random switching
929002511417	DN020B G3 LED4/CW 4.5W 220-240V D90 SNI	-
929002512917	DN020B G3 LED12/CW 14W 220-240V D150 SNI	-
929002674838	DN027B G3 LED6/WW 6W 220-240V L100 SQ	No
929002674938	DN027B G3 LED6/NW 6W 220-240V L100 SQ	No
929002675038	DN027B G3 LED6/CW 6W 220-240V L100 SQ	No
929002675138	DN027B G3 LED9/WW 9W 220-240V L125 SQ	No
929002675238	DN027B G3 LED9/NW 9W 220-240V L125 SQ	No
929002675338	DN027B G3 LED9/CW 9W 220-240V L125 SQ	No
929002675438	DN027B G3 LED12/WW 12W 220-240V L150 SQ	No
929002675538	DN027B G3 LED12/NW 12W 220-240V L150 SQ	No
929002675638	DN027B G3 LED12/CW 12W 220-240V L150 SQ	No
929003279917	DN020B G4 LED12/NW 13W 220-240V D150	Not applicable
929003280517	DN020B G4 LED20/NW 20W 220-240V D200	Not applicable
929002671538	DN027B G3 LED6/WW 6W 220-240V D90 RD	No
929002671638	DN027B G3 LED6/NW 6W 220-240V D90 RD	No
929002671738	DN027B G3 LED6/CW 6W 220-240V D90 RD	No
929002672138	DN027B G3 LED6/WW 6W 220-240V D100 RD	No
929002672238	DN027B G3 LED6/NW 6W 220-240V D100 RD	No
929002672338	DN027B G3 LED6/CW 6W 220-240V D100 RD	No
929002672438	DN027B G3 LED6/WW 6W 220-240V D125 RD	No

Order Code	Full Product Name	Driver failure rate at 5000 h
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	0.012 %
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	0.012 %
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	0.012 %
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	0.012 %
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	0.012 %
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	0.012 %
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	0.012 %
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	0.012 %
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	0.012 %
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	0.012 %
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	0.012 %
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	0.012 %
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	0.012 %
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	0.012 %
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	0.012 %
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	0.012 %
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	0.012 %
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	0.012 %
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	0.012 %
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	0.012 %
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	0.012 %
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	0.012 %
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	0.012 %
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	0.012 %
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	0.012 %
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	0.012 %



Order Code	Full Product Name	Suitable for random switching
929002672538	DN027B G3 LED6/NW 6W 220-240V D125 RD	No
929002672638	DN027B G3 LED6/CW 6W 220-240V D125 RD	No
929002672738	DN027B G3 LED9/WW 9W 220-240V D125 RD	No
929002672838	DN027B G3 LED9/NW 9W 220-240V D125 RD	No
929002672938	DN027B G3 LED9/CW 9W 220-240V D125 RD	No
929002673038	DN027B G3 LED9/WW 9W 220-240V D150 RD	No
929002673138	DN027B G3 LED9/NW 9W 220-240V D150 RD	No
929002673238	DN027B G3 LED9/CW 9W 220-240V D150 RD	No
929002673338	DN027B G3 LED12/WW 12W 220-240V D150 RD	No
929002673438	DN027B G3 LED12/NW 12W 220-240V D150 RD	No
929002673538	DN027B G3 LED12/CW 12W 220-240V D150 RD	No
929002673638	DN027B G3 LED12/WW 12W 220-240V D175 RD	No
929002673738	DN027B G3 LED12/NW 12W 220-240V D175 RD	No
929002673838	DN027B G3 LED12/CW 12W 220-240V D175 RD	No
929002673938	DN027B G3 LED15/WW 15W 220-240 D175 RD	No
929002674038	DN027B G3 LED15/NW 15W 220-240 D175 RD	No
929002674138	DN027B G3 LED15/CW 15W 220-240 D175 RD	No
929002674538	DN027B G3 LED20/WW 19W 220-240V D200 RD	No
929002674638	DN027B G3 LED20/NW 19W 220-240V D200 RD	No
929002674738	DN027B G3 LED20/CW 19W 220-240V D200 RD	No

Essential SmartBright LED Downlight



Order Code	Full Product Name	Suitable for random switching
929002675738	DN027C G3 LED9/WW 9W 220-240V D150	No
929002675838	DN027C G3 LED9/NW 9W 220-240V D150	No
929002675938	DN027C G3 LED9/CW 9W 220-240V D150	No
929002676038	DN027C G3 LED12/WW 12W 220-240V D175	No
929002676138	DN027C G3 LED12/NW 12W 220-240V D175	No
929002676238	DN027C G3 LED12/CW 12W 220-240V D175	No
929002676338	DN027C G3 LED15/WW 15W 220-240V D200	No
929002676438	DN027C G3 LED15/NW 15W 220-240V D200	No
929002676538	DN027C G3 LED15/CW 15W 220-240V D200	No
929002676638	DN027C G3 LED20/WW 19W 220-240V D225	No
929002676738	DN027C G3 LED20/NW 19W 220-240V D225	No
929002676838	DN027C G3 LED20/CW 19W 220-240V D225	No





Essential SmartBright LED Downlight





Essential SmartBright LED Downlight





Essential SmartBright LED Downlight



Essential SmartBright LED Downlight



Essential SmartBright LED Downlight



Essential SmartBright LED Downlight

