



Affordable and reliable energy saving LED Lighting Luminaires

Smartbright Waterproof G2

SmartBright Waterproof G2 is an innovation from SmartBright Waterproof G1, can be used to replace traditional waterproof luminaires with fluorescent lamps or LED tubes, provides quality of light with substantial energy & maintenance savings. The luminaire and its components are designed for both indoor and semi-outdoor application (anti-UV PC material housing and diffuser), it is an ideal lighting solution for canopy, food industry, car parks, car washers. Beyond that, SmartBright Waterproof G2 is also maintenance free by seal for life integral design, and reliable 25K hrs lifetime.

Benefits

- Easy Wiring: 3 wiring options for select, fulfil with customer wiring habits.
- Excellent Performance: good uniformity SDCM<5, high quality light CRI>80, more brighter with higher lumen output.
- Reliable Quality: 25K hours with 70% lumen maintained, wide range working temperature from -30°C to +45°C, can be applied in various industrial environments

Features

- Robust design: IP65 IK06, Anti UV Polycarbonate housing, dual extrusion technology.
- Easy Installation: Stainless Universal Mounting Clip, Stainless Screws, Stainless Hooks, all in 1 package with luminaire.

Smartbright Waterproof G2

Application

- Industry general area
- Food and beverage
- workshop and assembly line
- Car park
- Canopy, walkways
- Semi outdoor

Versions




Product details



WT066C Breather Detail Photo



WT066C Mounting Bracket Detail Photo



WT066C Wiring Detail Photo

