



Greenperform Cleanroom Teardrop G2, provide you a safe, reliable, comfortable cleanroom lighting experience.

Greenperform Cleanroom Teardrop G2

Greenperform Cleanroom Teardrop G2 is an optimized cleanroom lighting fixture. With its slim, compact and smooth housing design, Teardrop G2 maximally avoids dust attached in cleanroom application, and can meet the classification 10 ~1000. CR388C series products also provide excellent lighting quality, substantial energy saving and reliable quality of maintenance free. Both white and yellow lighting solutions are available, Teardrop G2 is your excellent option for both new projects and retrofit projects.

Benefits

- - Compact, slim, robust housing, avoid the dust attaching
- - soft, uniform lighting output, low flicking, friendly to human eyes
- - long lifetime, low energy consumption, delivers energy saving and set you free from product maintenance
- - Easy installation, saving your labor cost

Greenperform Cleanroom Teardrop G2


Features

- IP40, IK03, dural extrusion housing, cleanroom classification 10 - 1000
- CRI>80, SDCM<5, anti UV Polycarbonate optical diffuser
- 50K hours lifetime @ L70B50
- Surface& ceiling installation, track kits available for T-bar installation

Application

- Integrated circuit (VLS) manufacturing
- Fine mechanical components, aviation instruments, hydraulic parts
- Critical optical devices, optical discs
- Beverage, Aseptic filling (juice, custards)
- Food, Pharmaceutical industry
- Semiconductor manufacturing/ assembly
- etc.

Versions




CR388C Amber



CR388C Normal

Dimensional drawing



Greenperform Cleanroom Teardrop G2

Product details



CR388C Detail Photo

General Information

CE mark	-
Driver included	Yes
Glow-wire test	Temperature 750 °C, duration 5 s
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Optical cover type	Polycarbonate
Optic type	Symmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Temperature

Ambient temperature range	0 to +35 °C
---------------------------	-------------

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Protection class IEC	Safety class I
Mech. impact protection code	IK03
Ingress protection code	IP40

Initial Performance (IEC Compliant)

Initial chromaticity	SDCM<5
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401516941	CR388C LED20 Amber L120 PSU	-	-	105 lm/W	2,200 lm
911401516541	CR388C LED40 NW L120 PSU	4000 K	>80	120 lm/W	3,900 lm
911401516641	CR388C LED40 CW L120 PSU	6500 K	>80	120 lm/W	3,900 lm
911401516741	CR388C LED40 NW L120 PSD	4000 K	>80	190 lm/W	4,500 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401516941	CR388C LED20 Amber L120 PSU	21 W
911401516541	CR388C LED40 NW L120 PSU	32 W

Order Code	Full Product Name	Power Consumption
911401516641	CR388C LED40 CW L120 PSU	32 W
911401516741	CR388C LED40 NW L120 PSD	39 W

Controls and Dimming

Greenperform Cleanroom Teardrop G2

Order Code	Full Product Name	Dimmable
911401516941	CR388C LED20 Amber L120 PSU	No
911401516541	CR388C LED40 NW L120 PSU	No

Order Code	Full Product Name	Dimmable
911401516641	CR388C LED40 CW L120 PSU	No
911401516741	CR388C LED40 NW L120 PSD	Yes

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life	
		L80B50	L90B50
911401516941	CR388C LED20 Amber L120 PSU	45,000 hour(s)	40,000 hour(s)
911401516541	CR388C LED40 NW L120 PSU	-	-

Order Code	Full Product Name	Median useful life	
		L80B50	L90B50
911401516641	CR388C LED40 CW L120 PSU	45,000 hour(s)	40,000 hour(s)
911401516741	CR388C LED40 NW L120 PSD	45,000 hour(s)	40,000 hour(s)

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401516941	CR388C LED20 Amber L120 PSU	Not applicable
911401516541	CR388C LED40 NW L120 PSU	Not applicable

Order Code	Full Product Name	Maximum dim level
911401516641	CR388C LED40 CW L120 PSU	Not applicable
911401516741	CR388C LED40 NW L120 PSD	1%

