



Simply great LEDSwitch now to great quality LED at a great price

Ledinaire floodlight mini

The Ledinaire range contains a selection of popular off-the-shelf LED luminaires that come with the Philips high-quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

Benefits

- Philips quality and reliability
- Fast ROI: energy savings >80% (halogen lamps)
- Quick installation without opening the floodlight
- Philips high-quality finish, robust and fully reliable

Features

- System flux: 900 lm (10 W); 2,500 lm (27 W); 4,500 lm (45 W) versions with Neutral White, CRI 80 and a high-efficiency of 90 lm/W
- Extra flat IP65 design of floodlights, supplied with cable, can be mounted standing-up or hanging-down
- Motion detector versions
- Long lifetime of 50,000 hours (Ta 25 °C)
- Prismatic glass for comfortable light
- CE, CB and ROHS compliant

Application

- Building facades, retail outlets
- Gardens, underpasses
- Advertising hoardings

Ledinaire floodlight mini

Specifications

Aiming Horizontal	to °
Aiming Vertical	to °
AverageAmbientTempe rature	-25 to +40 °C
Beam angle	100°
Color	Grey and Black
	Flying leads/wires (Flying leads/wires)
	No
	Power supply unit (PSU)
	4000 K
	10, 27, 50 W
	90 lm/W

	900, 2500, 4500 lm
	50 to 60 Hz
	220 to 240 V
	0.13, 0.38, 0.64 A
	No
Material of Bracket	Bracket:
Material	Housing: polycarbonate
Material of Reflector	Reflector: -
	35000 h
	2/2 kV
	3 years

Versions



LED Module, system flux 900 lm -
LED - 100°

Product details



Ledinaire_mini-
BVP105_Led9-1DPP.TIF



Ledinaire_mini-
BVP105_Led9-2DPP.TIF



Ledinaire_mini-
BVP105_Led9-3DPP.TIF



Ledinaire_mini-
BVP105_Led9-4DPP.TIF

Ledinaire floodlight mini

Product details



Ledinaire_mini-
BVP105_Led9-5DPP.TIF



Ledinaire_mini-
BVP105_Led25-1DPP.TIF



Ledinaire_mini-
BVP105_Led25-2DPP.TIF



Ledinaire_mini-
BVP105_Led25-3DPP.TIF



Ledinaire_mini-
BVP105_Led25-4DPP.TIF



Ledinaire_mini-
BVP105_Led25-5DPP.TIF



Ledinaire_mini-
BVP105_Led45-1DPP.TIF



Ledinaire_mini-
BVP105_Led45-2DPP.TIF

Ledinaire floodlight mini

Product details



Ledinaire_mini-
BVP105_Led45-3DPP.TIF



Ledinaire_mini-
BVP105_Led45-4DPP.TIF



Ledinaire_mini-
BVP105_Led45-5DPP.TIF



Ledinaire_floodlight_mini-
BVP105-1DPP.TIF



Ledinaire_floodlight_mini-
BVP105-2DPP.TIF



Ledinaire_floodlight_mini-
BVP105_Led45-1DPP.TIF



Ledinaire_floodlight_mini-
BVP105_Led45-2DPP.TIF

Ledinaire floodlight mini

