



An Easier Way to More Savings

Essential Smartbright LED Batten

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Benefits

- Slim and trunkable, integrated design
- To replace T5 Essential Batten TCH086/084
- Polycarbonate housing with one pc extrusion process
- Semi-transparent endcap eliminates the black spot entirely in trunking
- Different type can mix and match, flexible in a long length
- Sockets and accessories compatible with BN066C & TCH086 EV

Features

- One piece PC extrusion housing, Single piece integral design for better aesthetics
- Transparent end cap, Enables continuous light line without black spots up to 10pcs
- CRI 80, SDCM <lt/> 7, 80lm/W, Superior light quality combined with good energy savings
- Slim profile, Ideal for task lighting / cove lighting applications
- Slim and narrow end cap, Fits the cove or shelf more easily
- Uniform Light, Optimal optical design to ensure no spottiness
- L70 20k hours, Reliable long lasting solution
- 4 lengths, 3 colors, Increased number of options for easy application

Application

- Indirect lighting: Shelf, cove, back light box, ambient
- Direct lighting: Convenient store, Long distance linear lighting