



Most affordable LED panel with excellent light quality

SmartBright Slim Panel

SmartBright Slim Panel provides the most affordable LED solution to replace TL troffer. Its slim design (height of luminaire only 10mm) and multiple mounting options cater various applications (including plastic ceiling). As an edge light architecture, SlimBright Slim Panel delivers comfortable light with Excellent uniformity.

Benefits

- 50% more energy efficient compared to conventional TL solution
- Full window illumination –deliver comfortable light with excellent uniformity
- Slim design with height of only 10mm

Features

- System efficacy 80lm/W
- CRI > 80, SDCM 5
- High reliability, 25k hours (L70@25deg)

Application

- Open plan office
- Cell office
- Hospital
- Meeting/Training room

SmartBright Slim Panel

Versions



RC091V W60L60

RC091V W30L120

Application Conditions	
Ambient temperature range	-10 to +35 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220/240 V
General Information	
Beam angle of light source	- °
CE mark	CE mark
Protection class IEC	Safety class II (II)
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.43, 0.40) SDCM>5
Init. Color Rendering Index	>80
Initial LED luminaire efficacy	80 lm/W
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Color	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color		Initial luminous flux	Initial input power
		Temperature			
911401845697	RC091V LED26S/840 PSU W60L60 GM	4000 K		2600 lm	34 W
911401845897	RC091V LED36S/840 PSU W60L60 GM	4000 K		3600 lm	45 W
911401846097	RC091V LED26S/865 PSU W60L60 GM	6500 K		2600 lm	34 W
911401846297	RC091V LED36S/865 PSU W60L60 GM	6500 K		3600 lm	45 W
911401846497	RC091V LED26S/840 PSU W60L60 PCV GM	4000 K		2600 lm	34 W
911401846697	RC091V LED36S/840 PSU W60L60 PCV GM	4000 K		3600 lm	45 W
911401846897	RC091V LED26S/865 PSU W60L60 PCV GM	6500 K		2600 lm	34 W
911401847097	RC091V LED36S/865 PSU W60L60 PCV GM	6500 K		3600 lm	45 W
911401845797	RC091V LED26S/840 PSU W30L120 GM	4000 K		2600 lm	34 W
911401845997	RC091V LED36S/840 PSU W30L120 GM	4000 K		3600 lm	45 W
911401846197	RC091V LED26S/865 PSU W30L120 GM	6500 K		2600 lm	34 W
911401846397	RC091V LED36S/865 PSU W30L120 GM	6500 K		3600 lm	45 W
911401846597	RC091V LED26S/840 PSU W30L120 PCV GM	4000 K		2600 lm	34 W
911401846797	RC091V LED36S/840 PSU W30L120 PCV GM	4000 K		3600 lm	45 W
911401846997	RC091V LED26S/865 PSU W30L120 PCV GM	6500 K		2600 lm	34 W
911401847197	RC091V LED36S/865 PSU W30L120 PCV GM	6500 K		3600 lm	45 W

SmartBright Slim Panel

