



Most affordable LED panel with excellent light quality

SmartBright Slim Panel

SmartBright Slim Panel provides the most affordable LED solution to replace TL troffer. Its slim design (height of luminaire only 10mm) and multiple mounting options cater various applications (including plastic ceiling). As an edge light architecture, SlimBright Slim Panel delivers comfortable light with Excellent uniformity.

Benefits

- 50% more energy efficient compared to conventional TL solution
- Full window illumination –deliver comfortable light with excellent uniformity
- Slim design with height of only 10mm

Features

- System efficacy 80lm/W
- CRI > 80, SDCM 5
- High reliability, 25k hours (L70@25deg)

Application

- Open plan office
- Cell office
- Hospital
- Meeting/Training room

SmartBright Slim Panel

Versions



Application Conditions

Ambient temperature range	-10 to +35 °C
Maximum dim level	Not applicable
Suitable for random switching	Not applicable

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220/240 V
---------------	-----------

General Information

Beam angle of light source	- °
CE mark	CE mark
Protection class IEC	Safety class II (II)
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB

Initial Performance (IEC Compliant)

Initial chromaticity	(0.43, 0.40) SDCM>5
Init. Corr. Colour Temperature	6500 K
Init. Colour Rendering Index	>80
Initial LED luminaire efficacy	80 lm/W
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	White
--------	-------

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux	Initial input power
911401846197	RC091V LED26S/865 PSU W30L120 GM	2600 lm	34 W
911401846397	RC091V LED36S/865 PSU W30L120 GM	3600 lm	45 W

SmartBright Slim Panel

