



Stylish, office-compliant lighting offering new possibilities

TrueLevel, surface mounted

Today's lighting fixtures need to deliver more than just light. In offices the ideal fixture needs to enable savings, and is expected to be ready for future advances. It must also be ready to be paired with lighting controls and systems. Moreover, the ideal office lighting fixture should also complement the interior design of the office space. Philips TrueLevel fulfills all these requirements and more! Building on the strengths of Philips TrueLine a superior light line technology for offices, TrueLevel's high efficiency, superior office-compliant lighting and readiness to be potentially paired with lighting systems makes it an excellent choice for offices. In addition, TrueLevel's stylish, minimalistic, clean design complements the interior architecture and can become a design element on its own.

Benefits

- High quality, office-compliant lighting
- Offering new possibilities in the office space
- Stylish design enhancing the interior architecture

Features

- No light interruptions on the light surface, sharp and well-defined corners, comfortable to the eye
- Ready to be paired with lighting controls
- Clean, minimalistic design

TrueLevel, surface mounted

Application

- Office buildings
- Educational spaces

Specifications


| | |
|--------------------------------------|---|
| Main color of the Luminaire | White RAL 9003 |
| Connection | 2 Push-in connector 5-pole (2 Push-in connector 5-pole) |
| Driver failure rate at 5000 h in % | 0.01 % |
| Initial correlated color temperature | 4000 K |
| Initial input power | 20.5 W, 28 W |

| | |
|--------------------------------|-------------------|
| Initial LED luminaire efficacy | 151, 153 lm/W |
| Initial luminous flux | 3100 lm, 4300 lm |
| Input frequency | 50 to 60 Hz |
| Input voltage | 220-240 V |
| Inrush current (A) | 19 A |
| Light source color | 940 neutral white |
| Material | Housing: steel |

Versions



Product details



TrueLevel, surface mounted

Product details



TrueLevel_Surface Mounted-
SM540C-2DPP.TIF



TrueLevel_Surface Mounted-
SM540C-3DPP.TIF



TrueLevel_Surface Mounted-
SM540C-5DPP.TIF



TrueLevel_Surface Mounted-
SM540C-7DPP.TIF

TrueLevel, surface mounted

| | |
|--|---|
| - | |
| Driver failure rate at 5000 h | 0.01 % |
| Application Conditions | |
| Ambient temperature range | +10 to +40 °C |
| Maximum dim level | 1% |
| Suitable for random switching | No |
| Approval and Application | |
| Mech. impact protection code | IK02 |
| Ingress protection code | IP40 |
| Controls and Dimming | |
| Dimmable | Yes |
| Operating and Electrical | |
| Input Voltage | 220-240 V |
| General Information | |
| CE mark | CE mark |
| Protection class IEC | Safety class I |
| Optical cover/lens type | Polymethyl methacrylate bowl/cover |
| Driver included | Yes |
| ENEC mark | ENEC mark |
| Flammability mark | For mounting on normally flammable surfaces |
| Glow-wire test | Temperature 650 °C, duration 5 s |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Optic type | - |
| Product Family Code | SM540C |
| Service tag | Yes |
| Initial Performance (IEC Compliant) | |
| Initial chromaticity | 0,38 ; 0,38 |
| Init. Corr. Color Temperature | 4000 K |
| Init. Color Rendering Index | ≥90 |
| Luminous flux tolerance | +/-10% |
| Mechanical and Housing | |
| Color | White RAL 9003 |

General Information

| Order Code | Full Product Name | Lamp family code |
|--------------|------------------------------------|------------------|
| 910505100091 | SM540C LED43S/940 PSD PIP L1480 WH | LED43S |
| 910505100093 | SM540C LED31S/940 PSD PIP L1480 WH | LED31S |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name | Initial LED | Initial luminous flux | Initial input power |
|--------------|------------------------------------|--------------------|-----------------------|---------------------|
| | | luminaire efficacy | | |
| 910505100091 | SM540C LED43S/940 PSD PIP L1480 WH | 153 lm/W | 4300 lm | 28 W |

TrueLevel, surface mounted

| Order Code | Full Product Name | Initial LED luminaire efficacy | Initial luminous flux | Initial input power |
|--------------|---------------------------------------|--------------------------------------|--------------------------|------------------------|
| 910505100093 | SM540C LED31S/940 PSD PIP L1480 WH | 151 lm/W | 3100 lm | 20.5 W |

