



Vibrant outdoor lighting has the power to revitalize a city's spirit, transforming it into an exciting, uplifting space where residents and visitors feel safe and at home even after dark.

CitySpirit Street LED (Color Ring) BDS482

Philips CitySpirit Street LED Colour Ring are luminaires designed to provide quality, environmentally friendly lighting that seamlessly integrates into the urban landscape. Equipped with LED technology, consistent light output, and decorative ring functionality, these luminaires deliver efficient and excellent lighting to any city.

Benefits

- Serviceability - LED driver module is easy replaceable
- Colour ring options - Available in red or green or blue

CitySpirit Street LED (Color Ring) BDS482

Features

- Stylish lighting possibilities - Choose from a selection of color rings to add flair to urban spaces
- Excellent light quality - Advanced optical design enhances visual comfort while high lumen output ensures visibility and safety

Application

- City centers and squares
- Residential and pedestrian area
- Promenades

Versions



CitySpirit Street BDS482

CitySpirit Street LED (Color Ring) BDS482

Application Conditions

Maximum dim level	Programmable
-------------------	--------------

Approval and Application

Mech. impact protection code	IK09
Surge Protection (Common/Differential)	4/2 kV

Controls and Dimming

Dimmable	Yes
----------	-----

General Information

CE mark	CE mark
Optical cover/lens type	Flat glass
Driver included	Yes
Lamp family code	CFT
Light source replaceable	Yes
Number of gear units	2 units
Optic type	Reflector transparent

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>70
Initial luminous flux	3680 lm

Mechanical and Housing

Color	Dark gray
-------	-----------

General Information

Order Code	Full Product Name	Light source color
911401617503	BDS482 LED37/NW 220-240V BL	740 neutral white
911401617603	BDS482 LED35/WW 220-240V RD	730 warm white
911401617703	BDS482 LED35/WW 220-240V GRN	730 warm white
911401618203	BDS482 LED37/NW 220-240V RD	740 neutral white
911401618303	BDS482 LED37/NW 220-240V GRN	740 neutral white
911401619103	BDS482 LED35/WW 220-240V BL	730 warm white
911401620804	BDS482 LED35/WW 220-240V GRN AUS	730 warm white
911401620904	BDS482 LED35/WW 220-240V BL AUS	730 warm white
911401621004	BDS482 LED35/WW 220-240V RD AUS	730 warm white
911401621104	BDS482 LED37/NW 220-240V RD AUS	740 neutral white
911401621304	BDS482 LED37/NW 220-240V BL AUS	740 neutral white
911401621804	BDS482 LED37/NW 220-240V GRN AUS	740 neutral white

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Order Code	Full Product Name	Init. Corr. Color Temperature
911401617503	BDS482 LED37/NW 220-240V BL	4000 K	911401620804	BDS482 LED35/WW 220-240V GRN AUS	3000 K
911401617603	BDS482 LED35/WW 220-240V RD	3000 K	911401620904	BDS482 LED35/WW 220-240V BL AUS	3000 K
911401617703	BDS482 LED35/WW 220-240V GRN	3000 K	911401621004	BDS482 LED35/WW 220-240V RD AUS	3000 K
911401618203	BDS482 LED37/NW 220-240V RD	4000 K	911401621104	BDS482 LED37/NW 220-240V RD AUS	4000 K
911401618303	BDS482 LED37/NW 220-240V GRN	4000 K	911401621304	BDS482 LED37/NW 220-240V BL AUS	4000 K
911401619103	BDS482 LED35/WW 220-240V BL	3000 K	911401621804	BDS482 LED37/NW 220-240V GRN AUS	4000 K

