



# An exterior precision-control linear direct-view luminaire with intelligent RGB light

## Accent MX Powercore gen3, RGB

iColor Accent MX Powercore gen2 is a direct-view linear LED luminaire ideally suited for creating long ribbons of colour and colour-changing effects. The variable resolution offers the precision to display large-scale video, graphics and intricately designed effects in a host of architectural, retail and entertainment settings. iColor Accent MX Powercore gen2 offers the efficiency and cost-effectiveness of Powercore technology in an outdoor-rated, road-ready aluminium housing.

### Benefits

- Rugged, durable construction for long-term outdoor use
- Support long runs of products without the need for new power or data
- Individually controllable in 30 mm to 1,200 mm wide segments

### Features

- Available in 60 cm and 120 cm versions
- Full colour output with good-quality white
- Light output of over 591 lumens for a 1,214 mm luminaire
- Wide viewing angle of 220°
- Integrated Powercore technology and DMX or Ethernet capability

### Application

- Architectural accent and effect lighting
- Entertainment applications
- Large-scale video displays

## Accent MX Powercore gen3, RGB

### Versions

