



Dimmable high Performance LED downlight for indoors

GreenPerform DN391/392/393/394/395 downlight

GreenPerform is a high performance Led downlight family suitable for use in a series of Lighting applications in Office, Retail and General Area Lighting. Available in a wide variety of lumen packs, color temp and options of all type of dimming(Phase Cut/Analogue/DALI), GreenPerform becomes the perfect solution for downlight applications for professional users.

Benefits

- Multiple options in Dimming
- Wide range of lumen pack and CCT
- Long life of 50K hours
- High colour consistency

Features

- Aluminium heat sink for better heat dissipation
- Higher life class of 50K burning hour
- Available in both Dimming & fixed output
- Low Energy consumption- High Efficacy more than 100lm/ Watt
- Suitable for low ceiling heights
- Wide range of lumen packs (600lm-2000lm)

GreenPerform DN391/392/393/394/395 downlight

Application

- Office Lighting
- Shop/Showroom Lighting
- Corridor Lighting
- Meeting & conference room lighting
- Reception & general area Lighting

Versions

