



Continuous slim suspended linear office Luminaire: Performanc and Elegance

Pureline SP680P

The PureLine family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting . The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

Benefits

- Optimized lighting for office space:smooth and comfortable
- Wider distribution allowing wider row spacing and hence reduction in connected load
- Dimmable and fixed output drivers
- Enhance Interiors

Features

- System efficacy more than 100 Lm/W
- Superior light quality with CRI more than 80
- THD Less than 10%
- Wide operating voltage 140-270V
- Suitable for Standalone & Continuous Mounting
- Option of Dimming available
- Up-Down lighting distribution
- Uniform & volumetric light distribution

Pureline SP680P

Application

- Office Lighting
- Meeting & conference room lighting

Versions

