



Best in class Extruded Aluminium batten with high Lumen Efficacy. Sleek but robust design

Smartbright BN100 Batten

High performance LED batten, can replace 2x40W conventional batten suitable for Classroom, hostel room, corridor, small shops, community center, club, small warehouse lighting applications.

Benefits

- Long Useful life
- Volumetric distribution improving safety in industrial environment
- Sleek aesthetic design complements interiors

Features

- Suitable for Surface & suspension mounting
- Extruded aluminium housing
- Slim integrated design, easy to install
- Energy Saving of up to 60% compared to conventional lighting

Application

- General Indoor Lighting
- Industrial usage

Smartbright BN100 Batten

Versions

