



# Best in class Extruded Aluminium batten with high Lumen Efficacy. Sleek but robust design

## Smartbright BN100 Batten

High performance LED batten, can replace 2x40W conventional batten suitable for Classroom, hostel room, corridor, small shops, community center, club, small warehouse lighting applications.

### Benefits

- Long Useful life
- Volumetric distribution improving safety in industrial environment
- Sleek aesthetic design complements interiors

### Features

- Suitable for Surface & suspension mounting
- Extruded aluminium housing
- Slim integrated design, easy to install
- Energy Saving of up to 60% compared to conventional lighting

### Application

- General Indoor Lighting
- Industrial usage

## Smartbright BN100 Batten

### Versions

