



# 1010 Beacon - adding safe and guiding light to your space

## 1010 Beacon

The Hadco 101 series Beacon is available in an all-aluminum, composite and cast bronze housing. It is line voltage luminaire featuring a fully gasketed borosilicate glass refractor lens. Lamping includes incandescent, CFL and HID.

### Benefits

- Durable and lasting construction
- Quick and easy relamping
- Protected against moisture, dust and insects

### Features

- Die cast aluminum construction
- Removable roof
- Silicone gasketing

### Application

- Walkway

## 1010 Beacon

### Versions

