



1020 Large Classic - showcasing the best features of your landscape

1020 Large Classic

The Hadco 1020 Bullyte is an excellent choice for accent lighting. Made from die cast aluminum the 1020 has a fully-adjustable swivel arm with vibration-proof locking teeth. Maximum lamping is a 150W PAR38/R40 incandescent lamp.

Benefits

- Durable and lasting construction
- Precision aiming
- Vibration-proof
- Fade and abrasion resistant

Features

- Die cast aluminum housing
- Fully adjustable swivel arm with locking teeth
- Polyester powdercoat finish

Application

- Walkway

1020 Large Classic

Versions

