



300 – performance. Pure and Simple

300 Emergency Cylinders

The Gardco 300 LINE is a series of compact, high performance cylinder luminaires in a variety of styles. The Emergency style utilizes a 42w compact fluorescent lamp. Housings are diecast aluminum with twin architectural reveals located near the luminaire apertures. A choice of two (2) models, each with two (2) light control styles is available in a wall mounted configuration. Luminaires are finished with a fade and abrasion resistant polyester powder coat offered in five standard colors.

Benefits

- Lasting durability and reliability
- Simplified mounting
- Suitable for a variety of applications
- Minimized glare

Features

- Die cast aluminum construction
- Matching brackets and one-piece luminaire
- Offers a wide choice of baffles and trims
- Recessed optical system

Application

- Education
- Municipal Buildings
- Security Lighting
- Office
- Parking Garages
- Hospitality

300 Emergency Cylinders

Versions

