



300 – performance. Pure and Simple

300 Enclosed Universal

The 300 LINE is a series of compact, high performance cylinder luminaires in a variety of styles and mounting configurations. The enclosed universal style uses high intensity discharge or incandescent lamps and is suitable for areas with direct rainfall. Housings are diecast aluminum with architectural twin reveals located near the luminaire aperture. A clear convex lens is offered with a knuckle mounted configuration. Luminaires are finished with a durable textured semi-gloss TGIC powderpaint in one of six (6) standard colors.

Benefits

- Lasting durability and reliability
- Simplified mounting
- Suitable for a variety of applications
- Minimized glare

Features

- Die cast aluminum construction
- Matching brackets and one-piece luminaire
- Offers a wide choice of baffles and trims
- Recessed optical system

Application

- Education
- Municipal Buildings
- Security Lighting
- Office
- Parking Garages
- Hospitality

300 Enclosed Universal

Versions

