



# 301 - performance. Pure and Simple

## 301 Up/Down Cylinder

Gardco Lighting has earned a reputation for transforming utilitarian outdoor wall-mounted lighting fixtures into contemporary architectural elements with state of the art photometric performance. The 301 Up/Down Cylinder line continues in this superb tradition. Traditionally up/down wall cylinders have required two lamps and ballasts. This has necessitated oversized luminaires that were often out of scale for many typical mounting heights. The 301 Series, through intelligent design, utilizes a single lamp and ballast to achieve the downlighting and uplighting luminaire functions. The resulting form is a remarkably compact cylinder featuring the trademark subtle twin reveals and assiduous design sensitivity. Typical inefficient cylinders have historically simply produced small circles of light, hot spots on vertical surfaces, or discomforting aperture brightness. The Gardco 301 Series however offers an unequalled variety of optical systems each with specific design attention paid to the lighting design objective. The use of highly specular spun and faceted reflectors assures that the 301 Series Cylinders produce the appropriate light levels and distribution. The regressed lamp position, carefully positioned reflector elements, egg crate louvers, and baffle option all provide exceptional control of high angle luminaire brightness. The variety of uplight options offered in the 301 Line demonstrates Gardco's keen understanding of the importance of the illumination of all surfaces. The illumination of walls, columns, and ceiling canopies provides visual interest, establishes site boundaries and guides pedestrian traffic. The use of high performance reflector systems and obscuring lenses ensures that the uplight distributions are uniform and free of hot spots. Recognizing that different lighting tasks require different optical system/lamp combinations, the 301 Line has the broadest offering of downlighting and uplighting options available in a wall mounted luminaire

### Benefits

- Lasting durability and reliability
- Simplified mounting
- Suitable for a variety of applications
- Minimized glare

## 301 Up/Down Cylinder

### Features

- Die cast aluminum construction
- Matching brackets and one-piece luminaire
- Offers a wide choice of baffles and trims
- Recessed optical system

### Application

- Education
- Municipal Buildings
- Security Lighting
- Office
- Parking Garages
- Hospitality

### Versions

